




- Compact short-stroke cylinders with standard port pattern from $\varnothing$ 32 mm
- Optimised fitting space and height
- Adaptable housing and piston rod variants for individual applications

Short-stroke cylinders ADVC/AEVC

Key features

FESTO



Brief description

-  - Diameter
4 ... 100 mm
-  - Stroke length
2.5 ... 25 mm


Short-stroke cylinders are ideal for clamping tasks with short strokes, e.g. in retaining devices.

The cylinders offer:


- Rapid response with applied pressure
- Large clamping forces in comparison to their size
- Minimal installation space

- Integrated sensor slots for contacting or contactless proximity sensors
- Mounting hole pattern to VDMA 24 562 for Ø 32 ... 100 mm


Fitting space comparison with 10 mm stroke



100%
Standard cylinder
DNC



45%
Compact cylinder
ADVU




33%
Short-stroke cylinder
ADVC

Sensor slots



T-slot for proximity sensor
SME/SMT-8



C-slot for proximity sensor SME/
SMT-10

Short-stroke cylinders ADVC/AEVC

Type codes



		ADVC	–	6	–	5	–	A	–	P	–	A
Type												
ADVC	Double acting short stroke cylinder											
AEVC	Single-acting short stroke cylinder											
Piston Ø [mm]												
Stroke [mm]												
Piston rod thread												
A	Male thread											
I	Female thread											
	Without thread											
Cushioning												
P	Flexible cushioning rings/plates at both ends											
Position sensing												
	No position sensing											
A	For proximity sensing											

Short-stroke cylinders ADVC/AEVC

Product range overview

FESTO

Function	Version	Type	Piston Ø [mm]	Stroke [mm]	Position sensing
Double-acting	Without position sensing				
		ADVC Ø 4 ... 25	4	2.5; 5	—
			6, 10, 12	5, 10	
			16, 20, 25	5, 10, 15, 20, 25	
		ADVC Ø 32 ... 100	32, 40	5, 10, 15, 20, 25	—
			50, 63, 80, 100	10, 15, 20, 25	
	With position sensing				
		ADVC-...-A Ø 6 ... 25	6, 10, 12	5, 10	■
			16, 20, 25	5, 10, 15, 20, 25	
		ADVC-...-A Ø 32 ... 100	32, 40	5, 10, 15, 20, 25	■
			50, 63, 80, 100	10, 15, 20, 25	
Single-acting	Without position sensing				
		AEVC Ø 4 ... 25	4	2.5; 5	—
			6, 10, 12	5, 10	
			16, 20, 25	5, 10, 25	
		AEVC Ø 32 ... 100	32	5, 10, 25	—
			40, 50, 63, 80, 100	10, 25	
	With position sensing				
		AEVC-...-A Ø 6 ... 25	6, 10, 12	5, 10	■
			16, 20, 25	5, 10, 25	
		AEVC-...-A Ø 32 ... 100	32	5, 10, 25	■
			40, 50, 63, 80, 100	10, 25	

Short-stroke cylinders ADVC/AEVC

Product range overview

FESTO


Type	Piston rod			Cushioning	➔ Page/Internet
	With male thread	With female thread	Without thread		
Without position sensing					
ADVC Ø 4 ... 25	■	■ From Ø 12	■ Ø 4 ... 12	■	8
ADVC Ø 32 ... 100	■	■	–	■	8
With position sensing					
ADVC-...-A Ø 6 ... 25	■	■ From Ø 12	■ Ø 6 ... 12	■	15
ADVC-...-A Ø 32 ... 100	■	■	–	■	15
Without position sensing					
AEVC Ø 4 ... 25	■	■ From Ø 12	■ Ø 4 ... 12	■	21
AEVC Ø 32 ... 100	■	■	–	■	21
With position sensing					
AEVC-...-A Ø 6 ... 25	■	■ From Ø 12	■ Ø 6 ... 12	■	28
AEVC-...-A Ø 32 ... 100	■	■	–	■	28

Short-stroke cylinders ADVC/AEVC

Peripherals overview


FESTO

Ø 32 ... 100 mm




Ø 4 ... 25 mm

Without position sensing



Ø 6 ... 25 mm

With position sensing



Short-stroke cylinders ADVC/AEVC

Peripherals overview


FESTO

Mounting attachments and accessories						
		Brief description	Piston Ø			➔ Page/Internet
			4, 6, 12	10, 16 ... 25	32 ... 100	
1	Mounting screws	Not included in scope of delivery	■ DIN 84	■ DIN 912	■ DIN 912	–
1	Mounting screws for Ø 80, 100	Not included in scope of delivery	–	–	■	43
2	Foot mounting HNC	For bearing and end caps	–	–	■	35
3	Flange mounting FNC	For bearing or end caps	–	–	■	36
4	Trunnion flange ZNCF	For bearing or end caps	–	–	■	37
5	Trunnion support LNZG	–	–	–	■	38
6	Swivel flange SNC	For end caps	–	–	■	39
7	Clevis foot LSNG	With spherical bearing	–	–	■	43
8	Clevis foot LSNSG	Weld-on, with spherical bearing	–	–	■	43
9	Swivel flange SNCS	With spherical bearing for end caps	–	–	■	41
10	Clevis foot LBG	–	–	–	■	43
11	Swivel flange SNCL	For end caps	–	–	■	42
12	Swivel flange SNCB	For end caps	–	–	■	40
13	Clevis foot LNG	–	–	–	■	43
14	Clevis foot LSN	With spherical bearing	–	–	■	43
15	Adapter kit DPNC	For connecting two cylinders with identical piston diameter to form a multi-position cylinder	–	–	■	34
16	Rod eye SGS	With spherical bearing	–	■	■	44
17	Right-angle clevis foot LQG	–	–	■	■	43
18	Rod clevis SGA	With male thread	–	–	■	44
19	Coupling piece KSG	For compensating radial deviations	–	–	■	44
20	Rod clevis SG	Permits a swivelling movement of the cylinder in one plane	–	■	■	44
21	Self-aligning rod coupler FK	For compensating radial and angular deviations	■ Ø 12	■	■	44
22	Slot cover ABP-5-S	To protect the sensor cable and keep dirt out of the sensor slots	–	–	■	45
23	Proximity sensors SME/SMT-8	Can be integrated in the cylinder profile barrel	–	–	■	45
24	Proximity sensors SME/SMT-10	Can be integrated in the cylinder profile barrel	–	■	■	46
25	One-way flow control valve GRLA	To regulate speed	■	■	■	46
26	Push-in fitting QS	For connecting compressed air tubing with standard external diameters	■	■	■	quick star

Short-stroke cylinders ADVC



Technical data, double-acting – without position sensing

FESTO



Ø - Diameter
4 ... 100 mm

— Stroke length
2.5 ... 25 mm



General technical data													
Piston Ø	4	6	10	12	16	20	25	32	40	50	63	80	100
Pneumatic connection	M3	M3	M5	M5	M5	M5	M5	G1/8	G1/8	G1/8	G1/8	G1/8	G1/4
Piston rod with female thread	–	–	–	■	■	■	■	■	■	■	■	■	■
Piston rod with male thread	■	■	■	■	■	■	■	■	■	■	■	■	■
Piston rod without thread	■	■	■	■	–	–	–	–	–	–	–	–	–
Operating medium	Filtered compressed air, lubricated or unlubricated												
Constructional design	Piston												
	Piston rod												
Cushioning	Flexible cushioning rings/plates at both ends												
Type of mounting	Via through-holes							Via through-holes					
	–							Via accessories					
Mounting position	Any												

Operating conditions													
Piston Ø	4	6	10	12	16	20	25	32	40	50	63	80	100
Operating pressure [bar]	2 ... 8	1.5 ... 8	1 ... 8	1 ... 10				0.6 ... 10					
Ambient temperature [°C]	-20 ... +80												
Corrosion resistance class CRC ¹⁾	1												

1) Corrosion resistance class 1 according to Festo standard 940 070

Components requiring low corrosion resistance. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers

Short-stroke cylinders ADVC

FESTO

Technical data, double-acting – without position sensing


Forces [N] and impact energy [J]													
Piston Ø	4	6	10	12	16	20	25	32	40	50	63	80	100
Theoretical force at 6 bar, advancing	7.5	17	47	68	121	189	295	483	754	1,178	1,870	3,016	4,712
Theoretical force at 6 bar, returning	5.7	13	40	51	91	141	247	415	686	1,056	1,750	2,847	4,418
Max. impact energy at end positions	0.003	0.005	0.03	0.06	0.10	0.14	0.18	0.26	0.36	0.60	0.64	0.90	1.20

Product weight [g]													
Stroke [mm]	Piston Ø												
	4	6	10	12	16	20	25	32	40	50	63	80	100
2.5	4	–	–	–	–	–	–	–	–	–	–	–	–
5	4.5	12.5	23	34	68	112	135	280	350	–	–	–	–
10	–	16	26	42	76	124	150	300	380	470	600	1,570	2,480
15	–	–	–	–	84	136	165	320	410	505	650	1,655	2,570
20	–	–	–	–	92	148	180	340	440	540	700	1,740	2,660
25	–	–	–	–	100	160	195	360	470	575	750	1,825	2,750

Moving load [g]													
Stroke [mm]	Piston Ø												
	4	6	10	12	16	20	25	32	40	50	63	80	100
2.5	0.2	–	–	–	–	–	–	–	–	–	–	–	–
5	0.25	1.2	2.8	6.6	11	22	27	46	69	–	–	–	–
10	–	1.5	3.3	7.7	13	25	30	51	74	127	178	339	719
15	–	–	–	–	15	28	33	56	79	135	186	351	739
20	–	–	–	–	17	31	36	61	84	143	194	363	759
25	–	–	–	–	19	34	39	66	89	151	202	375	779

Materials

Sectional view



Short-stroke cylinder	Ø 4	Ø 6 ... 100
1 Cylinder barrel	Anodised aluminium	Anodised aluminium
2 Cover cap	Anodised aluminium	Anodised aluminium
3 Piston rod	Anodised aluminium	High-alloy steel
4 Rod seal	Nitrile rubber	Polyurethane
Note on material	Free of copper, PTFE and silicone	Free of copper, PTFE and silicone

Short-stroke cylinders ADVC

Technical data, double-acting – without position sensing

FESTO


Dimensions

Download CAD data → www.festo.com

Ø 4 ... 25 mm


ADVC-...-I-P

Piston rod with female thread




ADVC-...-A-P

Piston rod with male thread



ADVC-...-P

Piston rod without thread



- - Note

Ø 4 mm

Do not exceed maximum screw-in depth of 3 mm and maximum tightening torque of 0.7 Nm.

Ø 10 mm

Depending on tolerance, the bearing cap may project by up to 0.65 mm.

Ø 12 mm

Depending on tolerance, the bearing cap may project by up to 0.35 mm.

+ = plus stroke length

Short-stroke cylinders ADVC

Technical data, double-acting – without position sensing

FESTO

Ø [mm]	Stroke [mm]	AF min.	AM -0.5	D1 Ø max.	D2 Ø	E max.	EE	FB Ø	KF	KK	L2 +0.2	L3
4	2.5	–	6	–	3.3 +0.1	10	M3	1.8	–	M2	10.5	1.8
	5											
6	5	–	6	–	5 +0.1	13	M3	2.9	–	M3	11	2.9
	10											
10	5	–	8	7.5	5.8 +0.1	18	M5	3.4	–	M4	16	3.4
	10										14	
12	5	8	8	10.7	6 H13	20	M5	3.4	M3	M5	18	3.4
	10											
16	5	10	12	–	8 H13	25	M5	4.5	M4	M6	18	4.6
	10											
	15											
	20											
	25											
20	5	12	12	–	10 H13	32	M5	5.5	M5	M8	22	5.7
	10											
	15											
	20											
	25											
25	5	12	12	–	10 H13	38	M5	5.5	M5	M8	22.5	5.7
	10											
	15											
	20											
	25											

Ø	Stroke	L4	L5	L6	MM Ø	P1	PL	T4	TG	U0	WH	ZJ	≈G1
[mm]	[mm]			max.					±0.1	max.		±0.8	
4	2.5	4	6.5	–	2	3.7	3.2	–	5.8	10	1	11.5	–
	5												
6	5	6	9	–	3	4.7	3	–	7	14	1	12	–
	10												
10	5	8	11.5	0.7	4	5.2	5.2	–	11	19	1.5	17.5	–
	10					6	5.5					15.5	
12	5	9	13	0.4	6	5.75	5.75	1.5	13	22	4	22	5
	10					9	6						
16	5	11.5	16.5	–	8	6	6	2	15	27	4	22	7
	10					7.5							
	15												
	20												
	25												
20	5	15	21	–	10	7.5	7	2	20	34	5	27	9
	10												
	15												
	20												
	25												
25	5	15.5	21.5	–	10	8	6.5	2	26	37	5	27.5	9
	10												
	15												
	20												
	25												

Short-stroke cylinders ADVC

Technical data, double-acting – without position sensing

FESTO


Dimensions

Download CAD data → www.festo.com

Ø 32 ... 100 mm



ADVC-...-I-P

Piston rod with female thread



ADVC-...-A-P**

Piston rod with male thread



+ = plus stroke length

Ø	AF	AM	BG*	D2	E	EE	FB	H	KF	KK
[mm]	min.	-0.5	min.	Ø F9	max.		Ø			
32	12	14	21.7	9	45	G1/8	5.2	7	M6	M10x1.25
40	12	14	21.7	9	53.5	G1/8	5.2	7	M6	M10x1.25
50	16	16	22.8	11	63.5	G1/8	6.8	7	M8	M12x1.25
63	16	16	22.8	11	75	G1/8	6.8	7.5	M8	M12x1.25
80	20	22	25	14	93	G1/8	8.5	7	M10	M16x1.5
100	24	28	25	14	113	G1/4	8.5	13	M12	M20x1.5

Ø	L2	L3	MM	P1	PL	RT	T4	TG	WH	ZJ	⌀1
[mm]	+0.2		Ø					±0.1		±0.8	
32	29	5.7	12	9	8.5	M6	2.6	32.5	6	35	10
40	29.5	5.7	12	11	9	M6	2.6	38	6	35.5	10
50	28	6.8	16	11.3	9.5	M8	3.3	46.5	8	36	13
63	35	6.8	16	12.5	11.5	M8	3.3	56.5	8	43	13
80	40	9	20	15	15	M10	4.7	72	8	48	17
100	49	9	25	16.5	19	M10	6.1	89	10	59	22

* Continuous thread with short overall length

** Nut for piston rod thread included in scope of delivery

Short-stroke cylinders ADVC

FESTO

Technical data, double-acting – without position sensing

Ordering data								
Type	Piston Ø	Stroke	Piston rod with male thread		Piston rod with female thread		Piston rod without thread	
	[mm]	[mm]	Part No.	Type	Part No.	Type	Part No.	Type
	4	2.5	188 054	ADVC-4-2,5-A-P	—		526 897	ADVC-4-2,5-P
		5	188 055	ADVC-4-5-A-P			526 898	ADVC-4-5-P
	6	5	188 066	ADVC-6-5-A-P	—		526 899	ADVC-6-5-P
		10	188 067	ADVC-6-10-A-P			526 900	ADVC-6-10-P
	10	5	188 078	ADVC-10-5-A-P	—		526 903	ADVC-10-5-P
		10	188 079	ADVC-10-10-A-P			526 904	ADVC-10-10-P
	12	5	188 094	ADVC-12-5-A-P	188 090	ADVC-12-5-I-P	530 568	ADVC-12-5-P
		10	188 095	ADVC-12-10-A-P	188 091	ADVC-12-10-I-P	530 569	ADVC-12-10-P
	16	5	188 123	ADVC-16-5-A-P	188 113	ADVC-16-5-I-P	—	
		10	188 124	ADVC-16-10-A-P	188 114	ADVC-16-10-I-P		
		15	188 125	ADVC-16-15-A-P	188 115	ADVC-16-15-I-P		
		20	188 126	ADVC-16-20-A-P	188 116	ADVC-16-20-I-P		
		25	188 127	ADVC-16-25-A-P	188 117	ADVC-16-25-I-P		
	20	5	188 155	ADVC-20-5-A-P	188 145	ADVC-20-5-I-P	—	
		10	188 156	ADVC-20-10-A-P	188 146	ADVC-20-10-I-P		
		15	188 157	ADVC-20-15-A-P	188 147	ADVC-20-15-I-P		
		20	188 158	ADVC-20-20-A-P	188 148	ADVC-20-20-I-P		
		25	188 159	ADVC-20-25-A-P	188 149	ADVC-20-25-I-P		
	25	5	188 187	ADVC-25-5-A-P	188 177	ADVC-25-5-I-P	—	
		10	188 188	ADVC-25-10-A-P	188 178	ADVC-25-10-I-P		
		15	188 189	ADVC-25-15-A-P	188 179	ADVC-25-15-I-P		
		20	188 190	ADVC-25-20-A-P	188 180	ADVC-25-20-I-P		
		25	188 191	ADVC-25-25-A-P	188 181	ADVC-25-25-I-P		

Short-stroke cylinders ADVC

Technical data, double-acting – without position sensing


FESTO

Ordering data					
Type	Piston Ø [mm]	Stroke [mm]	Piston rod with male thread		Piston rod with female thread
			Part No.	Type	Part No. Type
	32	5	188 219	ADVC-32-5-A-P	188 209 ADVC-32-5-I-P
		10	188 220	ADVC-32-10-A-P	188 210 ADVC-32-10-I-P
		15	188 221	ADVC-32-15-A-P	188 211 ADVC-32-15-I-P
		20	188 222	ADVC-32-20-A-P	188 212 ADVC-32-20-I-P
		25	188 223	ADVC-32-25-A-P	188 213 ADVC-32-25-I-P
	40	5	188 247	ADVC-40-5-A-P	188 237 ADVC-40-5-I-P
		10	188 248	ADVC-40-10-A-P	188 238 ADVC-40-10-I-P
		15	188 249	ADVC-40-15-A-P	188 239 ADVC-40-15-I-P
		20	188 250	ADVC-40-20-A-P	188 240 ADVC-40-20-I-P
		25	188 251	ADVC-40-25-A-P	188 241 ADVC-40-25-I-P
	50	10	188 272	ADVC-50-10-A-P	188 264 ADVC-50-10-I-P
		15	188 273	ADVC-50-15-A-P	188 265 ADVC-50-15-I-P
		20	188 274	ADVC-50-20-A-P	188 266 ADVC-50-20-I-P
		25	188 275	ADVC-50-25-A-P	188 267 ADVC-50-25-I-P
	63	10	188 296	ADVC-63-10-A-P	188 288 ADVC-63-10-I-P
		15	188 297	ADVC-63-15-A-P	188 289 ADVC-63-15-I-P
		20	188 298	ADVC-63-20-A-P	188 290 ADVC-63-20-I-P
		25	188 299	ADVC-63-25-A-P	188 291 ADVC-63-25-I-P
	80	10	188 320	ADVC-80-10-A-P	188 312 ADVC-80-10-I-P
		15	188 321	ADVC-80-15-A-P	188 313 ADVC-80-15-I-P
		20	188 322	ADVC-80-20-A-P	188 314 ADVC-80-20-I-P
		25	188 323	ADVC-80-25-A-P	188 315 ADVC-80-25-I-P
	100	10	188 344	ADVC-100-10-A-P	188 336 ADVC-100-10-I-P
		15	188 345	ADVC-100-15-A-P	188 337 ADVC-100-15-I-P
		20	188 346	ADVC-100-20-A-P	188 338 ADVC-100-20-I-P
		25	188 347	ADVC-100-25-A-P	188 339 ADVC-100-25-I-P

Short-stroke cylinders ADVC


Technical data, double-acting – with position sensing

FESTO




Ø - Diameter
6 ... 100 mm

└ - Stroke length
5 ... 25 mm



Ø 6 ... 25



Ø 32 ... 100

General technical data												
Piston Ø	6	10	12	16	20	25	32	40	50	63	80	100
Pneumatic connection	M3	M5	M5	M5	M5	M5	G1/8	G1/8	G1/8	G1/8	G1/8	G1/4
Piston rod with female thread	–	–	■	■	■	■	■	■	■	■	■	■
Piston rod with male thread	■	■	■	■	■	■	■	■	■	■	■	■
Piston rod without thread	■	■	■	–	–	–	–	–	–	–	–	–
Operating medium	Filtered compressed air, lubricated or unlubricated											
Constructional design	Piston											
	Piston rod											
Cushioning	Flexible cushioning rings/plates at both ends											
Position sensing	For proximity sensing											
Type of mounting	Via through-holes						Via through-holes					
	–						Via accessories					
Mounting position	Any											

Operating conditions												
Piston Ø	6	10	12	16	20	25	32	40	50	63	80	100
Operating pressure [bar]	1.5 ... 8	1 ... 8	1 ... 10				0.6 ... 10					
Ambient temperature [°C]	–20 ... +80 (note operating range of proximity sensors)											
Corrosion resistance class CRC ¹⁾	1											

1) Corrosion resistance class 1 according to Festo standard 940 070

Components requiring low corrosion resistance. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers

Short-stroke cylinders ADVC

Technical data, double-acting – with position sensing

FESTO


Forces [N] and impact energy [J]												
Piston Ø	6	10	12	16	20	25	32	40	50	63	80	100
Theoretical force at 6 bar, advancing	17	47	68	121	189	295	483	754	1,178	1,870	3,016	4,712
Theoretical force at 6 bar, returning	13	40	51	91	141	247	415	686	1,056	1,750	2,847	4,418
Max. impact energy at end positions	0.005	0.03	0.06	0.10	0.14	0.18	0.26	0.36	0.60	0.64	0.90	1.20

Product weight [g]												
Stroke [mm]	Piston Ø											
	6	10	12	16	20	25	32	40	50	63	80	100
5	20	37	70	98	162	195	320	460	–	–	–	–
10	23	45	79	106	174	210	340	490	630	710	1,940	2,970
15	–	–	–	114	186	225	360	520	665	760	2,025	3,060
20	–	–	–	122	198	240	380	550	700	810	2,110	3,150
25	–	–	–	130	210	255	400	580	735	860	2,195	3,240

Moving load [g]												
Stroke [mm]	Piston Ø											
	6	10	12	16	20	25	32	40	50	63	80	100
5	1.7	3.2	8.5	15	26	32	50	66	–	–	–	–
10	2	3.7	9.6	17	29	35	55	71	116	158	289	555
15	–	–	–	19	32	38	60	76	124	166	301	575
20	–	–	–	21	35	41	65	81	132	174	313	595
25	–	–	–	23	38	44	70	86	140	182	325	615

Materials

Sectional view



Short-stroke cylinder	
1	Cylinder barrel Anodised aluminium
2	Cover cap Anodised aluminium
3	Piston rod High-alloy steel
4	Rod seal Polyurethane
Note on material Free of copper, PTFE and silicone	

Short-stroke cylinders ADVC

Technical data, double-acting – with position sensing

FESTO


Dimensions

Download CAD data → www.festo.com

Ø 6 ... 25 mm

ADVC-...-I-P-A

Piston rod with female thread



- Note

Ø 10 mm


Depending on tolerance, the bearing cap may project by up to 0.65 mm.

Ø 12 mm

Depending on tolerance, the bearing cap may project by up to 0.35 mm.


ADVC-...-A-P-A

Piston rod with male thread



ADVC-...-P-A

Piston rod without thread



+ = plus stroke length

1 Slot for proximity sensor
SME/SMT-10

Ø	AF	AM	D1	D2	E	EE	FB	KF	KK	L2	L3
[mm]	min.	-0.5	Ø max.	Ø	max.		Ø			+0.2	
6	–	6	–	5 +0.1	16	M3	2.9	–	M3	20.5	2.9
10	–	8	7.5	5.8 +0.1	21	M5	3.4	–	M4	22	3.4
12	8	8	10.7	6 H13	24	M5	3.4	M3	M5	31	3.4
16	10	12	–	8 H13	28	M5	4.5	M4	M6	30	4.6
20	12	12	–	10 H13	32	M5	5.5	M5	M8	32	5.7
25	12	12	–	10 H13	38	M5	5.5	M5	M8	32	5.7

Ø	L4	L5	L6	MM	P1	PL	T4	TG	U0	WH	ZJ	≈C1
[mm]			max.	Ø				±0.1	max.		±0.8	
6	5	8	–	3	5.2	3	–	10	16	1	21.5	–
10	7	10.5	0.7	4	6	6	–	14	22	1.5	23.5	–
12	8	12	0.4	6	7	6	1.5	16	26	4	35	5
16	12	17	–	8	8	6	2	18	32	4	34	7
20	15	21	–	10	7.5	7	2	20	39	5	37	9
25	15.5	21.5	–	10	10	6	2	26	42	5	37	9

Short-stroke cylinders ADVC

Technical data, double-acting – with position sensing

FESTO

Dimensions

Download CAD data → www.festo.com


Ø 32 ... 100 mm

ADVC-...-I-P-A

Piston rod with female thread


+ = plus stroke length

- 1 Slot for proximity sensor SME/SMT-8
- 2 Slot for proximity sensor SME/SMT-10



ADVC-...-A-P-A**

Piston rod with male thread



Ø	AF	AM	BG*	D2	E	EE	FB	H	KF	KK
[mm]	min.	-0.5	min.	Ø F9	max.		Ø			
32	12	14	21.7	9	45	G1/8	5.2	7	M6	M10x1.25
40	12	14	21.7	9	53.5	G1/8	5.2	7	M6	M10x1.25
50	16	16	22.8	11	63.5	G1/8	6.8	7	M8	M12x1.25
63	16	16	22.8	11	75	G1/8	6.8	7.5	M8	M12x1.25
80	20	22	25	14	93	G1/8	8.5	7	M10	M16x1.5
100	24	28	25	14	113	G1/4	8.5	13	M12	M20x1.5

Ø	L2	L3	MM	P1	PL	RT	T4	TG	WH	ZJ	±C1
[mm]	+0.2		Ø					±0.1		±0.8	
32	33	5.7	12	9	8.5	M6	2.6	32.5	6	39	10
40	38	5.7	12	13.5	9.5	M6	2.6	38	6	44	10
50	38	6.8	16	11.3	9.5	M8	3.3	46.5	8	46	13
63	41	6.8	16	12.5	10.5	M8	3.3	56.5	8	49	13
80	49	9	20	15	8.5	M10	4.7	72	8	57	17
100	58	9	25	16.5	10.5	M10	6.1	89	10	68	22

* Continuous thread with short overall length

** Nut for piston rod thread included in scope of delivery

Short-stroke cylinders ADVC

Technical data, double-acting – with position sensing

FESTO

Ordering data									
Type	Piston Ø	Stroke	Piston rod with male thread		Piston rod with female thread		Piston rod without thread		
	[mm]		Part No.	Type	Part No.	Type	Part No.	Type	
	6	5	188 064	ADVC-6-5-A-P-A	–		526 901	ADVC-6-5-P-A	
		10	188 065	ADVC-6-10-A-P-A			526 902	ADVC-6-10-P-A	
	10	5	188 076	ADVC-10-5-A-P-A	–		526 905	ADVC-10-5-P-A	
		10	188 077	ADVC-10-10-A-P-A			526 906	ADVC-10-10-P-A	
	12	5	188 092	ADVC-12-5-A-P-A	188 088	ADVC-12-5-I-P-A	530 572	ADVC-12-5-P-A	
		10	188 093	ADVC-12-10-A-P-A	188 089	ADVC-12-10-I-P-A	530 573	ADVC-12-10-P-A	
	16	5	188 118	ADVC-16-5-A-P-A	188 108	ADVC-16-5-I-P-A	–		
		10	188 119	ADVC-16-10-A-P-A	188 109	ADVC-16-10-I-P-A			
		15	188 120	ADVC-16-15-A-P-A	188 110	ADVC-16-15-I-P-A			
		20	188 121	ADVC-16-20-A-P-A	188 111	ADVC-16-20-I-P-A			
		25	188 122	ADVC-16-25-A-P-A	188 112	ADVC-16-25-I-P-A			
	20	5	188 150	ADVC-20-5-A-P-A	188 140	ADVC-20-5-I-P-A	–		
		10	188 151	ADVC-20-10-A-P-A	188 141	ADVC-20-10-I-P-A			
		15	188 152	ADVC-20-15-A-P-A	188 142	ADVC-20-15-I-P-A			
		20	188 153	ADVC-20-20-A-P-A	188 143	ADVC-20-20-I-P-A			
		25	188 154	ADVC-20-25-A-P-A	188 144	ADVC-20-25-I-P-A			
	25	5	188 182	ADVC-25-5-A-P-A	188 172	ADVC-25-5-I-P-A	–		
		10	188 183	ADVC-25-10-A-P-A	188 173	ADVC-25-10-I-P-A			
		15	188 184	ADVC-25-15-A-P-A	188 174	ADVC-25-15-I-P-A			
		20	188 185	ADVC-25-20-A-P-A	188 175	ADVC-25-20-I-P-A			
		25	188 186	ADVC-25-25-A-P-A	188 176	ADVC-25-25-I-P-A			

Short-stroke cylinders ADVC

Technical data, double-acting – with position sensing

FESTO

Ordering data					
Type	Piston Ø [mm]	Stroke [mm]	Piston rod with male thread		Piston rod with female thread
			Part No.	Type	Part No. Type
	32	5	188 214	ADVC-32-5-A-P-A	188 204 ADVC-32-5-I-P-A
		10	188 215	ADVC-32-10-A-P-A	188 205 ADVC-32-10-I-P-A
		15	188 216	ADVC-32-15-A-P-A	188 206 ADVC-32-15-I-P-A
		20	188 217	ADVC-32-20-A-P-A	188 207 ADVC-32-20-I-P-A
		25	188 218	ADVC-32-25-A-P-A	188 208 ADVC-32-25-I-P-A
	40	5	188 242	ADVC-40-5-A-P-A	188 232 ADVC-40-5-I-P-A
		10	188 243	ADVC-40-10-A-P-A	188 233 ADVC-40-10-I-P-A
		15	188 244	ADVC-40-15-A-P-A	188 234 ADVC-40-15-I-P-A
		20	188 245	ADVC-40-20-A-P-A	188 235 ADVC-40-20-I-P-A
		25	188 246	ADVC-40-25-A-P-A	188 236 ADVC-40-25-I-P-A
	50	10	188 268	ADVC-50-10-A-P-A	188 260 ADVC-50-10-I-P-A
		15	188 269	ADVC-50-15-A-P-A	188 261 ADVC-50-15-I-P-A
		20	188 270	ADVC-50-20-A-P-A	188 262 ADVC-50-20-I-P-A
		25	188 271	ADVC-50-25-A-P-A	188 263 ADVC-50-25-I-P-A
	63	10	188 292	ADVC-63-10-A-P-A	188 284 ADVC-63-10-I-P-A
		15	188 293	ADVC-63-15-A-P-A	188 285 ADVC-63-15-I-P-A
		20	188 294	ADVC-63-20-A-P-A	188 286 ADVC-63-20-I-P-A
		25	188 295	ADVC-63-25-A-P-A	188 287 ADVC-63-25-I-P-A
	80	10	188 316	ADVC-80-10-A-P-A	188 308 ADVC-80-10-I-P-A
		15	188 317	ADVC-80-15-A-P-A	188 309 ADVC-80-15-I-P-A
		20	188 318	ADVC-80-20-A-P-A	188 310 ADVC-80-20-I-P-A
		25	188 319	ADVC-80-25-A-P-A	188 311 ADVC-80-25-I-P-A
	100	10	188 340	ADVC-100-10-A-P-A	188 332 ADVC-100-10-I-P-A
		15	188 341	ADVC-100-15-A-P-A	188 333 ADVC-100-15-I-P-A
		20	188 342	ADVC-100-20-A-P-A	188 334 ADVC-100-20-I-P-A
		25	188 343	ADVC-100-25-A-P-A	188 335 ADVC-100-25-I-P-A

Short-stroke cylinders AEVC


Technical data, single-acting – without position sensing

FESTO




Ø - Diameter
4 ... 100 mm

l - Stroke length
2.5 ... 25 mm



Ø 4 ... 25



Ø 32 ... 100

General technical data													
Piston Ø	4	6	10	12	16	20	25	32	40	50	63	80	100
Pneumatic connection	M3	M3	M5	M5	M5	M5	M5	G1/8	G1/8	G1/8	G1/8	G1/8	G1/4
Piston rod with female thread	–	–	–	■	■	■	■	■	■	■	■	■	■
Piston rod with male thread	■	■	■	■	■	■	■	■	■	■	■	■	■
Piston rod without thread	■	■	■	■	–	–	–	–	–	–	–	–	–
Operating medium	Filtered compressed air, lubricated or unlubricated												
Constructional design	Piston												
	Piston rod												
Cushioning	Flexible cushioning rings/plates at both ends												
Type of mounting	Via through-holes							Via through-holes					
	–							Via accessories					
Mounting position	Any												

Operating conditions													
Piston Ø	4	6	10	12	16	20	25	32	40	50	63	80	100
Operating pressure [bar]	2.5 ... 8	2 ... 8	1.5 ... 8	1.5 ... 10				1 ... 10					
Ambient temperature [°C]	–20 ... +80												
Corrosion resistance class CRC ¹⁾	1												

1) Corrosion resistance class 1 according to Festo standard 940 070

Components requiring low corrosion resistance. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers

Short-stroke cylinders AEVC

Technical data, single-acting – without position sensing

FESTO

Forces [N] and impact energy [J]													
Piston Ø	4	6	10	12	16	20	25	32	40	50	63	80	100
Theoretical force at 6 bar, advancing	5	11	41	59	105	170	270	450	700	1,120	1,800	2,900	4,500
Theoretical force at 6 bar, returning	1	3	3	4	5	10 ¹⁾	15	22	28	40	50	85	140
Max. impact energy at end positions	0.003	0.005	0.03	0.06	0.10	0.14	0.18	0.26	0.36	0.60	0.64	0.90	1.20

1) AEVC-20-5-... = 5 N

 Note		The degree of friction depends upon the mounting position, and the type of load involved. Single-acting cylinders should as far as possible be operated without lateral forces.
--	--	---

Product weight [g]													
Stroke [mm]	Piston Ø												
	4	6	10	12	16	20	25	32	40	50	63	80	100
2.5	3.7	–	–	–	–	–	–	–	–	–	–	–	–
5	4.5	12	17	24	60	85	130	220	–	–	–	–	–
10	–	18	24	40	80	130	160	290	370	410	490	1,900	2,850
25	–	–	–	–	150	200	250	400	560	680	770	2,400	3,500

Moving load [g]													
Stroke [mm]	Piston Ø												
	4	6	10	12	16	20	25	32	40	50	63	80	100
2.5	0.15	–	–	–	–	–	–	–	–	–	–	–	–
5	0.2	1	2	4.4	8	14	22	40	–	–	–	–	–
10	–	1.4	2.6	6.9	11	21	25	48	65	105	157	327	678
25	–	–	–	–	19	32	37	62	83	140	191	365	739


Short-stroke cylinders AEVC

Technical data, single-acting – without position sensing

FESTO

Materials

Sectional view



Short-stroke cylinder	Ø 4	Ø 6 ... 100
1 Cylinder barrel	Anodised aluminium	Anodised aluminium
2 Cover cap	Anodised aluminium	Anodised aluminium
3 Piston rod	Anodised aluminium	High-alloy steel
4 Rod seal	Nitrile rubber	Polyurethane
Note on material	Free of copper, PTFE and silicone	Free of copper, PTFE and silicone

Short-stroke cylinders AEVC

Technical data, single-acting – without position sensing

FESTO


Dimensions

Download CAD data → www.festo.com

Ø 4 ... 25 mm

AEVC-...-I-P

Piston rod with female thread



Note

Ø 10 mm


Depending on tolerance, the bearing cap may project by up to 0.65 mm.

Ø 12 mm

Depending on tolerance, the bearing cap may project by up to 0.35 mm.


AEVC-...-A-P

Piston rod with male thread



AEVC-...-P

Piston rod without thread



+ = plus stroke length

Short-stroke cylinders AEVC

Technical data, single-acting – without position sensing

FESTO

Ø	Stroke	AF	AM	D1 Ø	D2 Ø	E	EE	FB Ø	KF	KK	L2	L3
[mm]	[mm]	min.	−0.5	max.		max.					+0.2	
4	2.5	−	6	−	3.3 +0.1	10	M3	1.8	−	M2	10.5	1.8
	5											
6	5	−	6	−	5 +0.1	13	M3	2.9	−	M3	11	2.9
	10										13.4	
10	5	−	8	7.5	5.8 +0.1	18	M5	3.4	−	M4	11	3.4
	10										13	
12	5	8	8	10.7	6 H13	20	M5	3.4	M3	M5	11	3.4
	10										17.5	
16	5	10	12	−	8 H13	25	M5	4.5	M4	M6	15	4.6
	10										17.5	
	25										22	
20	5	8	12	−	10 H13	32	M5	5.5	M5	M8	15	5.7
	10	12									20.5	
	25										23.5	
25	5	12	12	−	10 H13	38	M5	5.5	M5	M8	21.1	5.7
	10										25.2	
	25											

Ø	Stroke	L4	L5	L6	MM Ø	PL	T4	TG	UO	WH	ZJ	≈C1
[mm]	[mm]			max.				±0.1	max.		±0.8	
4	2.5	4	6.5	–	2	3.2	–	5.8	10	1	11.5	–
	5										11.5	
6	5	6	9	–	3	3	–	7	14	1	12	–
	10										14.4	
10	5	8	11.5	0.7	4	5.5	–	11	19	1	12	–
	10										14	
12	5	9	13	0.4	6	6	1.5	13	22	1	12	–
	10										18.5	
16	5	11.5	16.5	–	8	6	2	15	27	1	16	7
	10										18.5	
	25										23	
20	5	15	21	–	10	7	2	20	34	1	16	9
	10										21.5	
	25										24.5	
25	5	15.5	21.5	–	10	6.5	2	26	37	1	22.1	9
	10										26.2	
	25										26.2	

Short-stroke cylinders AEVC

Technical data, single-acting – without position sensing

FESTO


Dimensions

Download CAD data → www.festo.com

Ø 32 ... 100 mm


AEVC-...-I-P

Piston rod with female thread



AEVC-...-A-P**

Piston rod with male thread



+ = plus stroke length

Ø	Stroke	AF	AM	BG*	D2	E	EE	FB	H	KF	KK	L2	L3	MM	PL	RT	T4	TG	WH	ZJ	≈G1
[mm]	[mm]	min.	-0.5	min.	Ø F9	max.		Ø				+0.2		Ø				±0.1		±0.8	
32	5	12	14	21.7	9	45	G ¹ / ₈	5.2	7	M6	M10x1.25	21	5.7	12	9.5	M6	2.6	32.5	1	22	10
	10											25								26	
	25											25								26	
40	10	12	14	21.7	9	53.5	G ¹ / ₈	5.2	7	M6	M10x1.25	24.5	5.7	12	9.5	M6	2.6	38	1	25.5	10
	25											29.5								30.5	
50	10	16	16	22.8	11	63.5	G ¹ / ₈	6.8	7	M8	M12x1.25	20.6	6.8	16	9.5	M8	3.3	46.5	0.5	21.1	13
	25											28								28.5	
63	10	16	16	22.8	11	75	G ¹ / ₈	6.8	7.5	M8	M12x1.25	25	6.8	16	11.5	M8	3.3	56.5	1	26	13
	25											32								33	
80	10	20	22	25	14	93	G ¹ / ₈	8.5	7	M10	M16x1.5	42	9	20	15	M10	4.7	72	1	43	17
	25											42								43	
100	10	24	28	25	14	113	G ¹ / ₄	8.5	13	M12	M20x1.5	49	9	25	19	M10	6.1	89	1	50	22
	25											49								50	

* Continuous thread with short overall length

** Nut for piston rod thread included in scope of delivery

Short-stroke cylinders AEVC

Technical data, single-acting – without position sensing

FESTO

Ordering data									
Type	Piston Ø	Stroke	Piston rod with male thread		Piston rod with female thread		Piston rod without thread		
	[mm]	[mm]	Part No.	Type	Part No.	Type	Part No.	Type	
	4	2.5	188 052	AEVC-4-2,5-A-P	–		188 050	AEVC-4-2,5-P	
		5	188 053	AEVC-4-5-A-P		188 051	AEVC-4-5-P		
	6	5	188 062	AEVC-6-5-A-P	–		188 058	AEVC-6-5-P	
		10	188 063	AEVC-6-10-A-P		188 059	AEVC-6-10-P		
	10	5	188 074	AEVC-10-5-A-P	–		188 070	AEVC-10-5-P	
		10	188 075	AEVC-10-10-A-P		188 071	AEVC-10-10-P		
	12	5	188 086	AEVC-12-5-A-P	188 082	AEVC-12-5-I-P	530 566	AEVC-12-5-P	
		10	188 087	AEVC-12-10-A-P	188 083	AEVC-12-10-I-P	530 567	AEVC-12-10-P	
	16	5	188 105	AEVC-16-5-A-P	188 099	AEVC-16-5-I-P	–		
		10	188 106	AEVC-16-10-A-P	188 100	AEVC-16-10-I-P			
		25	188 107	AEVC-16-25-A-P	188 101	AEVC-16-25-I-P			
	20	5	188 137	AEVC-20-5-A-P	188 131	AEVC-20-5-I-P	–		
		10	188 138	AEVC-20-10-A-P	188 132	AEVC-20-10-I-P			
		25	188 139	AEVC-20-25-A-P	188 133	AEVC-20-25-I-P			
	25	5	188 169	AEVC-25-5-A-P	188 163	AEVC-25-5-I-P	–		
		10	188 170	AEVC-25-10-A-P	188 164	AEVC-25-10-I-P			
		25	188 171	AEVC-25-25-A-P	188 165	AEVC-25-25-I-P			

Ordering data						
Type	Piston Ø [mm]	Stroke [mm]	Piston rod with male thread		Piston rod with female thread	
			Part No.	Type	Part No.	Type
	32	5	188 201	AEVC-32-5-A-P	188 195	AEVC-32-5-I-P
		10	188 202	AEVC-32-10-A-P	188 196	AEVC-32-10-I-P
		25	188 203	AEVC-32-25-A-P	188 197	AEVC-32-25-I-P
	40	10	188 230	AEVC-40-10-A-P	188 226	AEVC-40-10-I-P
		25	188 231	AEVC-40-25-A-P	188 227	AEVC-40-25-I-P
	50	10	188 258	AEVC-50-10-A-P	188 254	AEVC-50-10-I-P
		25	188 259	AEVC-50-25-A-P	188 255	AEVC-50-25-I-P
	63	10	188 282	AEVC-63-10-A-P	188 278	AEVC-63-10-I-P
		25	188 283	AEVC-63-25-A-P	188 279	AEVC-63-25-I-P
	80	10	188 306	AEVC-80-10-A-P	188 302	AEVC-80-10-I-P
		25	188 307	AEVC-80-25-A-P	188 303	AEVC-80-25-I-P
	100	10	188 330	AEVC-100-10-A-P	188 326	AEVC-100-10-I-P
		25	188 331	AEVC-100-25-A-P	188 327	AEVC-100-25-I-P

Short-stroke cylinders AVEC



Technical data, single-acting – with position sensing

FESTO



Ø - Diameter
6 ... 100 mm

— Stroke length
5 ... 25 mm



General technical data												
Piston Ø	6	10	12	16	20	25	32	40	50	63	80	100
Pneumatic connection	M3	M5	M5	M5	M5	M5	G½	G½	G½	G½	G½	G¼
Piston rod with female thread	–	–	■	■	■	■	■	■	■	■	■	■
Piston rod with male thread	■	■	■	■	■	■	■	■	■	■	■	■
Piston rod without thread	■	■	■	–	–	–	–	–	–	–	–	–
Operating medium	Filtered compressed air, lubricated or unlubricated											
Constructional design	Piston											
	Piston rod											
Cushioning	Flexible cushioning rings/plates at both ends											
Position sensing	For proximity sensing											
Type of mounting	Via through-holes						Via through-holes					
	–						Via accessories					
Mounting position	Any											

Operating conditions												
Piston Ø	6	10	12	16	20	25	32	40	50	63	80	100
Operating pressure [bar]	2 ... 8	1.5 ... 8	1.5 ... 10				1 ... 10					
Ambient temperature [°C]	–20 ... +80 (note operating range of proximity sensors)											
Corrosion resistance class CRC ¹⁾	1											

1) Corrosion resistance class 1 according to Festo standard 940 070

Components requiring low corrosion resistance. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers

Short-stroke cylinders AEVC

Technical data, single-acting – with position sensing

FESTO

Forces [N] and impact energy [J]												
Piston Ø	6	10	12	16	20	25	32	40	50	63	80	100
Theoretical force at 6 bar, advancing	11	41	59	105	170	270	450	700	1,120	1,800	2,900	4,500
Theoretical force at 6 bar, returning	3	3	4	5	10 ¹⁾	15	22	28	40	50	85	140
Max. impact energy at end positions	0.005	0.03	0.06	0.10	0.14	0.18	0.26	0.36	0.60	0.64	0.90	1.20

1) AEVC-20-5-... = 5 N


 Note	The degree of friction depends upon the mounting position, and the type of load involved. Single-acting cylinders should as far as possible be operated without lateral forces.
--	---

Product weight [g]												
Stroke [mm]	Piston Ø											
	6	10	12	16	20	25	32	40	50	63	80	100
5	19	37	70	95	160	195	320	–	–	–	–	–
10	23	44	79	105	170	205	340	490	630	720	1,940	2,970
25	–	–	–	130	200	250	390	580	730	870	3,290	3,220

Moving load [g]												
Stroke [mm]	Piston Ø											
	6	10	12	16	20	25	32	40	50	63	80	100
5	1.5	3	8.5	15	26	32	49	–	–	–	–	–
10	1.8	3.5	9.5	17	29	35	54	70	116	155	284	546
25	–	–	–	26	40	47	67	83	140	179	321	604

Materials

Sectional view



Short-stroke cylinder		
1	Cylinder barrel	Anodised aluminium
2	Cover cap	Anodised aluminium
3	Piston rod	High-alloy steel
4	Rod seal	Polyurethane
Note on material		Free of copper, PTFE and silicone

Short-stroke cylinders AEVC

Technical data, single-acting – with position sensing

FESTO


Dimensions

Download CAD data → www.festo.com

Ø 6 ... 25 mm

AEVC-...-I-P-A

Piston rod with female thread



-  - Note

Ø 10 mm


Depending on tolerance, the bearing cap may project by up to 0.65 mm.

Ø 12 mm

Depending on tolerance, the bearing cap may project by up to 0.35 mm.


AEVC-...-A-P-A

Piston rod with male thread



AEVC-...-P-A

Piston rod without thread



+ = plus stroke length

1 Slot for proximity sensor
SME/SMT-10

Short-stroke cylinders AEVC

Technical data, single-acting – with position sensing

FESTO

Ø [mm]	Stroke [mm]	AF min.	AM	D1 Ø max.	D2 Ø	E max.	EE	FB Ø	KF	KK	L2 +0.2	L3
6	5	–	6	–	5 +0.1	16	M3	2.9	–	M3	20.5	2.9
	10											
10	5	–	8	7.5	5.8 +0.1	21	M5	3.4	–	M4	22	3.4
	10											
12	5	8	8	10.7	6 H13	24	M5	3.4	M3	M5	31	3.4
	10											
16	5	10	12	–	8 H13	28	M5	4.5	M4	M6	30	4.6
	10										34.5	
	25											
20	5	12	12	–	10 H13	32	M5	5.5	M5	M8	32	5.7
	10										35	
	25											
25	5	12	12	–	10 H13	38	M5	5.5	M5	M8	32	5.7
	10										36.1	
	25											

Ø [mm]	Stroke [mm]	L4	L5	L6 max.	MM Ø	PL	T4	TG ±0.1	U0 max.	WH	ZJ ±0.8	≈C1
6	5	5	8	–	3	3	–	10	16	1	21.5	–
	10											
10	5	7	10.5	0.7	4	6	–	14	22	1.5	23.5	–
	10											
12	5	8	12	0.4	6	6	1.5	16	26	4	35	5
	10											
16	5	12	17	–	8	6	2	18	32	4	34	7
	10										38.5	
	25											
20	5	15	21	–	10	7	2	20	39	5	37	9
	10										40	
	25											
25	5	15.5	21.5	–	10	6	2	26	42	5	37	9
	10										41.1	
	25											

Short-stroke cylinders AEVC

Technical data, single-acting – with position sensing

FESTO

Dimensions

Download CAD data → www.festo.com


Ø 32 ... 100 mm

AEVC-...-I-P-A

Piston rod with female thread


+ = plus stroke length

- 1 Slot for proximity sensor SME/SMT-8
- 2 Slot for proximity sensor SME/SMT-10



AEVC-...-A-P-A**

Piston rod with male thread



Ø	AF min.	AM -0.5	BG* min.	D2 Ø F9	E max.	EE	FB Ø	H	KF	KK
32	12	14	21.7	9	45	G $\frac{1}{8}$	5.2	7	M6	M10x1.25
40	12	14	21.7	9	53.5	G $\frac{1}{8}$	5.2	7	M6	M10x1.25
50	16	16	22.8	11	63.5	G $\frac{1}{8}$	6.8	7	M8	M12x1.25
63	16	16	22.8	11	75	G $\frac{1}{8}$	6.8	7.5	M8	M12x1.25
80	20	22	25	14	93	G $\frac{1}{8}$	8.5	7	M10	M16x1.5
100	24	28	25	14	113	G $\frac{1}{4}$	8.5	13	M12	M20x1.5

Ø	L2 +0.2	L3	MM Ø	PL	RT	T4	TG ±0.1	WH	ZJ ±0.8	±C1
32	33	5.7	12	8.5	M6	2.6	32.5	6	39	10
40	38	5.7	12	9.5	M6	2.6	38	6	44	10
50	38	6.8	16	9.5	M8	3.3	46.5	8	48	13
63	41	6.8	16	10.5	M8	3.3	56.5	8	49	13
80	49	9	20	8.5	M10	4.7	72	8	57	17
100	58	9	25	10.5	M10	6.1	89	10	68	22

* Continuous thread with short overall length

** Nut for piston rod thread included in scope of delivery

Short-stroke cylinders AEVC

Technical data, single-acting – with position sensing

FESTO

Ordering data									
Type	Piston Ø	Stroke	Piston rod with male thread		Piston rod with female thread		Piston rod without thread		
	[mm]		Part No.	Type	Part No.	Type	Part No.	Type	
	6	5	188 060	AEVC-6-5-A-P-A	–		188 056	AEVC-6-5-P-A	
		10	188 061	AEVC-6-10-A-P-A			188 057	AEVC-6-10-P-A	
	10	5	188 072	AEVC-10-5-A-P-A	–		188 068	AEVC-10-5-P-A	
		10	188 073	AEVC-10-10-A-P-A			188 069	AEVC-10-10-P-A	
	12	5	188 084	AEVC-12-5-A-P-A	188 080	AEVC-12-5-I-P-A	530 570	AEVC-12-5-P-A	
		10	188 085	AEVC-12-10-A-P-A	188 081	AEVC-12-10-I-P-A	530 571	AEVC-12-10-P-A	
	16	5	188 102	AEVC-16-5-A-P-A	188 096	AEVC-16-5-I-P-A	–		
		10	188 103	AEVC-16-10-A-P-A	188 097	AEVC-16-10-I-P-A			
		25	188 104	AEVC-16-25-A-P-A	188 098	AEVC-16-25-I-P-A			
	20	5	188 134	AEVC-20-5-A-P-A	188 128	AEVC-20-5-I-P-A	–		
		10	188 135	AEVC-20-10-A-P-A	188 129	AEVC-20-10-I-P-A			
		25	188 136	AEVC-20-25-A-P-A	188 130	AEVC-20-25-I-P-A			
	25	5	188 166	AEVC-25-5-A-P-A	188 160	AEVC-25-5-I-P-A	–		
		10	188 167	AEVC-25-10-A-P-A	188 161	AEVC-25-10-I-P-A			
		25	188 168	AEVC-25-25-A-P-A	188 162	AEVC-25-25-I-P-A			

Ordering data							
Type	Piston Ø [mm]	Stroke [mm]	Piston rod with male thread		Piston rod with female thread		
			Part No.	Type	Part No.	Type	
	32	5	188 198	AEVC-32-5-A-P-A	188 192	AEVC-32-5-I-P-A	
		10	188 199	AEVC-32-10-A-P-A	188 193	AEVC-32-10-I-P-A	
		25	188 200	AEVC-32-25-A-P-A	188 194	AEVC-32-25-I-P-A	
	40	10	188 228	AEVC-40-10-A-P-A	188 224	AEVC-40-10-I-P-A	
		25	188 229	AEVC-40-25-A-P-A	188 225	AEVC-40-25-I-P-A	
	50	10	188 256	AEVC-50-10-A-P-A	188 252	AEVC-50-10-I-P-A	
		25	188 257	AEVC-50-25-A-P-A	188 253	AEVC-50-25-I-P-A	
	63	10	188 280	AEVC-63-10-A-P-A	188 276	AEVC-63-10-I-P-A	
		25	188 281	AEVC-63-25-A-P-A	188 277	AEVC-63-25-I-P-A	
	80	10	188 304	AEVC-80-10-A-P-A	188 300	AEVC-80-10-I-P-A	
		25	188 305	AEVC-80-25-A-P-A	188 301	AEVC-80-25-I-P-A	
	100	10	188 328	AEVC-100-10-A-P-A	188 324	AEVC-100-10-I-P-A	
		25	188 329	AEVC-100-25-A-P-A	188 325	AEVC-100-25-I-P-A	

Short-stroke cylinders ADVC/AEVC

Accessories



FESTO

Adapter kit DPNC

Material:

Flange: Wrought aluminium alloy

Threaded studs, hex nuts: Galvanised steel



Dimensions and ordering data									
For Ø [mm]	Stroke [mm]	F1	ZJ				Weight [g]	Part No.	Type
			without position sensing ADVC		with position sensing AEVC				
32	5	27	35	22	39	39	85	174 418	DPNC-32
	10, 15, 20, 25			26					
40	5, 10	27	35.5	25.5	44	44	115	174 419	DPNC-40
	15, 20, 25			30.5					
50	10	32	36	21.1	46	48	210	174 420	DPNC-50
	15, 20, 25			28.5					
63	10	28	43	26	49	49	360	174 421	DPNC-63
	15, 20, 25			33					
80	10, 15, 20, 25	38	48	43	57	57	620	174 422	DPNC-80
100	10, 15, 20, 25	38	59	50	68	68	1,190	174 423	DPNC-100

Connecting two cylinders with identical piston Ø as a 3 or 4-position cylinder

A 3 or 4-position cylinder consists of two separate cylinders whose piston rods advance in opposing directions.


This means that depending upon actuation and stroke pattern, this type of cylinder can assume up to four

positions. In each case the cylinder is driven precisely against a stop. Note that when one end of the piston rod is

fixed, the cylinder barrel executes the movement. The cylinder must be connected with flexible line connections.


To achieve 3 positions

Two cylinders with identical stroke length must be connected together.



To achieve 4 positions

Two cylinders with different stroke lengths must be connected together.




Short-stroke cylinders ADVC/AEVC

FESTO

Accessories

Foot mounting HNC

Material:
Galvanised steel
Free of copper, PTFE and silicone



Dimensions and ordering data												
For Ø	Stroke	AB Ø	AH	AO	AT	AU	SA				TR	US
[mm]	[mm]						without position sensing		with position sensing			
							ADVC	AEVC	ADVC	AEVC		
32	5	7	32	6.5	4	24	77	69	81	81	32	45
	10, 15, 20, 25							73				
40	5, 10	10	36	9	4	28	85.5	80.5	94	94	36	54
	15, 20, 25							85.5				
50	10	10	45	9.5	5	32	92	84.6	102	104	45	64
	15, 20, 25							92				
63	10	10	50	12.5	5	32	99	89	105	105	50	75
	15, 20, 25							96				
80	10, 15, 20, 25	12	63	15	6	41	122	124	131	131	63	93
100	10, 15, 20, 25	14.5	71	17.5	6	41	131	131	140	140	75	110

For Ø	Stroke	XA				XS				CRC ¹⁾	Weight	Part No.	Type
		without position sensing		with position sensing		without position sensing		with position sensing					
[mm]	[mm]	ADVC	AEVC	ADVC	AEVC	ADVC	AEVC	ADVC	AEVC		[g]		
32	5	59	46	63	63	26	21	26	26	2	135	174 369	HNC-32
	10, 15, 20, 25		50										
40	5, 10	63.5	53.5	72	72	30	25	30	30	2	180	174 370	HNC-40
	15, 20, 25		58.5										
50	10	68	53.1	78	80	35	27.5	35	35	2	325	174 371	HNC-50
	15, 20, 25		60.5										
63	10	75	58	81	81	35	28	35	35	2	405	174 372	HNC-63
	15, 20, 25		65										
80	10, 15, 20, 25	89	84	98	98	43	36	43	43	2	820	174 373	HNC-80
100	10, 15, 20, 25	100	91	109	109	45	36	45	45	2	1,000	174 374	HNC-100

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents

Note
Screws with special lengths are required to fit the sizes Ø 80 mm and Ø 100 mm. → 43

Short-stroke cylinders ADVC/AEVC

Accessories


FESTO

Flange mounting FNC

Material:

Galvanised steel

Free of copper, PTFE and silicone



Dimensions and ordering data								
For Ø	Stroke	D1 Ø H11	E	FB Ø H13	MF	R	TF	UF
[mm]	[mm]							
32	5	30	45	7	10	32	64	80
	10, 15, 20, 25							
40	5, 10	35	54	9	10	36	72	90
	15, 20, 25							
50	10	40	65	9	12	45	90	110
	15, 20, 25							
63	10	45	75	9	12	50	100	120
	15, 20, 25							
80	10, 15, 20, 25	45	93	12	16	63	126	150
100	10, 15, 20, 25	55	110	14	16	75	150	175

For Ø [mm]	Stroke [mm]	ZF				CRC ¹⁾	Weight [g]	Part No.	Type
		without position sensing ADVC		with position sensing AEVC					
32	5	45	32	49	49	2	240	174 376	FNC-32
	10, 15, 20, 25		36						
40	5, 10	45.5	35.5	54	54	2	280	174 377	FNC-40
	15, 20, 25		40.5						
50	10	48	33.5	58	60	2	520	174 378	FNC-50
	15, 20, 25		40.5						
63	10	55	38	61	61	2	690	174 379	FNC-63
	15, 20, 25		45						
80	10, 15, 20, 25	64	59	73	73	2	1,650	174 380	FNC-80
100	10, 15, 20, 25	75	66	84	84	2	2,400	174 381	FNC-100

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents

 - Note
Screws with special lengths are required to fit the sizes Ø 80 mm and Ø 100 mm. → 43


Short-stroke cylinders ADVC/AEVC

Accessories

FESTO

Trunnion flange ZNCF

Material:
Special steel casting
Free of copper, PTFE and silicone



Dimensions and ordering data										
For Ø	Stroke	C2	C3	D1 Ø H11	TD Ø e9	TK	TL	TM	US	XH
[mm]	[mm]									
32	5	71	86	30	12	16	12	50	45	2
	10, 15, 20, 25									
40	5, 10	87	105	35	16	20	16	63	54	4
	15, 20, 25									
50	10	99	117	40	16	24	16	75	64	4
	15, 20, 25									
63	10	116	136	45	20	24	20	90	75	4
	15, 20, 25									
80	10, 15, 20, 25	136	156	45	20	28	20	110	93	6
100	10, 15, 20, 25	164	189	55	25	38	25	132	110	9

For Ø [mm]	Stroke [mm]	XL				CRC ¹⁾	Weight [g]	Part No.	Type
		without position sensing ADVC		with position sensing AEVC					
32	5	43	30	47	47	2	130	174 411	ZNCF-32
	10, 15, 20, 25		34						
40	5, 10	45.5	35.5	54	54	2	240	174 412	ZNCF-40
	15, 20, 25		40.5						
50	10	48	33.1	58	60	2	390	174 413	ZNCF-50
	15, 20, 25		40.5						
63	10	55	38	61	61	2	600	174 414	ZNCF-63
	15, 20, 25		45						
80	10, 15, 20, 25	62	57	71	71	2	1,150	174 415	ZNCF-80
100	10, 15, 20, 25	78	69	87	87	2	2,030	174 416	ZNCF-100

1) Corrosion resistance class 2 according to Festo standard 940 070
Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents

 Note
Screws with special lengths are required to fit the sizes Ø 80 mm and Ø 100 mm. → 43

Short-stroke cylinders ADVC/AEVC

Accessories

FESTO

Trunnion support LN2G


Material:

Trunnion support:

Anodised aluminium

Plain bearing: Plastic

Free of copper, PTFE and silicone



Dimensions and ordering data															
For Ø	CR	DA	FK	FN	FS	H1	HB	KE	NH	TH	UL	CRC ¹⁾	Weight	Part No.	Type
[mm]	Ø D11	Ø H13	±0.1				Ø H13			±0.2			[g]		
32	12	11	15	30	10.5	15	6.6	6.8	18	32	46	2	125	32 959	LN2G-32
40, 50	16	15	18	36	12	18	9	9	21	36	55	2	400	32 960	LN2G-40/50
63, 80	20	18	20	40	13	20	11	11	23	42	65	2	480	32 961	LN2G-63/80
100	25	20	25	50	16	24.5	14	13	28.5	50	75	2	960	32 962	LN2G-100/125

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents


Short-stroke cylinders ADVC/AEVC

FESTO

Accessories

Swivel flange SNC

Material:
Die-cast aluminium



Dimensions and ordering data							
For Ø	Stroke	CG	CP	EK	FL	L	SR
[mm]	[mm]	H14	h14	h9	±0.2		
32	5	14	34	10	22	13	10
	10, 15, 20, 25						
40	5, 10	16	40	12	25	16	12
	15, 20, 25						
50	10	21	45	16	27	16	12
	15, 20, 25						
63	10	21	51	16	32	21	16
	15, 20, 25						
80	10, 15, 20, 25	25	65	20	36	22	16
100	10, 15, 20, 25	25	75	20	41	27	20

For Ø [mm]	Stroke [mm]	XC				CRC ¹⁾	Weight [g]	Part No.	Type
		without position sensing ADVC		with position sensing AEVC					
32	5	57	44	61	61	2	90	174 383	SNC-32
	10, 15, 20, 25		48						
40	5, 10	60.5	50.5	69	69	2	120	174 384	SNC-40
	15, 20, 25		55.5						
50	10	63	48.1	73	75	2	240	174 385	SNC-50
	15, 20, 25		55.5						
63	10	75	58	81	81	2	320	174 386	SNC-63
	15, 20, 25		65						
80	10, 15, 20, 25	84	79	93	93	2	625	174 387	SNC-80
100	10, 15, 20, 25	100	91	109	109	2	830	174 388	SNC-100

1) Corrosion resistance class 2 according to Festo standard 940 070
Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents

Note
Screws with special lengths are required to fit the sizes Ø 80 mm and Ø 100 mm. → 43

Short-stroke cylinders ADVC/AEVC

Accessories


FESTO

Swivel flange SNCB

Material:

Die-cast aluminium

Free of copper, PTFE and silicone



Dimensions and ordering data								
For Ø	Stroke	CB	EK	FL	L	ML	MR	UB
[mm]	[mm]	H14	Ø e8	±0.2				h14
32	5	26	10	22	13	55	8.5	45
	10, 15, 20, 25							
40	5, 10	28	12	25	16	63	12	52
	15, 20, 25							
50	10	32	12	27	16	71	12	60
	15, 20, 25							
63	10	40	16	32	21	83	16	70
	15, 20, 25							
80	10, 15, 20, 25	50	16	36	22	103	16	90
100	10, 15, 20, 25	60	20	41	27	127	20	110

For Ø [mm]	Stroke [mm]	XC				CRC ¹⁾	Weight [g]	Part No.	Type
		without position sensing ADVC		with position sensing AEVC					
32	5	57	44	61	61	2	100	174 390	SNCB-32
	10, 15, 20, 25		48						
40	5, 10	60.5	50.5	69	69	2	150	174 391	SNCB-40
	15, 20, 25		55.5						
50	10	63	48.1	73	75	2	225	174 392	SNCB-50
	15, 20, 25		55.5						
63	10	75	58	81	81	2	365	174 393	SNCB-63
	15, 20, 25		65						
80	10, 15, 20, 25	84	79	93	93	2	610	174 394	SNCB-80
100	10, 15, 20, 25	100	91	109	109	2	925	174 395	SNCB-100

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents

-  - Note
Screws with special lengths are required to fit the sizes Ø 80 mm and Ø 100 mm. → 43

Short-stroke cylinders ADVC/AEVC



Accessories

FESTO

Swivel flange SNCS

Material:

Die-cast aluminium



Dimensions and ordering data							
For Ø	Stroke	CN	EP	EX	FL	LT	MS
[mm]	[mm]	Ø H7	±0.2		±0.2		
32	5	10	10.5	14	22	13	15
	10, 15, 20, 25						
40	5, 10	12	12	16	25	16	17
	15, 20, 25						
50	10	16	15	21	27	16	20
	15, 20, 25						
63	10	16	15	21	32	21	22
	15, 20, 25						
80	10, 15, 20, 25	20	18	25	36	22	27
100	10, 15, 20, 25	20	18	25	41	27	29

For Ø [mm]	Stroke [mm]	XC				CRC ¹⁾	Weight [g]	Part No.	Type
		without position sensing ADVC		with position sensing AEVC					
32	5	57	44	61	61	2	85	174 397	SNCS-32
	10, 15, 20, 25		48						
40	5, 10	60.5	50.5	69	69	2	125	174 398	SNCS-40
	15, 20, 25		55.5						
50	10	63	48.1	73	75	2	210	174 399	SNCS-50
	15, 20, 25		55.5						
63	10	75	58	81	81	2	280	174 400	SNCS-63
	15, 20, 25		65						
80	10, 15, 20, 25	84	79	93	93	2	540	174 401	SNCS-80
100	10, 15, 20, 25	100	91	109	109	2	700	174 402	SNCS-100

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents

 Note
Screws with special lengths are required to fit the sizes Ø 80 mm and Ø 100 mm. → 43

Short-stroke cylinders ADVC/AEVC

Accessories



FESTO

Swivel flange SNCL

Material:

Die-cast aluminium

Free of copper, PTFE and silicone



Dimensions and ordering data						
For Ø	Stroke	CD	EW	FL	L	MR
[mm]	[mm]	Ø H9	-0.2/-0.6	±0.2		
32	5	10	26	22	13	10
	10, 15, 20, 25					
40	5, 10	12	28	25	16	12
	15, 20, 25					
50	10	12	32	27	16	12
	15, 20, 25					
63	10	16	40	32	21	16
	15, 20, 25					
80	10, 15, 20, 25	16	50	36	22	16
100	10, 15, 20, 25	20	60	41	27	20

For Ø [mm]	Stroke [mm]	XC				CRC ¹⁾	Weight [g]	Part No.	Type
		without position sensing ADVC		with position sensing AEVC					
32	5	57	44	61	61	2	75	174 404	SNCL-32
	10, 15, 20, 25		48						
40	5, 10	60.5	50.5	69	69	2	100	174 405	SNCL-40
	15, 20, 25		55.5						
50	10	63	48.1	73	75	2	160	174 406	SNCL-50
	15, 20, 25		55.5						
63	10	75	58	81	81	2	250	174 407	SNCL-63
	15, 20, 25		65						
80	10, 15, 20, 25	84	79	93	93	2	405	174 408	SNCL-80
100	10, 15, 20, 25	100	91	109	109	2	655	174 409	SNCL-100

1) Corrosion resistance class 2 according to Festo standard 940 070







Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents

 - Note
Screws with special lengths are required to fit the sizes Ø 80 mm and Ø 100 mm. → 43

Short-stroke cylinders ADVC/AEVC

Accessories

FESTO

Ordering data – Mounting attachments				Technical data → Internet: clevis foot			
Designation	For Ø	Part No.	Type	Designation	For Ø	Part No.	Type
Clevis foot mounting LNG				Clevis foot mounting LSN			
	32	33 890	LNG-32		32	5 561	LSN-32
	40	33 891	LNG-40		40	5 562	LSN-40
	50	33 892	LNG-50		50	5 563	LSN-50
	63	33 893	LNG-63		63	5 564	LSN-63
	80	33 894	LNG-80		80	5 565	LSN-80
	100	33 895	LNG-100		100	5 566	LSN-100
Clevis foot mounting LSNG				Weld-on clevis foot mounting LSNSG			
	32	31 740	LSNG-32		32	31 747	LSNSG-32
	40	31 741	LSNG-40		40	31 748	LSNSG-40
	50	31 742	LSNG-50		50	31 749	LSNSG-50
	63	31 743	LSNG-63		63	31 750	LSNSG-63
	80	31 744	LSNG-80		80	31 751	LSNSG-80
	100	31 745	LSNG-100		100	31 752	LSNSG-100
Clevis foot LBG on swivel flange SNCS				Clevis foot LBG on rod eye SGS			
	32	31 761	LBG-32		32, 40	31 761	LBG-32
	40	31 762	LBG-40		50, 63	31 762	LBG-40
	50	31 763	LBG-50		80	31 763	LBG-50
	63	31 764	LBG-63			31 764	LBG-63
	80	31 765	LBG-80		100	31 765	LBG-80
	100	31 766	LBG-100			31 766	LBG-100
Clevis foot, right-angled LQG							
	32, 40	31 768	LQG-32				
	50, 63	31 769	LQG-40				
	80	31 770	LQG-50				
		31 771	LQG-63				
	100	31 772	LQG-80				
		31 773	LQG-100				


Ordering data				
Special screw	For Ø	For accessory	Part No.	PU ¹⁾
	80, 100	HNC, FNC, SNC, SNCS, SNCL, SNCB	238 600 M10x30	1
	80	ZNCF	204 138 M10x40	
	100	ZNCF	370 524 M10x50	

1) Packaging unit quantity

Short-stroke cylinders ADVC/AEVC

Accessories

FESTO


Ordering data – Piston rod attachments				Technical data → Internet: piston-rod attachment			
Designation	For Ø	Part No.	Type	Designation	For Ø	Part No.	Type
Rod eye SGS				Rod clevis SGA			
	10	9 253	SGS-M4		32	–	–
	16	9 254	SGS-M6		40		
	20	9 255	SGS-M8		50		
	25				63		
	32	9 261	SGS-M10x1,25		32	32 954	SGA-M10x1,25
	40				40		
	50	9 262	SGS-M12x1,25		50	10 767	SGA-M12x1,25
	63				63		
	80	9 263	SGS-M16x1,5		80	10 768	SGA-M16x1,5
	100	9 264	SGS-M20x1,5		100	10 769	SGA-M20x1,5
Rod clevis SG				Self-aligning rod coupler FK			
	10	6 532	SG-M4		10	6 528	FK-M4
	12	–	–		12	30 984	FK-M5
	16	3 110	SG-M6		16	2 061	FK-M6
	20	3 111	SG-M8		20	2 062	FK-M8
	25				25		
	32	6 144	SG-M10x1,25		32	6 140	FK-M10x1,25
	40				40		
	50	6 145	SG-M12x1,25		50	6 141	FK-M12x1,25
	63				63		
	80	6 146	SG-M16x1,5		80	6 142	FK-M16x1,5
	100	6 147	SG-M20x1,5		100	6 143	FK-M20x1,5
Coupling piece KSG							
	32	32 963	KSG-M10x1,25				
	40						
	50	32 964	KSG-M12x1,25				
	63						
	80	32 965	KSG-M16x1,5				
	100	32 966	KSG-M20x1,5				

Short-stroke cylinders ADVC/AEVC

Accessories

FESTO

Ordering data – Proximity sensors for T-slot, magneto-resistive					Technical data ➔ Internet: smt	
	Type of mounting	Switch output	Electrical connection	Cable length [m]	Part No.	Type
N/O contact						
	Insertable in the slot from above, flush with cylinder profile	PNP	Cable, 3-wire	2.5	543 867	SMT-8M-PS-24V-K-2,5-OE
			Plug M8x1, 3-pin	0.3	543 866	SMT-8M-PS-24V-K-0,3-M8D
			Plug M12x1, 3-pin	0.3	543 869	SMT-8M-PS-24V-K-0,3-M12
		NPN	Cable, 3-wire	2.5	543 870	SMT-8M-NS-24V-K-2,5-OE
			Plug M8x1, 3-pin	0.3	543 871	SMT-8M-NS-24V-K-0,3-M8D
	Insertable in the slot lengthwise, flush with the cylinder profile	PNP	Cable, 3-wire	2.5	175 436	SMT-8-PS-K-LED-24-B
			Plug M8x1, 3-pin	0.3	175 484	SMT-8-PS-S-LED-24-B
N/C contact						
	Insertable in the slot from above, flush with cylinder profile	PNP	Cable, 3-wire	7.5	543 873	SMT-8M-PO-24V-K7,5-OE

Ordering data – Proximity sensors for T-slot, magnetic reed					Technical data → Internet: sme	
	Type of mounting	Switch output	Electrical connection	Cable length [m]	Part No.	Type
N/O contact						
	Insertable in the slot from above, flush with cylinder profile	Contacting	Cable, 3-wire	2.5	543 862	SME-8M-DS-24V-K-2,5-OE
				5.0	543 863	SME-8M-DS-24V-K-5,0-OE
			Cable, 3-wire	2.5	543 872	SME-8M-ZS-24V-K-2,5-OE
			Plug M8x1, 3-pin	0.3	543 861	SME-8M-DS-24V-K-0,3-M8D
	Insertable in the slot lengthwise, flush with the cylinder profile	Contacting	Cable, 3-wire	2.5	150 855	SME-8-K-LED-24
			Plug M8x1, 3-pin	0.3	150 857	SME-8-S-LED-24
N/C contact						
	Insertable in the slot lengthwise, flush with the cylinder profile	Contacting	Cable, 3-wire	7.5	160 251	SME-8-O-K-LED-24

Ordering data – Connecting cables				Technical data → Internet: nebu	
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part No.	Type
	Straight socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541 333	NEBU-M8G3-K-2.5-LE3
			5	541 334	NEBU-M8G3-K-5-LE3
	Straight socket, M12x1, 5-pin	Cable, open end, 3-wire	2.5	541 363	NEBU-M12G5-K-2.5-LE3
			5	541 364	NEBU-M12G5-K-5-LE3
	Angled socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541 338	NEBU-M8W3-K-2.5-LE3
			5	541 341	NEBU-M8W3-K-5-LE3
	Angled socket, M12x1, 5-pin	Cable, open end, 3-wire	2.5	541 367	NEBU-M12W5-K-2.5-LE3
			5	541 370	NEBU-M12W5-K-5-LE3

Ordering data – Slot cover for T-slot					
	Mounting	Length		Part No.	Type
	Insertable from above	2x 0.5 m		151 680	ABP-5-S

Short-stroke cylinders ADVC/AEVC

Accessories

FESTO

Ordering data – Proximity switches for C-slot, magneto-resistive					Technical data → Internet: smt	
	Type of mounting	Switch output	Electrical connection, connection direction	Cable length [m]	Part No.	Type
N/O contact						
	Insertable in the slot lengthwise	PNP	Plug M8x1, 3-pin, in-line	0,3	173 220	SMT-10-PS-SL-LED-24
			Cable, 3-wire, in-line	2,5	173 218	SMT-10-PS-KL-LED-24

Ordering data – Proximity switches for C-slot, magnetic reed					Technical data → Internet: sme	
	Type of mounting	Switch output	Electrical connection, connection direction	Cable length [m]	Part No.	Type
N/O contact						
	Insertable in the slot lengthwise	Contacting	Plug M8x1, 3-pin, in-line	0,3	173 212	SME-10-SL-LED-24
			Cable, 3-wire, in-line	2,5	173 210	SME-10-KL-LED-24

Ordering data – Connecting cables				Technical data → Internet: nebu	
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part No.	Type
	Straight socket, M8x1, 3-pin	Cable, open end, 3-wire	2,5	541 333	NEBU-M8G3-K-2.5-LE3
			5	541 334	NEBU-M8G3-K-5-LE3
	Angled socket, M8x1, 3-pin	Cable, open end, 3-wire	2,5	541 338	NEBU-M8W3-K-2.5-LE3
			5	541 341	NEBU-M8W3-K-5-LE3

Ordering data – One-way flow control valves			Technical data ➔ Internet: grl		
	Connection		Material	Part No.	Type
	Thread	For tubing O.D.			
For exhaust air					
	M3	3	Metal design	175 041	GRLA-M3-QS-3
	M5	3		193 137	GRLA-M5-QS-3-D
		4		193 138	GRLA-M5-QS-4-D
		6		193 139	GRLA-M5-QS-6-D
		G1/8		3	193 142
	4			193 143	GRLA-1/8-QS-4-D
	6			193 144	GRLA-1/8-QS-6-D
	8			193 145	GRLA-1/8-QS-8-D
	G1/4	6		193 146	GRLA-1/4-QS-6-D
		8		193 147	GRLA-1/4-QS-8-D
		10		193 148	GRLA-1/4-QS-10-D
For supply air					
	M3	3	Metal design	175 043	GRLZ-M3-QS-3
	M5	3		193 153	GRLZ-M5-QS-3-D
		4		193 154	GRLZ-M5-QS-4-D
		6		193 155	GRLZ-M5-QS-6-D
		G1/8		3	193 156
	4			193 157	GRLZ-1/8-QS-4-D
	6			193 158	GRLZ-1/8-QS-6-D
	8			193 159	GRLZ-1/8-QS-8-D

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components

Complete custom engineered solutions



Custom Control Cabinets

Comprehensive engineering support and on-site services



Complete Systems

Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical

Electromechanical actuators, motors, controllers & drives



Pneumatics

Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices

PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

United States

Customer Resource Center

502 Earth City Expy., Suite 125
Earth City, MO 63045

For ordering assistance, or to find
your nearest Festo Distributor,

Call: 1.800.99.FESTO

Fax: 1.800.96.FESTO

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO

Fax: 1.800.96.FESTO

Email: product.support@us.festo.com

Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788
www.festo.com/us

Sales Offices

Appleton

N. 922 Tower View Drive, Suite N
Greenville, WI 54942

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057

Detroit - Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326

New York

395 Moreland Road
Hauppauge, NY 11788

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550

Design and Manufacturing Operations



East: 395 Moreland Road, Hauppauge, NY 11788



Central: 1441 East Business Center Drive, Mt. Prospect, IL 60056



West: 4935 Southfront Road, Suite F, Livermore, CA 94550

Mexico

Headquarters

Festo Pneumatic, S.A.
Av. Ceylán 3, Col. Tequesquahuac
54020 Tlalnepantla, Edo. de México
Call: 011 52 [55] 53 21 66 00
Fax: 011 52 [55] 53 21 66 65
Email: festo.mexico@mx.festo.com
www.festo.com/mx



Canada

Headquarters

Festo Inc.
5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Call: 1.905.624.9000
Fax: 1.905.624.9001
Email: info.ca@ca.festo.com
www.festo.com/ca



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan
Latvia Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com