


Tiger Classic valve

FESTO



Characteristics

At a glance

General information:

- Particularly robust poppet valve principle for all 3/2- and 5/2-way valves
- Pneumatically actuated or electrically with F solenoid coil
- With flow rate performances up to 7500 l/min
- With internal or external pilot air
- Pipe connection thread sizes G1/8, G1/4, G1/2 and G3/4
- Proven mounting by hollow bolt on PAL or PRS rails (without ATEX category)
- Optimized switching times due to patented U-ring and servo control
- Note: Valves for potentially explosive areas (ATEX category) are not suitable for mounting on PAL manifold rails or PRS manifold rails.


F-solenoid coils:

- Voltage: 12 to 230 V DC; 12 to 240 V AC (50 to 60 Hz)
- Power consumption 4.1 to 5.5 W DC; 3.85 to 9 VA AC
- Specified types suitable for potentially explosive atmospheres in accordance with the ATEX directive
- Solenoid coil can be easily replaced at a later date
- Solenoid coil not in scope of delivery

Variants:

- VL/O-3-...: Normally closed or normally open, depending on the choice of connections
- MFH-3-..., MOFH-3-...: MFH-3-... Normally closed, MOFH-3-... Normally open; these valves can be converted to the other valve version by turning the seal under the cover.
- MFH-3-...S: This valve type can also be used from 0 to 0.8 MPa as MOFH (unactuated passage) with separate control line.
- MFH-5-...S: This valve can also be used for low working pressures due to the external pilot air connection.

Mounting method



The Tiger Classic valves can be mounted on PAL manifold rails with a common supply port or on PRS manifold blocks with a common supply port and common exhausts. The valves are fastened to the rails and blocks with hollow bolts. The manifold rail and manifold block have 2 to 6 valve positions. Vacant positions can be closed with cap nuts for PAL manifold rails and with cover plates for PRS blocks. A separate pressure level can be supplied to individual valves via hollow bolts with threaded connections.

Type code

001	Series
MCH	Solenoid valve, with armature tube for C solenoid coil, single solenoid, normally closed
MFH	Solenoid valve, with armature tube for F solenoid coil, single solenoid, normally closed
MOCH	Solenoid valve, with armature tube for C solenoid coil, single solenoid, normally open
JMFH	Solenoid valve, with armature tube for F solenoid coil, double solenoid
MOFH	Solenoid valve, with armature tube for F solenoid coil, single solenoid, normally open
JMFDH	Solenoid valve, with armature tube for F solenoid coil, with dominant signal, double solenoid
JH	Pneumatic double pilot valve, double solenoid
JDH	Pneumatic double pilot valve with dominant signal, double solenoid
VL/O	Pneumatic valve, single solenoid, normally open or closed
VL	Pneumatic valve, single solenoid

002	Valve function	
3	3/2 directional control valve	
5	5/2 directional control valve	
003	Pneumatic connection	
G18	G1/8	
G14	G1/4	
G12	G1/2	
G34	G3/4	
004	EX certification EU	
	None	
EX4	II 2GD	
005	Pilot air	
	Internal	
S	External	

Datasheet

Solenoid valves, 3/2directional valves, General technical data

Pneumatic connection 1	G1/8	G1/4	G1/2	G3/4
Valve function	3/2-way, closed, monostable, 3/2-way, monostable, open			
Structural design	Plate seat			
Lap	Negative overlap			
Sealing principle	Soft			
Actuation type	Electrical			
Reset method	Mechanical spring			
Type of control	Piloted			
Pilot air supply port	External			External, Internal
Flow direction	Non-reversible, Reversible			
Exhaust air function	Adjustable			
Manual override	Detenting			
Type of mounting ¹⁾	Alternatively:, On terminal strip, With through-hole			
Mounting position	Any			
Electrical connection	Via F coil, to be ordered separately			
Venting hole connection	M3			
Pilot air port 12	M5		G1/8	
b-value	—		0.3	—
Nominal width	5 mm	7 mm	14 mm	19 mm
Normal nominal flow rate (normalized to DIN 1343)	500 l/min	800 l/min	3,700 l/min	7,500 l/min
Product weight	240 g	320 g	1,100 g	1,260 g

1) Fastening of types MFH-3-3/4- and MOFH-3-3/4- only with through hole

Solenoid valves, 3/2-way valves, safety-related characteristics

Max. positive test pulse with 0 signal	2,200 µs
Max. negative test pulse on 1 signal ¹⁾	3,700 µs

1) not valid for types MFH-3-3/4- and MOFH-3-3/4-

Solenoid valves, 3/2-way valves, ATEX

ATEX category gas	II 2G
Type of ignition protection for gas	Ex h IIC T4 Gb
ATEX category for dust	II 2D
Type of (ignition) protection for dust	Ex h IIIC T130°C Db
Explosive ambient temperature	-5°C ≤ Ta ≤ +40°C
CE marking (see declaration of conformity)	as per EU explosion protection directive (ATEX)
UKCA marking (see declaration of conformity)	acc. to UK EX instructions
Explosion protection certification outside the EU	EPL Db (GB) EPL Gb (GB)
Degree of protection	IP65

Datasheet

Solenoid valves, 3/2directional valves, operating and environmental conditions

Pneumatic connection 1	G1/8	G1/4	G1/2	G3/4
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]			
Pilot medium	Compressed air as per ISO 8573-1:2010 [7:4:4]			
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)			
Operating pressure	-0.095 ... 1 MPa			
Operating pressure	-0.95 ... 10 bar			
Pilot pressure	1 ... 8 bar			
Pilot pressure MPa	0.1 ... 0.8 MPa			
Ambient temperature	-5 ... 40°C			
Temperature of medium	-10 ... 60°C			
Storage temperature	-20 ... 60°C			
Certification	c UL us - recognized (OL)			
Corrosion resistance class (CRC) ¹⁾	1 - Low corrosion stress			
LABS (PWIS) conformity	VDMA24364-B1/B2-L			

1) For more information, visit www.festo.com/x/topic/kbk

Electrical data

Electrical connection	Via F coil, to be ordered separately
Coil characteristics	See solenoid coil, to be ordered separately
Degree of protection	IP65


Weights

Weights					
Pneumatic connection 1	G1/8	G1/4	G1/2	G3/4	
Valve function	3/2-way, closed, monostable				3/2-way, monostable, open
Pilot air supply port	External			Internal	
On switching time	9 ms	10 ms	18 ms	36 ms	40 ms
Switching time off	33 ms	29 ms	90 ms	32 ms	29 ms

Materials


Housing material	Die-cast aluminum
Seals material	NBR
Note on materials	RoHS compliant

Solenoid valves, 3/2-way valves, minimum pilot pressure p_{12}/p_{14} as a function of operating pressure p_1 (external pilot air supply), MFH-3-1/8-S




Datasheet


Solenoid valves, 3/2-way valves, minimum pilot pressure p_{12}/p_{14} as a function of operating pressure p_1 (external pilot air supply), MFH-3-1/4-S



Solenoid valves, 3/2-way valves, minimum pilot pressure p_{12}/p_{14} as a function of operating pressure p_1 (external pilot air supply), MFH-3-1/2-S



Solenoid valves, 3/2-way valves, minimum pilot pressure p_{12}/p_{14} as a function of operating pressure p_1 (external pilot air supply), MFH-3-3/4-S



Datasheet

General technical data

Pneumatic connection 1	G1/8	G1/4	G1/2
Valve function	5/2-way, monostable		
Structural design	Plate seat		
Lap	Negative overlap		
Sealing principle	Soft		
Actuation type	Electrical		
Reset method	Mechanical spring		
Type of control	Piloted		
Pilot air supply port	External		
Flow direction	Non-reversible		
Exhaust air function	Adjustable		
Manual override	Detenting		
Type of mounting	Alternatively:, On terminal strip, With through-hole		
Mounting position	Any		
Electrical connection	Via F coil, to be ordered separately		
Venting hole connection	M3		
b-value	–	0.19	0.32
Nominal width	5 mm	7 mm	14 mm
Normal nominal flow rate (normalized to DIN 1343)	500 l/min	1,000 l/min	3,700 l/min
Product weight	270 g	290 g	1,135 g
C value	–	4.49	–

Solenoid valves, 5/2-way valves, safety-related characteristics

Max. positive test pulse with 0 signal	2,200 µs
Max. negative test pulse on 1 signal	3,700 µs

Solenoid valves, 5/2directional valves, operating and environmental conditions

Pneumatic connection 1	G1/8	G1/4	G1/2
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]		
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)		
Operating pressure	0 ... 1 MPa	0 ... 0.8 MPa	0 ... 1 MPa
Operating pressure	0 ... 10 bar	0 ... 8 bar	0 ... 10 bar
Pilot pressure	1.2 ... 8 bar	1.5 ... 8 bar	1 ... 8 bar
Pilot pressure MPa	0.12 ... 0.8 MPa	0.15 ... 0.8 MPa	0.1 ... 0.8 MPa
Ambient temperature	-5 ... 40°C		
Temperature of medium	-10 ... 60°C		
Storage temperature	-20 ... 60°C		
Certification	c UL us - recognized (OL)		
Corrosion resistance class (CRC) ¹⁾	1 - Low corrosion stress		
LABS (PWIS) conformity	VDMA24364-B1/B2-L		

1) For more information, visit www.festo.com/x/topic/kbk

Solenoid valves, 5/2 directional valves, electrical data

Electrical connection	Via F coil, to be ordered separately
Coil characteristics	See solenoid coil, to be ordered separately
Degree of protection	IP65


Weights

Pneumatic connection 1	G1/8	G1/4	G1/2
On switching time	8 ms	9 ms	21 ms
Switching time off	36 ms	29 ms	150 ms


Datasheet

Materials	
Housing material	Die-cast aluminum
Seals material	NBR, TPE-U(PU)
Note on materials	RoHS compliant


Solenoid valves, 5/2-way valves, minimum pilot pressure p_{12}/p_{14} as a function of operating pressure p_1 (external pilot air supply), MFH-5-1/8-S



Solenoid valves, 5/2-way valves, minimum pilot pressure p_{12}/p_{14} as a function of operating pressure p_1 (external pilot air supply), MFH-5-1/4-S



Datasheet

Solenoid valves, 5/2-way valves, minimum pilot pressure p_{12}/p_{14} as a function of operating pressure p_1 (external pilot air supply), MFH-5-1/2-S

General technical data

General technical data				
Pneumatic connection 1	G1/8		G1/4	G1/2
Actuation type	Electrical	Pneumatic	Electrical	
Valve function	5/2-way, bistable, 5/2-way, dominant, bistable	5/2-way, bistable	5/2-way, bistable, 5/2-way, dominant, bistable	5/2-way, bistable
Structural design	Plate seat			
Lap	Negative overlap			
Sealing principle	Soft			
Type of control	Piloted			
Pilot air supply port	External			
Flow direction	Non-reversible			
Exhaust air function	Adjustable			
Manual override	Detenting			
Type of mounting	Alternatively:, On terminal strip, On PR manifold rail, With through-hole	Alternatively:, On terminal strip, With through-hole		
Mounting position	Any			
Electrical connection	Via F coil, to be ordered separately			
Venting hole connection	M3	–	M3	
Pilot air port 12	M5			G1/8
b-value	–			0.3
Nominal width	5 mm		7 mm	14 mm
Normal nominal flow rate (normalized to DIN 1343)	600 l/min, 601 l/min	600 l/min	1,100 l/min	4,500 l/min
Product weight	260 g		344 g, 530 g	1,210 g

Solenoid valves, 5/2-way valves, double solenoid valves, safety-related characteristics

Pneumatic connection 1	G1/8		G1/4	G1/2
Max. switching frequency	16 Hz	25 Hz	16 Hz	25 Hz
Max. positive test pulse with 0 signal	2,200 µs			
Max. negative test pulse on 1 signal	3,700 µs			

Datasheet

Solenoid valves, 5/2directional valves, solenoid pilot valves, operating and environmental conditions

Pneumatic connection 1	G1/8	G1/4	G1/2
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]		
Pilot medium	Compressed air as per ISO 8573-1:2010 [7:4:4]		Compressed air as per ISO 8573-1:2010 [7:4:4], Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)		
Operating pressure	0 ... 1 MPa		0 ... 0.8 MPa
Operating pressure	0 ... 10 bar		0 ... 8 bar
Pilot pressure MPa	0.12 ... 0.8 MPa		0.05 ... 0.8 MPa
Pilot pressure	1.2 ... 8 bar		0.5 ... 8 bar
Ambient temperature	-5 ... 40°C		
Temperature of medium	-10 ... 60°C		
Storage temperature	-20 ... 60°C		
Certification	c UL us - recognized (OL)		
Corrosion resistance class (CRC) ¹⁾	1 - Low corrosion stress		
LABS (PWIS) conformity	VDMA24364-B1/B2-L		

1) For more information, visit www.festo.com/x/topic/kbk

Solenoid valves, 5/2-way valves, double solenoid valves, safety-related characteristics


Electrical connection	Via F coil, to be ordered separately
Coil characteristics	See solenoid coil, to be ordered separately
Degree of protection	IP65

Weights

Pneumatic connection 1	G1/8	G1/4	G1/2
Valve function	5/2-way, bistable	5/2-way, dominant, bistable	5/2-way, bistable
Changeover time	10 ms	16 ms	11 ms


Materials

Housing material	Die-cast aluminum
Seals material	NBR, TPE-U(PU)
Note on materials	RoHS compliant


Solenoid valves, 5/2-way valves, double solenoid valves, minimum pilot pressure p_{12}/p_{14} as a function of operating pressure p_1 (external pilot air supply), JMFH-5-1/8-S

Datasheet

Solenoid valves, 5/2-way valves, double solenoid valves, minimum pilot pressure p_{12}/p_{14} as a function of operating pressure p_1 (external pilot air supply), JMFH-5-1/4-S



Solenoid valves, 5/2-way valves, double solenoid valves, minimum pilot pressure p_{12}/p_{14} as a function of operating pressure p_1 (external pilot air supply), JMFH-5-1/2-S



Datasheet

General technical data				
Pneumatic connection 1	G1/8	G1/4	G1/2	G3/4
Valve function	3/2, open/closed, monostable			
Structural design	Plate seat			
Lap	Negative overlap			
Sealing principle	Soft			
Actuation type	Pneumatic			
Reset method	Mechanical spring			
Type of control	directly			
Pilot air supply port	External			
Flow direction	Reversible			
Exhaust air function	Adjustable			
Manual override	–		None	–
Type of mounting	Alternatively:, On terminal strip, On PR manifold rail, With through-hole	Alternatively:, On terminal strip, With through-hole		
Mounting position	Any			
Electrical connection	–			Via F coil, to be ordered separately
Venting hole connection	M3			
Pilot air port 12	G1/8		G1/4	
b-value	–		0.3	–
Nominal width	5 mm	7 mm	14 mm	19 mm
Normal nominal flow rate (normalized to DIN 1343)	500 l/min	800 l/min	3,700 l/min	7,500 l/min
Product weight	150 g	230 g	860 g	1,200 g

Pneumatic valves, 3/2-way valves, safety-related characteristics				
Pneumatic connection 1	G1/8	G1/4	G1/2	G3/4
Max. switching frequency	12 Hz	–		
Max. positive test pulse with 0 signal	2,200 µs	–		
Max. negative test pulse on 1 signal	3,700 µs	–		

Pneumatic valves, 3/2-way valves, ATEX	
ATEX category gas	II 2G
Type of ignition protection for gas	Ex h IIC T4 Gb
ATEX category for dust	II 2D
Type of (ignition) protection for dust	Ex h IIIC T130°C Db
Explosive ambient temperature	-10°C ≤ Ta ≤ +60°C
CE marking (see declaration of conformity) ¹⁾	as per EU explosion protection directive (ATEX)
UKCA marking (see declaration of conformity) ²⁾	acc. to UK EX instructions
Explosion protection certification outside the EU	EPL Db (GB) EPL Gb (GB)
Degree of protection	IP65

1) Further information www.festo.com/catalogue/...d/Support/Downloads.2) Further information www.festo.com/catalogue/...d/Support/Downloads.

Datasheet

Pneumatic valves, 3/2directional valves, operating and environmental conditions

Pneumatic connection 1	G1/8	G1/4	G1/2	G3/4
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]			
Pilot medium	Compressed air as per ISO 8573-1:2010 [7:4:4]			
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)			
Operating pressure	-0.095 ... 1 MPa			
Operating pressure	-0.95 ... 10 bar			
Pilot pressure MPa	0.1 ... 1 MPa			
Pilot pressure	1 ... 10 bar			
Ambient temperature	-10 ... 60°C			
Temperature of medium	-10 ... 60°C			
Storage temperature	-20 ... 60°C			
Corrosion resistance class (CRC) ¹⁾	1 - Low corrosion stress			
LABS (PWIS) conformity	VDMA24364-B1/B2-L			

1) For more information, visit www.festo.com/x/topic/kbk


Weights

Pneumatic connection 1	G1/8	G1/4	G1/2	G3/4
On switching time	4 ms	7 ms	17 ms	12 ms
Switching time off	10 ms	26 ms	30 ms	35 ms

Materials


Housing material	Die-cast aluminum
Seals material	NBR
Note on materials	RoHS compliant

Pneumatic valves, 3/2-way valves, minimum pilot pressure $p_{12}/p_{14}/p_{110}$ as a function of operating pressure p_1/p_{11} , VL/0-3-1/4 - normally closed




Datasheet


Pneumatic valves, 3/2-way valves, minimum pilot pressure $p_{12}/p_{14}/p_{110}$ as a function of operating pressure p_1/p_{11} , VL/0-3-1/4 - normally open





Pneumatic valves, 3/2-way valves, minimum pilot pressure $p_{12}/p_{14}/p_{110}$ as a function of operating pressure p_1/p_{11} , VL/0-3-1/2 - normally closed



Pneumatic valves, 3/2-way valves, minimum pilot pressure $p_{12}/p_{14}/p_{110}$ as a function of operating pressure p_1/p_{11} , VL/0-3-1/2 - normally open



Datasheet

Pneumatic valves, 3/2-way valves, minimum pilot pressure $p_{12}/p_{14}/p_{110}$ as a function of operating pressure p_1/p_{11} , VL/0-3-3/4 - normally closedPneumatic valves, 3/2-way valves, minimum pilot pressure $p_{12}/p_{14}/p_{110}$ as a function of operating pressure p_1/p_{11} , VL/0-3-3/4 - normally open

General technical data

Pneumatic connection 1	G1/8	G1/4	G1/2
Valve function	5/2-way, monostable		
Structural design	Plate seat		
Lap	Negative overlap		
Sealing principle	Soft		
Actuation type	Pneumatic		
Reset method	Mechanical spring		
Type of control	directly		
Pilot air supply port	External		
Flow direction	Non-reversible		
Exhaust air function	Adjustable		
Manual override	–		None
Type of mounting	Alternatively:, On terminal strip, On PR manifold rail, With through-hole		Alternatively:, On terminal strip, With through-hole
Mounting position	Any		
Venting hole connection	M3		
Pilot air port 12	G1/8	–	
b-value	–		0.32
C value	–		17.65 l/sbar
Nominal width	5 mm	7 mm	14 mm
Normal nominal flow rate (normalized to DIN 1343)	500 l/min	800 l/min	3,700 l/min
Product weight	220 g		1,070 g

Datasheet

Pneumatic valves, 5/2-way valves, safety-related characteristics

Pneumatic connection 1	G1/8	G1/4	G1/2
Max. switching frequency	12	–	–
Max. positive test pulse with 0 signal	2,200	–	–
Max. negative test pulse on 1 signal	3,700	–	–

Pneumatic valves, 5/2directional valves, operating and environmental conditions

Pneumatic connection 1	G1/8	G1/4	G1/2
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]		
Pilot medium	Compressed air as per ISO 8573-1:2010 [7:4:4]		
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)		
Operating pressure	0 ... 1 MPa	0 ... 0.8 MPa	0 ... 1 MPa
Operating pressure	0 ... 10 bar	0 ... 8 bar	0 ... 10 bar
Pilot pressure MPa	0.12 ... 1 MPa		
Pilot pressure	1.2 ... 10 bar		
Ambient temperature	-10 ... 60°C		
Temperature of medium	-10 ... 60°C		
Storage temperature	-20 ... 60°C		
Corrosion resistance class (CRC) ¹⁾	1 - Low corrosion stress		
LABS (PWIS) conformity	VDMA24364-B1/B2-L		


1) For more information, visit www.festo.com/x/topic/kbk

Weights


Pneumatic connection 1	G1/8	G1/4	G1/2
On switching time	5 ms	7 ms	3 ms
Switching time off	16 ms	11 ms	27 ms

Materials

Housing material	Die-cast aluminum
Seals material	NBR, TPE-U(PU)
Note on materials	RoHS compliant

Pneumatic valves, 5/2-way valves, minimum pilot pressure p₁₂/p₁₄ as a function of operating pressure p₁, VL-5-1/8

Datasheet

Pneumatic valves, 5/2-way valves, minimum pilot pressure p_{12}/p_{14} as a function of operating pressure p_1 , VL-5-1/4Pneumatic valves, 5/2-way valves, minimum pilot pressure p_{12}/p_{14} as a function of operating pressure p_1 , VL-5-1/2

General technical data

Pneumatic connection 1	G1/8	G1/4	G1/2
Valve function	5/2-way, bistable, 5/2-way, dominant, bistable		5/2-way, bistable
Structural design	Plate seat		
Lap	Negative overlap		
Sealing principle	Soft		
Actuation type	Pneumatic		
Type of control	directly		
Pilot air supply port	External		
Flow direction	Non-reversible		
Exhaust air function	Adjustable		
Manual override	—		Detenting
Type of mounting	Alternatively:, On terminal strip, With through-hole		
Mounting position	Any		
Venting hole connection	M3		
b-value	—		0.3
Nominal width	5 mm	7 mm	14 mm
Normal nominal flow rate (normalized to DIN 1343)	600 l/min	1,100 l/min	4,500 l/min
Product weight	330 g	1,130 g	

Datasheet

Pneumatic valves, 5/2-way valves, impulse valves, safety-related characteristics

Pneumatic connection 1	G1/8	G1/4	G1/2
Max. switching frequency	12 Hz		
Max. positive test pulse with 0 signal	2,200	–	
Max. negative test pulse on 1 signal	3,700	–	

Pneumatic valves, 5/2directional valves, Double pilot valves, Operating and environmental conditions

Pneumatic connection 1	G1/8	G1/4	G1/2
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]		
Pilot medium	–	Compressed air as per ISO 8573-1:2010 [7:4:4]	
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)		
Operating pressure	0 ... 1 MPa	0 ... 0.8 MPa	0 ... 1 MPa
Operating pressure	0 ... 10 bar	0 ... 8 bar	0 ... 10 bar
Pilot pressure MPa	0.12 ... 1 MPa		
Pilot pressure	1.2 ... 10 bar		
Ambient temperature	-10 ... 60°C		
Temperature of medium	-10 ... 60°C		
Storage temperature	-20 ... 60°C		
Corrosion resistance class (CRC) ¹⁾	1 - Low corrosion stress		
LABS (PWIS) conformity	VDMA24364-B1/B2-L		


1) For more information, visit www.festo.com/x/topic/kbk

Weights

Pneumatic connection 1	G1/8	G1/4	G1/2
Valve function	5/2-way, bistable	5/2-way, dominant, bistable	5/2-way, bistable
Changeover time	7 ms	12 ms	3 ms


Materials

Housing material	Die-cast aluminum
Seals material	NBR, TPE-U(PU)
Note on materials	RoHS compliant


Pneumatic valves, 5/2-way valves, impulse valves, minimum pilot pressure p₁₂/p₁₄ as a function of operating pressure p₁, JH-5-1/8

Datasheet


Pneumatic valves, 5/2-way valves, impulse valves, minimum pilot pressure p_{12}/p_{14} as a function of operating pressure p_1 , JDH-5-1/8



Pneumatic valves, 5/2-way valves, impulse valves, minimum pilot pressure p_{12}/p_{14} as a function of operating pressure p_1 , JH-5-1/4




Pneumatic valves, 5/2-way valves, impulse valves, minimum pilot pressure p_{12}/p_{14} as a function of operating pressure p_1 , JDH-5-1/4




Datasheet

Pneumatic valves, 5/2-way valves, impulse valves, minimum pilot pressure p_{12}/p_{14} as a function of operating pressure p_1 , JH-5-1/2



Dimensions

Dimensions – Solenoid valves, 3/2-way valves, MFH, MOFH

[Download CAD data](http://www.festo.com)


[1] Additional connection for external pilot air with MFH-3-... /MOFH-3-...

[2] Solenoid coil can be rotated by 360°


[3] Manual override can be repositioned by 180°

	B1	B2	B3	B4	B6	D1	D2	D4	D5 Ø
MFH-3-1/8	26 ±0,2	3,5	3,5	–	22	G1/8	–	M5	5,5
MOFH-3-1/8				2,7			M5		
MFH-3-1/8-S									
MFH-3-1/4	30,4 ±0,15	5	5	–		G1/4	–	M5	6,5
MOFH-3-1/4				4			M5		
MFH-3-1/4-S	30,4								
MFH-3-1/2	52 ±0,15	8	8	–		G1/2	–	M5	8,6
MOFH-3-1/2							G1/8		
MFH-3-1/2-S	52								
MFH-3-3/4	68 ±0,15	8	8	–		G3/4	–	M5	8,6
MOFH-3-3/4							G1/8		
MFH-3-3/4-S	68								

	H1	H2	H3	H4	H5	H6	H7	L1	L2
MFH-3-1/8	97	115	12,5	19 ±0,15	22	–	63	45 ±0,15	71
MOFH-3-1/8						9,5			
MFH-3-1/8-S						–			
MFH-3-1/4	112	130	17	24 ±0,15	29	–	78	50 ±0,15	73,5
MOFH-3-1/4				24		9,5		50	
MFH-3-1/4-S				–		–		–	
MFH-3-1/2	151	168,8	30 ±0,15	38 ±0,15	49 ±0,15	–	117	80 ±0,2	88,5
MOFH-3-1/2			30	38	49	10,5		80	
MFH-3-1/2-S			–	–	–	–		–	
MFH-3-3/4	171	187	34	44 ±0,15	56	–	137	92 ±0,2	94,5
MOFH-3-3/4				44		11		92	
MFH-3-3/4-S				–		–		–	

Dimensions


Dimensions – Solenoid valves, 3/2-way valves, mounting pattern [Download CAD data](http://www.festo.com) www.festo.com



	D5 Ø	H10	H12	L3
MFH-3-1/8	5,5	12,5	22	35 ±0,15
MOFH-3-1/8				
MFH-3-1/8-S				
MFH-3-1/4	6,5	5	29	40 ±0,15
MOFH-3-1/4				
MFH-3-1/4-S				
MFH-3-1/2	8,6	68	49	58 ±0,2
MOFH-3-1/2				
MFH-3-1/2-S				
MFH-3-3/4	8,6	78	56	72 ±0,2
MOFH-3-3/4				
MFH-3-3/4-S				

Dimensions

Dimensions – Solenoid valves, 5/2-way valves, MFH

[Download CAD data](http://www.festo.com)


[1] Additional connection for external pilot air with MFH-5-...-S

[2] Solenoid coil can be rotated by 360°


[3] Manual override can be repositioned by 180°

	B1	B2	B3	B4	B6	D1	D2	D4	D5 Ø
MFH-5-1/8	26 ±0,2	3,5 ±0,15	3,5 ±0,15	–	22	G1/8	M5	M5	5,5
MFH-5-1/8-S		3,5	3,5	2,7					5,5 – 6,2
MFH-5-1/4	30,4 ±0,1	–	5 ±0,15	–		G1/4	M5		6,5 ±0,14
MFH-5-1/4-S				4					min. 6,5
MFH-5-1/2	52 ±0,15	–	8	–		G1/2	G1/8		8,5
MFH-5-1/2-S									

	H1	H2	H3	H4	H5	H6	H7	L1	L2
MFH-5-1/8	117	131	13,5	19	23	–	83	45 ±0,15	71
MFH-5-1/8-S		135		19 ±0,15		9,5			71,5
MFH-5-1/4	128	145	12	24 ±0,15	28 +0,1/-0,2	–	94	50 +0,4/-0,2	73,5
MFH-5-1/4-S						9,5			
MFH-5-1/2	192	209,8	32 ±0,15	38 ±0,15	51 ±0,15	–	158	80 +0,4/-0,2	87,5
MFH-5-1/2-S						10,5			

Dimensions

Dimensions – Solenoid valves, 5/2-way valves, mounting pattern [Download CAD data](http://www.festo.com) www.festo.com




	D5 ø	H10	H11	H12	H13	L3
MFH-5-1/8	5,5	32,5	–	23	19 ±0,15	35 ±0,15
MFH-5-1/8-S	5,5 – 6,2					
MFH-5-1/4	6,5 ±0,14	5	–	72	–	40 ±0,15
MFH-5-1/4-S	min. 6,5					
MFH-5-1/2	8,5	29,5	80 ±0,15	49,5	40 ±0,1	58 ±0,15
MFH-5-1/2-S						

Dimensions

Dimensions – Solenoid valves, 5/2-way valves, solenoid pulse valves, JMFH, JMFDH

Download CAD data www.festo.com



- [1] Additional connection for external pilot air with JMF...H-5-...-S
- [2] Solenoid coil can be rotated by 360°
- [3] Manual override can be repositioned by 180°

Dimensions


	B1	B2	B3	B4	D1	D2	D4	D5 ø
JMFH-5-1/8	26 +0,2	3,5 +0,15	3,5 +0,15	–	G1/8	–	M5	5,5
JMFDH-5-1/8				2,7		M5		
JMFH-5-1/8-S								
JMFH-5-1/4	30,4 ±0,1	–	5	–	G1/4	–	M5	min. 6,5
JMFDH-5-1/4				4		M5		
JMFH-5-1/4-S								
JMFH-5-1/2	52	–	8	–	G1/2	–	M5	9,6 +0,2
JMFH-5-1/2-S	52 ±0,15					G1/8		8,5

	H1	H2	H4	H6	H7	L1	L2
JMFH-5-1/8	184	219	19 ±0,15	–	116,5	45 ±0,15	71,5
JMFDH-5-1/8				9,5			
JMFH-5-1/8-S							
JMFH-5-1/4	202	238	24 -0,3	–	134	50 +0,4/-0,2	74
JMFDH-5-1/4				9,5			
JMFH-5-1/4-S							
JMFH-5-1/2	244	279,6	38	–	176	80	88,5
JMFH-5-1/2-S			38 ±0,1	10,5		80 +0,4/-0,2	87,5

Dimensions

Dimensions – Solenoid valves, 5/2-way valves, double solenoid valves,
mounting pattern


Download CAD data www.festo.com



	D5 ø	H10	H12	H13	L3
JMFH-5-1/8	5,5	19	58,3	–	35
JMFDH-5-1/8					
JMFH-5-1/8-S					
JMFH-5-1/4	min. 6,5	67	67	–	40
JMFDH-5-1/4					
JMFH-5-1/4-S					
JMFH-5-1/2	9,6 +0,2	40	88	80	58
JMFH-5-1/2-S	8,5				

Dimensions

Dimensions – Pneumatic valves, 3/2-way valves, VL/O Download CAD data www.festo.com




	B1	B2	B3	B5	D1	D3	D5 ø	H3	H4	H5	H8	H9	L1
VL/O-3-1/8	26	3,5	3,5	3	G1/8	G1/8	5,5	12,5	19	22	65	8	45
VL/O-3-1/4	30,4	5	5	–	G1/4	G1/8	6,5	17	24	29	80	8	50
VL/O-3-1/2	52	8	8	–	G1/2	G1/4	8,6	30	38	49	118	10	80
VL/O-3-3/4	68	8	8	–	G3/4	G1/4	8,6	34	44	56	138	10	92

Dimensions

Dimensions – Pneumatic valves, 3/2-way valves, mounting pattern


Download CAD data www.festo.com



	D5 Ø	H10	H12	L3
VL/O-3-1/8	5,5	12,5	22	35 ±0,15
VL/O-3-1/4	6,5	5	29	40 ±0,15
VL/O-3-1/2	8,6	68	49	58 ±0,2
VL/O-3-3/4	8,6	78	56	72 ±0,2

Dimensions


Dimensions – Pneumatic valves, 5/2-way valves, VL Download CAD data www.festo.com



	B1	B2	B3	B5	D1	D3	D5 ø	H3	H4	H5	H8	H9	L1
VL-5-1/8	26	3,5	3,5	3	G1/8	G1/8	5,5	13,5	19	23	85	8	45
VL-5-1/4	30,4 ±0,1	–	5,2	–	G1/4	G1/8	6,5	12	24	28	96	8	50
VL-5-1/2	52	–	8	–	G1/2	G1/4	9	32	38	51	159	10	80

Dimensions


Dimensions – Pneumatic valves, 5/2-way valves, mounting pattern

[Download CAD data](http://www.festo.com) www.festo.com


	D5 ø	H10	H11	H12	H13	L3
VL-5-1/8	5,5	32,5	–	23	19 ±0,15	35 ±0,15
VL-5-1/4	6,5	5	–	72	–	40 ±0,15
VL-5-1/2	9	29,5	80 ±0,15	49,5	40 ±0,1	58 ±0,15

Dimensions

Dimensions – Pneumatic valves, 5/2 way valves, double pilot valves, JH, JDH Download CAD data www.festo.com




	B1	B2	B3	B5	D1	D3	D5 Ø	D6 Ø	H1	H4	H8	H9	L1
JH-5-1/8	26	3,5	3,5	3	G1/8	G1/8	5,3	5	132	19	120	8	45
JDH-5-1/8													
JH-5-1/4	30,4	–	5	–	G1/4	G1/8	6,5	5	149	24	138	8	50
JDH-5-1/4													
JH-5-1/2	52	–	8	–	G1/2	G1/4	9,6 +0,2	9,9	193	38	178	10	80

Dimensions

Dimensions – Pneumatic valves, 5/2-way valves, double pilot valves, mounting pattern


Download CAD data www.festo.com



	D5 Ø	H10	H11	H12	H13	L3
JH-5-1/8	5,3	60	–	50,5	19	35
JDH-5-1/8						
JH-5-1/4	6,5	40	–	107	–	40 ±0,2
JDH-5-1/4						
JH-5-1/2	9,6 +0,2	49	80 ±0,15	69	40 ±0,1	58 ±0,15

Dimensions

Dimensions – Manifold rail PAL Download CAD data www.festo.com




	B1	B2	B3	B4	B5	D1	D3	D4	H1	H2	H3	L5	L6	L7	L8	⌀ 1	⌀ 2
PAL-1/8	20	21	2	33,5	44,5	G1/8	G1/4	5,2	44	32	43	18	34	12	4	19	8
PAL-1/4	28	27	2	42	56	G1/4	G3/8	7	56	44	56	20	32	14	4	24	10
PAL-1/2	40	40	3	73	93	G1/2	G3/4	11	80	60	75	35	69	16	5	36	17

Dimensions

Dimensions – Manifold block PRS


Download CAD data www.festo.com




	B1	B2	B3	B4	D1	D2	D3	H1	H2	H3	H4	L3	L4	L5	L6	L7	L8	≈ 1	≈ 2
PRS-1/8	28,5	22	12,5	10,8	G1/8	G3/8	6,6	80	56	38	28	23,5	7	27	7	12	5	8	14
PRS-1/4	34,5	27,5	14	14	G1/4	G1/2	6,6	92	62	48	31	29,2	5	31,4	7	14	6	10	17

Ordering data


Solenoid valves, 3/2-way valves, MFH-..., without F solenoid coil, internal pilot air supply

	Pneumatic connection 1	Pneumatic connection 2	Pneumatic connection 3	Part no.	Type
	G1/8	G1/8	G1/8	535897	MFH-3-1/8-EX
				7802	MFH-3-1/8
	G1/4	G1/4	G1/4	9964	MFH-3-1/4
				535898	MFH-3-1/4-EX
	G1/2	G1/2	G1/2	9857	MFH-3-1/2
				535899	MFH-3-1/2-EX
	G3/4	G3/4	G3/4	536190	MFH-3-3/4-EX
				11967	MFH-3-3/4


Solenoid valves, 3/2-way valves, MOFH-..., without F solenoid coil, internal pilot air supply

	Pneumatic connection 1	Pneumatic connection 2	Pneumatic connection 3	Part no.	Type
	G1/8	G1/8	G1/8	7877	MOFH-3-1/8
				535903	MOFH-3-1/8-EX
	G1/4	G1/4	G1/4	7876	MOFH-3-1/4
				535904	MOFH-3-1/4-EX
	G1/2	G1/2	G1/2	535905	MOFH-3-1/2-EX
				7884	MOFH-3-1/2
	G3/4	G3/4	G3/4	11969	MOFH-3-3/4
				536192	MOFH-3-3/4-EX


Solenoid valves, 3/2-way valves, MFH-..., without F solenoid coil, external pilot air supply, reversible (vacuum at port 1 without restrictions, vacuum at port 3 with restrictions)

	Pneumatic connection 1	Pneumatic connection 2	Pneumatic connection 3	Part no.	Type
	G1/8	G1/8	G1/8	535900	MFH-3-1/8-S-EX
				7958	MFH-3-1/8-S
	G1/4	G1/4	G1/4	7959	MFH-3-1/4-S
				535901	MFH-3-1/4-S-EX
	G1/2	G1/2	G1/2	7960	MFH-3-1/2-S
				535902	MFH-3-1/2-S-EX
	G3/4	G3/4	G3/4	536191	MFH-3-3/4-S-EX
				11968	MFH-3-3/4-S


Solenoid valves, 5/2-way valves, MFH-..., without F solenoid coil, internal pilot air supply


	Pneumatic connection 1	Pneumatic connection 2	Pneumatic connection 3	Part no.	Type
	G1/8	G1/8	G1/8	535906	MFH-5-1/8-EX
				9982	MFH-5-1/8
	G1/4	G1/4	G1/4	535907	MFH-5-1/4-EX
				6211	MFH-5-1/4
	G1/2	G1/2	G1/2	6420	MFH-5-1/2
				535908	MFH-5-1/2-EX


Solenoid valves, 5/2-way valves, MFH-..., without F solenoid coil, external pilot air supply


	Pneumatic connection 1	Pneumatic connection 2	Pneumatic connection 3	Part no.	Type
	G1/8	G1/8	G1/8	10348	MFH-5-1/8-S
				535909	MFH-5-1/8-S-EX
	G1/4	G1/4	G1/4	535910	MFH-5-1/4-S-EX
				10349	MFH-5-1/4-S
	G1/2	G1/2	G1/2	535911	MFH-5-1/2-S-EX
				35547	MFH-5-1/2-S


Ordering data


Solenoid valves, 5/2-way valves, double solenoid valves, JMFH-..., without F solenoid coil, internal pilot air supply					
	Pneumatic connection 1	Pneumatic connection 2	Pneumatic connection 3	Part no.	Type
	G1/8	G1/8	G1/8	8820	JMFH-5-1/8
				535912	JMFH-5-1/8-EX
	G1/4	G1/4	G1/4	535913	JMFH-5-1/4-EX
				10410	JMFH-5-1/4
	G1/2	G1/2	G1/2	535914	JMFH-5-1/2-EX
				10166	JMFH-5-1/2

Solenoid valves, 5/2-way valves, double solenoid valves, JMFH-..., without F solenoid coil, external pilot air supply					
	Pneumatic connection 1	Pneumatic connection 2	Pneumatic connection 3	Part no.	Type
	G1/8	G1/8	G1/8	535915	JMFH-5-1/8-S-EX
				14008	JMFH-5-1/8-S
	G1/4	G1/4	G1/4	14009	JMFH-5-1/4-S
				535916	JMFH-5-1/4-S-EX
	G1/2	G1/2	G1/2	35548	JMFH-5-1/2-S
				535917	JMFH-5-1/2-S-EX


Solenoid valves, 5/2-way valves, double solenoid valves, JMFHD-..., without F solenoid coil, internal pilot air supply, with dominant signal at 14					
	Pneumatic connection 1	Pneumatic connection 2	Pneumatic connection 3	Part no.	Type
	G1/8	G1/8	G1/8	536193	JMFHD-5-1/8-EX
				8821	JMFHD-5-1/8
	G1/4	G1/4	G1/4	536194	JMFHD-5-1/4-EX
				10411	JMFHD-5-1/4

Pneumatic valves, 3/2-way valves, mechanical reset type, normally open or closed, reversible (vacuum at port 1 without restrictions, vacuum at port 3 with restrictions), VL/O-...					
	Pneumatic connection 1	Pneumatic connection 2	Pneumatic connection 3	Part no.	Type
	G1/8	G1/8	G1/8	536028	VL/O-3-1/8-B-EX
				7803	VL/O-3-1/8-B
	G1/4	G1/4	G1/4	536029	VL/O-3-1/4-EX
				9984	VL/O-3-1/4
	G1/2	G1/2	G1/2	9983	VL/O-3-1/2
				536030	VL/O-3-1/2-EX
	G3/4	G3/4	G3/4	10049	VL/O-3-3/4
				536031	VL/O-3-3/4-EX

Pneumatic valves, 5/2-way valves, mechanical reset type, VL-...					
	Pneumatic connection 1	Pneumatic connection 2	Pneumatic connection 3	Part no.	Type
	G1/8	G1/8	G1/8	536032	VL-5-1/8-EX
				9764	VL-5-1/8
	G1/4	G1/4	G1/4	536033	VL-5-1/4-EX
				9199	VL-5-1/4
	G1/2	G1/2	G1/2	9445	VL-5-1/2
				536034	VL-5-1/2-EX


Pneumatic valves, 5/2 way valves, impulse valves, JH-...					
	Pneumatic connection 1	Pneumatic connection 2	Pneumatic connection 3	Part no.	Type
	G1/8	G1/8	G1/8	536035	JH-5-1/8-EX
				8823	JH-5-1/8
	G1/4	G1/4	G1/4	536036	JH-5-1/4-EX
				10408	JH-5-1/4
	G1/2	G1/2	G1/2	10165	JH-5-1/2
				536037	JH-5-1/2-EX

Ordering data

Pneumatic valves, 5/2 way valves, impulse valves, with dominant signal at 14, JDH-...					
	Pneumatic connection 1	Pneumatic connection 2	Pneumatic connection 3	Part no.	Type
	G1/8	G1/8	G1/8	536038	JDH-5-1/8-EX
				8824	JDH-5-1/8
	G1/4	G1/4	G1/4	536039	JDH-5-1/4-EX
				10409	JDH-5-1/4

Peripherals overview

Solenoid valves, mounting on manifold block




Accessories		→ Page/Internet
Type/order code	Description	
[1] Solenoid valve JMFH	For F solenoid coil	jmfh
[2] F-solenoid coil MSFG, MSFW	–	46
[3] Illuminating seal M...-LD	For displaying the switching status	47
[4] Plug socket MSSD-F	For valves MFH, JMFH	47
[5] Connecting cable KMF	For valves MFH, JMFH	47
[6] Plug socket MSSD-F-S	For valves MFH, JMFH	
[7] Push-in fitting QS	For connecting tubing with standard O.D.	qs
[8] Cover plate PRSB	To cover a vacant position	46
[9] Blanking plug B	3 pieces included in the scope of delivery of the PRS manifold block	blindstopfen

Peripherals overview

Accessories		→ Page/Internet
Type/order code	Description	
[10] Manifold block PRS	–	45
[11] Hollow bolt VT	For compressed air distribution or for separate compressed air supply	46
[12] Silencer	For mounting in exhaust ports	u

Peripherals overview

Solenoid valves, mounting on manifold rail




Accessories		→ Page/Internet
Type/order code	Description	
[1] Solenoid valve MFH	For F solenoid coil	mfh
[2] Solenoid valve JMFH	For F solenoid coil	jmfh
[3] Silencer	For mounting in exhaust ports	u
[4] Push-in fitting QS	For connecting tubing with standard O.D.	qs
[5] F-solenoid coil MSFG, MSFW	—	46
[6] Illuminating seal M...-LD	For displaying the switching status	47
[7] Plug socket MSSD-F	-	47
[8] Connecting cable KMF	-	47
[9] Plug socket MSSD-FS	For valves MFH, JMFH	

Peripherals overview

Accessories		→ Page/Internet
Type/order code	Description	
[10] Cap nut VTM	To close a vacant position	45
[11] Manifold rail PAL	–	45
[12] Hollow bolt VT	For compressed air distribution or for separate compressed air supply	46
[13] Blanking plug B	3 pieces included in the scope of delivery of the PRS manifold block	↗ blindstopfen

Peripherals overview


Pneumatic valves, mounting on manifold block



Accessories			→ Page/Internet
Type/order code	Description		
[1] Pneumatic valve VL, JH	–		vl, jh
[2] Push-in fitting QS	For connecting tubing with standard O.D.		qs
[3] Cover plate PRSB	To cover a vacant position		46
[4] Blanking plug B	3 pieces included in the scope of delivery of the PRS manifold block		blindstopfen
[5] Manifold block PRS	–		45
[6] Hollow bolt VT	For compressed air distribution or for the separate compressed air supply		46
[7] Silencer	For mounting in exhaust ports		u

Peripherals overview

Pneumatic valves, mounting on manifold rail




Accessories		→ Page/Internet
Type/order code	Description	
[1] Pneumatic valve VL, JH	–	v l, j h
[2] Push-in fitting QS	For connecting tubing with standard O.D.	q s
[3] Silencer	For mounting in exhaust ports	u
[4] Cap nut VTM	To close a vacant position	45
[5] Manifold rail PAL	–	45
[6] Hollow bolt VT	For compressed air distribution or for the separate compressed air supply	46
[7] Blanking plug B	3 pieces included in the scope of delivery of the PRS manifold block	blindstopfen

Accessories

Manifold rail PAL					
	Pneumatic connection 1	Product weight	Material of sub-base	Part no.	Type
	G1/4	145 g	Aluminum, Anodized	8601	PAL-1/8-2
		170 g		8602	PAL-1/8-3
		190 g		8603	PAL-1/8-4
		215 g		8604	PAL-1/8-5
		240 g		9767	PAL-1/8-6
	G3/8	330 g	Aluminum	9188	PAL-5-1/4-2
		405 g		9189	PAL-5-1/4-3
		480 g		9190	PAL-5-1/4-4
		555 g		9191	PAL-5-1/4-5
		630 g		9192	PAL-5-1/4-6
	G3/4	770 g	Aluminum, Anodized	9492	PAL-1/2-2
		915 g		9493	PAL-1/2-3
		1,060 g		9494	PAL-1/2-4
		1,220 g		9495	PAL-1/2-5
		1,370 g		9496	PAL-1/2-6

Hollow bolt VT for manifold rail PAL					
	Pneumatic connection 1	Pneumatic connection 2	Hollow bolt material	Part no.	Type
	External thread G1/4	for barbed fitting, inside diameter 4 mm, with nut for barbed fitting, inside diameter 6 mm, with nut	Anodized aluminum	5928	VT-1/8-1
				9986	VT-1/2
			Chromated steel	8626	VT-1/8
				206147	VT-1/4-2

Cap nut VTM for closing reserve spaces					
	LABS (PWIS) conformity			Part no.	Type
	VDMA24364-B1/B2-L			9768	VTM-1/8
				9987	VTM-1/2
				3099	VTM-1/4

Manifold block PRS					
	Pneumatic connection 1	Product weight	Material of sub-base	Part no.	Type
	G3/8	360 g	Aluminum	11898	PRS-1/8-2-B
		460 g		11899	PRS-1/8-3-B
		625 g		11900	PRS-1/8-4-B
		650 g		11901	PRS-1/8-5-B
		750 g		11902	PRS-1/8-6-B
	G1/2	590 g		10185	PRS-1/4-2
		750 g		10186	PRS-1/4-3
		900 g		10187	PRS-1/4-4
		1,070 g		10188	PRS-1/4-5
		1,230 g		10189	PRS-1/4-6

Accessories

Hollow bolt VT for manifold block PRS

	Hollow bolt material	Part no.	Type
	Chromated steel	9499	VT-1/4-PRS
		11539	VT-1/8-PRS


PRSB cover plate for closing reserve spaces

	Material of sub-base	Product weight	Part no.	Type
	Aluminum	55 g	11687	PRSB-1/8
		80 g	11688	PRSB-1/4


Hollow bolt VT for separate compressed air supply to the valve

	Hollow bolt material	Part no.	Type
	Chromated steel	12635	VT-1/4-AJ-P
		12910	VT-1/8-AJS-P
		12634	VT-1/8-AJK-P


F solenoid coils, without plug socket


	Coil characteristics	Type of ignition protection for gas	Type of (ignition) protection for dust	Part no.	Type
	110 V AC: 50/60 Hz, initial power 9.0 VA, holding power 7.0 VA	Ex nA IIC T4 X Gc	Ex tc IIIC T130°C X Dc IP65	34420	MSFW-110-50/60-OD
				536933	MSFW-110-50/60-EX
	12 V DC: 4.1 W	Ex nA IIC T4 X Gc	Ex tc IIIC T130°C X Dc IP65	34410	MSFG-12-OD
	230 V AC: 50/60 Hz, initial power 9.0 VA, holding power 7.0 VA			34422	MSFW-230-50/60-OD
	240 V AC: 50/60 Hz, initial power 9.0 VA, holding power 7.0 VA	Ex nA IIC T4 X Gc	Ex tc IIIC T130°C X Dc IP65	536934	MSFW-230-50/60-EX
				34424	MSFW-240-50/60-OD
	24 V AC: 50/60 Hz, initial power 9.0 VA, holding power 7.0 VA	Ex nA IIC T4 X Gc	Ex tc IIIC T130°C X Dc IP65	34415	MSFW-24-50/60-OD
	24 V DC: 4.5 W, 42 V AC: 50/60 Hz, initial power 9.0 VA, holding power 7.0 VA			536932	MSFW-24-50/60-EX
	24 V DC: 4.5 W	Ex nA IIC T4 X Gc	Ex tc IIIC T130°C X Dc IP65	34411	MSFG-24/42-50/60-OD
	42 V DC: 5.5 W			536931	MSFG-24-EX
	48 V AC: 50/60 Hz, initial power 9.0 VA, holding power 7.0 VA			34413	MSFG-42-OD
				34418	MSFW-48-50/60-OD


F solenoid coils, cable with open end, 3-wire


	Coil characteristics	Type of ignition protection for gas	Type of (ignition) protection for dust	Cable length	Part no.	Type
	110 V AC: 50/60 Hz, power 4.18 VA	Ex mb IIC T5 Gb	Ex mb IIIC T95°C Db	1 m	8059811	VACF-B-K1-16B-1-EX4-M
				5 m	8059812	VACF-B-K1-16B-5-EX4-M
	230 V AC: 50/60 Hz, power 5.0 VA			1 m	8059809	VACF-B-K1-3A-1-EX4-M
				5 m	8059810	VACF-B-K1-3A-5-EX4-M
	24 V AC: 50/60 Hz, power 3.85 VA			1 m	8059808	VACF-B-K1-1A-1-EX4-M

Accessories


F solenoid coils, cable with open end, 3-wire						
	Coil characteristics	Type of ignition protection for gas	Type of (ignition) protection for dust	Cable length	Part no.	Type
	24 V DC: 4.36 W	Ex mb IICT5 Gb	Ex mb IICT95°C Db	1 m	8059804	VACF-B-K1-1-1-EX4-M
				5 m	8059805	VACF-B-K1-1-5-EX4-M
				10 m	8059806	VACF-B-K1-1-10-EX4-M
				20 m	8059807	VACF-B-K1-1-20-EX4-M

Plug socket, without cable, cable connection with clamping screws				
	Electrical connection 2	Cable fitting	Part no.	Type
		M16x1.5	539710	MSDD-F-M16
	Screw terminal	Pg9	34431	MSDD-F


Connecting cable					
	Switching position indication	Nominal operating voltage DC	Cable length	Part no.	Type
			2.5 m	30936	KMF-1-230AC-2.5
			5 m	30938	KMF-1-230AC-5
	LED	24 V	2.5 m	30935	KMF-1-24DC-2.5-LED
			5 m	30937	KMF-1-24DC-5-LED
			10 m	193458	KMF-1-24-10-LED

Connecting cable					
	Switching position indication	Nominal operating voltage DC	Cable length	Part no.	Type
			2.5 m	30936	KMF-1-230AC-2.5
			5 m	30938	KMF-1-230AC-5
	LED	24 V	2.5 m	30935	KMF-1-24DC-2.5-LED
			5 m	30937	KMF-1-24DC-5-LED
			10 m	193458	KMF-1-24-10-LED

Illuminating seal for F solenoid coils			
	DC operating voltage range	Part no.	Type
	12 ... 24 V	19143	MF-LD-12-24DC

Plate for wide solenoid coils, as spacer when using wider solenoid coils from other manufacturers (thickness 6.35 mm), for 3/2-way valves			
	LABS (PWIS) conformity	Part no.	Type
	VDMA24364-B2-L	541667	MPL-TC-3-18
		541669	MPL-TC-3-14

Accessories

Plate for wide solenoid coils, as spacer when using wider solenoid coils from other manufacturers (thickness 6.35 mm), for 5/2-way valves			
	LABS (PWIS) conformity	Part no.	Type
	VDMA24364-B2-L	541670	MPL-TC-5-14
		541668	MPL-TC-5-18