
Standards-based valves to ISO 5599-1



Key features



Innovative

- High-performance valves in a sturdy metal housing
- Individual electrical connection via square plug sockets or centrally for each valve via round plug sockets
- Valve replacement under pressure possible using vertical pressure shut-off plate
- Reverse operation
- Vacuum operation

Versatile

- Modular system offering a range of configuration options
- Conversions and extensions are possible at any time
- Possible to integrate innovative function modules
  - Pressure regulator plate
  - Throttle plate
  - Vertical pressure shut-off plate
  - Vertical supply plate
- Vertical supply plates permit a flexible air supply and variable pressure zones
- Wide range of valve functions
- Extensive operating voltage range from 12 V DC to 230 V AC

Reliable

- Sturdy and durable metal components
  - Valves
  - Horizontally linked sub-bases
  - Vertically stacked sub-bases
- Fast troubleshooting thanks to LED in the plug socket or illuminating seal
- LED integrated in the valve with the round plug variant
- Reliable servicing thanks to valves that can be replaced quickly and easily
- Manual override
- Durable thanks to tried-and-tested piston spool valves

Easy to install

- Plug-in pressure gauges on the pressure regulator plate

Ordering data – Product options


Configurable product
This product and all its product options can be ordered using the configurator.

The configurator can be found at
➔ **www.festo.com/catalogue/...**
Enter the part number or the type.

Part no.	Type
8033845	VSVA-B-.-F.
566995	VSVA-B

Key features

Simple valve manifold assembly



[1] Pilot valve with pneumatic interface to ISO 15218
[2] Various voltages
[3] Armature tube for plug-on solenoid coils
[4] End plate
[5] Manifold sub-base
[6] Various valve functions
[7] Cover plate for vacant/expansion position
[8] Electrical connection type B to industry standard (11 mm)
[9] 3-pin round plug
[10] Manual override

Equipment options

2x 2/2-way valve, single solenoid

- Normally closed
- Normally closed, vacuum operation possible at port 3 and 5

2x 3/2-way valve, single solenoid

- Normally open
- Normally closed
- 1x normally open, 1x normally closed
- Reverse operation possible

5/2-way valve

- Single solenoid, mechanical or pneumatic spring return
- Double solenoid
- Double solenoid, with dominant signal at port 14

5/3-way valve

- Mid-position pressurised
- Mid-position closed
- Mid-position exhausted

Operation with external pilot air supply

- For vacuum applications
- For working pressures lower than 3 bar
- For significant pressure fluctuations in the power section. The power section and the pneumatic control section are isolated
- For heavily lubricated air in the power section
- For manifolds where the pressure zones are created via ducts 3 and 5 (not possible with 2x 3/2-way valves)
- For manifolds or pressure zones that are equipped with reversible 2x 3/2-way valves (valves on request)

Operation with internal pilot air supply

- For small pressure fluctuations in the power section
- For using pressure regulator plates in a vertical stacking design, also in reverse operation
- As a low-cost solution

Reverse operation with compressed air supply via ducts 3 and 5


- Pressure zone separation via ducts 3 and 5
  - Example: duct 3 vacuum, duct 5 ejector pulse
  - Example: high pressure in duct 3 for advancing the piston rod of a double-acting cylinder. Low pressure in duct 5 for retracting the piston rod with low energy consumption
- 2x 3/2-way valves used as 5/4-way valve with controllable overlap and pressure zone separation with the reversible variant

Reverse operation with a pressure regulator plate, compressed air supply via duct 1

- Reversible pressure regulator combined with a reversible 2x 3/2-way valve regulates ports 2 and 4
  - AB regulator for each of ports 2 and 4
  - A regulator for port 4
  - B regulator for port 2
- Reversible pressure regulators are in the regulating position immediately after the power supply is switched on
  - Adjustment possible at any time
  - Dynamic response characteristics
  - Reduced regulator load because the supply pressure is maintained when the valve is switched
  - Not exhausted via the regulator

Key features

Valve manifold assembly with vertical stacking



[1] Solenoid valve with individual pilot valves and pneumatic interface to ISO 15218, can be connected using square plug sockets
[2] Pressure regulator for adjusting the force of the actuated drive
[3] Vertical pressure shut-off plate for replacing solenoid valves during operation
[4] Vertical supply plate as separate compressed air supply for a valve
[5] Throttle plate for adjusting the speed of the drive
[6] Solenoid valve with central round plug
[7] Valve with 8 mm armature tube
[8] Solenoid coil with connecting cable for valves with 8 mm armature tube

Key features

Vertical stacking function

Pressure regulator

- Single variant to regulate the pressure in duct 4 or 2 or 1 at the valve
- Dual variant to regulate the pressure in ducts 4 and 2 individually
- As reversible version with ducts 1 and 3/5 swapped internally
- With pressure gauge connection

Throttle plate

- Designed with two throttle valves, at which the exhaust air flow rate at ducts 5 or 3 can be adjusted.
- The movement of the actuator is initiated via the manual override on the valve and the required speed is set via the throttle plate.


Vertical pressure shut-off plate

- This is equipped with a switch with which the compressed air supply can be shut off. As a result, components mounted on the vertical pressure shut-off plate (e.g. a valve) can be replaced without switching off the overall air supply.
- If the control chain has a redundant connection, the cycle can continue even in the case of a cyclical control system.

Vertical supply plate


- As additional air supply for a valve
- Separates the valve from duct 1 of the manifold sub-base
- To supply an additional pressure zone

Valves with solenoid coil MSF




The directional control valve has a pilot control to ISO 15218. The solenoid coil plugged onto the armature tube can be chosen in different designs and operating voltages.

Vaves with 8 mm armature tube




The directional control valve has a pilot control to ISO 15218 with 8 mm armature tube. The electrical connection is established via a standardised plug with plug pattern type A, B or C.

Valves with square plug type B to industry standard




The electrical connection is established via a standardised plug with plug pattern type B, industry standard, 24 V DC.

Valves with central plug M12



The electrical connection is established via a standardised M12 plug, 24 V DC (EN 61076-2-101).


Valves with individual plug M12x1



The electrical connection is established via a standardised M12 plug, 24 V DC (2-pin or 4-pin to VDMA).


Key features

Pressure regulator with one regulated duct




- For pressure regulation at the supply input duct 1. The set pressure is identical for ducts 2 and 4
- For pressure regulation at working port 4
  - The pressure regulator for reverse operation is supplied via duct 1 of the manifold sub-base and supplies duct 5 on the valve
  - The valve is exhausted via duct 1 to ducts 3 and 5 of the manifold sub-base
- For pressure regulation at working port 2
  - In reverse operation duct 3 is supplied

Pressure regulator with 2 regulated ducts




- For pressure regulation at working ports 4 and 2
- The pressure regulators for reverse operation are supplied via duct 1 of the manifold sub-base and supply ducts 5 and 3 on the valve
- The directional control valve is exhausted via duct 1 to ducts 3 and 5 of the manifold sub-base.

Vertical supply plate




- As intermediate supply
  - For one valve
  - To supply an additional pressure zone
- Can be equipped with a valve

Throttle plate



- Exhaust air flow control in ducts 3 and 5
- The throttle plates act as supply-air flow control for pressure zones that are created via ducts 3 and 5

Vertical pressure shut-off plate



A switch activated with a slotted screwdriver shuts off duct 1:

- The throttle plates, pressure regulators or valves positioned above it can be replaced
- Other components of the control chain such as drives, for example, can be replaced once the valve has been exhausted


Pressure gauge



Plugs into the pressure regulators

Key features

Hole pattern on sub-base to ISO 5599-1



[A] Width 42 mm
[B] Width 52 mm
[C] Width 65 mm
[D] Width 76 mm

Sub-base port identifications

Duct	Function	Description
[14]	Control section	Pilot air supply for pilot valves 12 and 14
[5]	Power section	Exhaust port
[4]	Power section	Working port
[1]	Power section	Working air supply port
[2]	Power section	Working port
[3]	Power section	Exhaust port
[12]	Control section	Exhaust port for pilot air supply

Key features

Pilot air supply

The pneumatic supply ports are located on the right and left end plates and on the supply plates.
The ports differ for the following types of pilot air supply:
- Internal pilot air supply
- External pilot air supply

The port for the external pilot air supply is on the right and left end plates. Internal pilot air supply takes place in the valve itself and the ports for pilot air supply are not provided on the end plates.

Note

If a gradual pressure build-up is required in the system by using a soft-start valve, then external pilot air should be selected so that the pilot pressure is already applied in full at the point of switch-on.

Internal pilot air supply

Internal pilot air supply can be selected if the working pressure is between 2 and 10 bar, 3 and 10 bar, 2 and 16 bar or 3 and 16 bar, depending on the valve.


In this case the pilot air supply is branched from the compressed air supply 1 using an internal connection in the valve.

External pilot air supply

If the supply pressure is less than 2 or 3 bar, you must operate your valve manifold assembly VSVA using external pilot air supply.

The pilot air supply is then supplied via ports 12 and 14 on the end plates.

Using the seals with ducted/unducted pilot exhaust air













[1] Ducted pilot air exhaust
[2] Turning the seal 180°
[3] Unducted pilot air exhaust (as supplied)

Valve manifold assemblies VSVA are delivered with unducted pilot air exhaust. By turning the seal between the valve and manifold block, exhaust air (pilot air) can be diverted into pilot duct 12 and can thus be ducted and silenced (see illustration).

Key features

Pilot air supply via end plates

		Description
End plate left (graphical illustration)		
		Internal pilot air supply • Pilot air supply is branched within the valve from port 1 • Port 12 is not available • Port 14 is not available • Exhaust air via ports 3 and 5 • Pilot exhaust air via port 12
		External pilot air supply • Pilot air supply via ports 12 and 14 • Exhaust air via ports 3 and 5 • Unducted pilot exhaust air
		External pilot air supply, ducted pilot exhaust air • Pilot air supply via port 14 • Exhaust air via ports 3 and 5 • Pilot exhaust air via port 12 • For valves with central plug M12, 3-pin
End plate right (graphical illustration)		
		Internal pilot air supply • Pilot air supply is branched within the valve from port 1 • Port 12 is not available • Port 14 is not available • Exhaust air via ports 3 and 5 • Pilot exhaust air via port 12
		External pilot air supply • Pilot air supply via ports 12 and 14 • Exhaust air via ports 3 and 5 • Unducted pilot exhaust air
		External pilot air supply, ducted pilot exhaust air • Pilot air supply via port 14 • Exhaust air via ports 3 and 5 • Pilot exhaust air via port 12 • For valves with central plug M12, 3-pin


Key features

Creating pressure zones and separating exhaust air




















The valve manifold assembly VSVA offers a number of options for creating pressure zones if different working pressures are required.
Pressure zones are created by isolating the internal supply ducts between the manifold sub-bases by appropriate duct separation.

Compressed air is supplied and exhausted via the end plates and supply plates.
The position of the supply plates and duct separations can be freely selected.

Duct separations are integrated ex-works as per your order.
Duct separations can be distinguished by their coding, even when the valve terminal is assembled.




Creating pressure zones

Separating seal				Description
Coding	Sample image	Coding	Basic representation	
				Duct 1 separated • Different supply pressure for each pressure zone • Supply pressure for each pressure zone can be switched off separately
				Ducts 3 and 5 separated • The valves (for different pressure zones) do not affect each other via the exhaust ducts
				Ducts 12 and 14 separated • Different pilot pressure for each supply zone • Operation with internal and external pilot air supply possible according to pressure zone • Pilot pressure for each pressure zone can be switched off separately
				Ducts 1, 3 and 5 separated • Different supply pressure for each pressure zone • The valves (for different pressure zones) do not affect each other via the exhaust ducts • Supply pressure for each pressure zone can be switched off separately
				Ducts 1, 3, 5, 12 and 14 separated • Different supply pressure for each pressure zone • Supply pressure for each pressure zone can be switched off separately • The valves (for different pressure zones) do not affect each other via the exhaust ducts • Different pilot pressure for each supply zone • Operation with internal and external pilot air supply possible according to pressure zone • Pilot pressure for each pressure zone can be switched off separately

Key features

Examples: Creating pressure zones



[1] Pressure zone separation in ducts 1, 3 and 5. Pressure supply and exhausting via the respective end plate for each of the two pressure zones. Pilot air is supplied jointly via the left end plate.

Potential benefit:
- Two different supply pressures
- The valves do not affect each other via the exhaust ducts

[2] Pressure zone separation in ducts 3 and 5. The pressure for both pressure zones is supplied jointly via the end plates. Each of the two pressure zones is exhausted separately via the respective end plate. Pilot air is supplied jointly via the left end plate.













Potential benefit:
- The valves do not affect each other via the exhaust ducts

[3] Pressure zone separation in duct 1. Pressure supply via the respective end plate for each of the two pressure zones. Both pressure zones are exhausted jointly via the end plates. Pilot air supplied jointly via the left end plate.




Potential benefit:
- Two different supply pressures

Key features






Using 2x 3/2-way valve as 5/4-way valve

Code	Symbol	Table of values	Equivalent circuit symbol	Function
K				• Normally exhausted • The double-acting drive connected to ducts 2 and 4 is unpressurised when the valve is in the normal position and can be moved by an external force • If there is a signal at Y1(14) and Y2(12), there is pressure at ducts 2 and 4
				• Normally closed (by combining valve code K and two check valves) • The pilot-operated check valves connected to ports 2 and 4 are unpressurised when the valve is in the normal position and the pressures in the drive close the check valves so it is leak-tight • The drive remains stationary when the forces are in equilibrium • Leakages can only occur via the drive seals • If there is a signal at Y1(14) and Y2(12), the pressure at ducts 2 and 4 is the same
N				• Normally open • The double-acting drive connected to ducts 2 and 4 is supplied with the same pressure at both ends when the valve is in the normal position and remains stationary when the forces are balanced • If there is a signal at Y1(10) and Y2(10), ducts 2 and 4 are exhausted, the drive is unpressurised and can be moved by an external force
H				• Normally open to duct 2 • The double-acting drive connected to ducts 2 and 4 is supplied with pressure via duct 2 when the valve is in the normal position. Duct 4 is exhausted. When the system is in its initial position, the drive is thus in a clearly defined position, as would also be the case with a 5/2-way single solenoid valve • If there is a signal at Y1(14) and Y2(10), duct 2 is exhausted and there is pressure at duct 4. The drive leaves the initial position • A closed circuit can also be created with this 2x 3/2-way valve by combining it with pilot operated check valves. However, this is then selected by an active signal at Y2(10).





Product range overview

Function		Type	Valve function	Flow rate Valve [l/min]	Operating voltage	→ Page/Internet
Width 42 mm **Working port G1/4**	**Valve with armature tube for solenoid coil MSF**					
		**MFH-5/2**	5/2-way single solenoid valve	1200	12 V DC, 24 V DC, 42 V DC, 24 V AC, 42 V AC, 48 V AC, 110 V AC, 120 V AC, 230 V AC, 240 V AC	30
		JMF	5/2-way double solenoid valve	1200		
		MFH-5/3	5/3-way solenoid valve, mid-position valve	1200		
	Valve with 8 mm armature tube					
		**VSVA-B-T32**	2x 3/2-way single solenoid valve	1400	12 V DC, 24 V DC, 24 V AC, 48 V AC, 110 V AC, 120 V AC, 230 V AC, 240 V AC	45
		VSVA-B-M52	5/2-way single solenoid valve	1800		
		VSVA-B-B52	5/2-way double solenoid valve	1800		
		VSVA-B-D52	5/2-way valve, double solenoid, with dominant signal	1800		
		VSVA-B-P53	5/3-way solenoid valve, mid-position valve	1800		
	Valve with square plug type B to industry standard					
		**VSVA-B-M52...A1**	5/2-way valve, single solenoid	1342	24 V DC	67
		VSVA-B-B52...A1	5/2-way valve, double solenoid	1341		
		VSVA-B-P53...A1	5/3-way valve, mid-position valve	1289		
	Valve with central plug M12, 3-pin					
		**VSVA-B-T22**	2x 2/2-way single solenoid valve	1300	24 V DC	71
		VSVA-B-T32	2x 3/2-way single solenoid valve	1100		
		VSVA-B-M52	5/2-way single solenoid valve	1300		
		VSVA-B-B52	5/2-way double solenoid valve	1300		
		VSVA-B-D52	5/2-way double solenoid valve	1300		
		VSVA-B-TR1-B52	5/2-way double solenoid valve, timer valve	1300		
		VSVA-B-P53	5/3-way solenoid valve, mid-position valve	1300		
	Valve with individual plug M12					
		**MDH-5/2**	5/2-way single solenoid valve	1200	24 V DC, 42 V AC, 110 V AC, 230 V AC	87
		JMD	5/2-way double solenoid valve	1200		
		MDH-5/3	5/3-way solenoid valve, mid-position valve	1200		
	Pneumatic valve					
		**VL-5/2**	5/2-way pneumatic valve, monostable	1200	–	111
		J	5/2-way pneumatic valve, bistable	1200		
		VL-5/3	5/3-way pneumatic valve, mid-position valve	1200		

Product range overview

Function		Type	Valve function	Flow rate Valve [l/min]	Operating voltage	→ Page/Internet
Width 52 mm **Working port G3/8**	**Valve with armature tube for solenoid coil MSF**					
		**MFH-5/2**	5/2-way single solenoid valve	2300	12 V DC, 24 V DC, 42 V DC, 24 V AC, 42 V AC, 48 V AC, 110 V AC, 120 V AC, 230 V AC, 240 V AC	35
		JMF	5/2-way double solenoid valve	2300		
		MFH-5/3	5/3-way solenoid valve, mid-position valve	2300		
	Valve with 8 mm armature tube					
		**VSVA-B-T32**	2x 3/2-way single solenoid valve	2100	12 V DC, 24 V DC, 24 V AC, 48 V AC, 110 V AC, 120 V AC, 230 V AC, 240 V AC	56
		VSVA-B-M52	5/2-way single solenoid valve	4100		
		VSVA-B-B52	5/2-way double solenoid valve	4000		
		VSVA-B-D52	5/2-way valve, double solenoid, with dominant signal	4000		
		VSVA-B-P53	5/3-way solenoid valve, mid-position valve	3700		
	Valve with central plug M12, 3-pin					
		**VSVA-B-T22**	2x 2/2-way single solenoid valve	2800	24 V DC	77
		VSVA-B-T32	2x 3/2-way single solenoid valve	2200		
		VSVA-B-M52	5/2-way single solenoid valve	2800		
		VSVA-B-B52	5/2-way double solenoid valve	2800		
		VSVA-B-D52	5/2-way double solenoid valve	2800		
		VSVA-B-P53	5/3-way solenoid valve, mid-position valve	2700		
	Valve with individual plug M12					
		**MDH-5/2**	5/2-way single solenoid valve	2300	24 V DC, 42 V AC, 110 V AC, 230 V AC	92
		JMD	5/2-way double solenoid valve	2300		
		MDH-5/3	5/3-way solenoid valve, mid-position valve	2300		
	Pneumatic valve					
		**VL-5/2**	5/2-way pneumatic valve, monostable	2300	–	117
		J	5/2-way pneumatic valve, bistable	2300		
		VL-5/3	5/3-way pneumatic valve, mid-position valve	2300		

Product range overview

Function		Type	Valve function	Flow rate Valve [l/min]	Operating voltage	→ Page/Internet
Width 65 mm	**Valve with armature tube for solenoid coil MSF**					
Working port G1/2		**MFH-5/2**	5/2-way single solenoid valve	4500	12 V DC, 24 V DC, 42 V DC, 24 V AC, 42 V AC, 48 V AC, 110 V AC, 120 V AC, 230 V AC, 240 V AC	40
		JMF	5/2-way double solenoid valve	4500		
		MFH-5/3	5/3-way solenoid valve, mid-position valve	4000		
	Valve with central plug M12, 4-pin					
		**MEBH-5/2**	5/2-way single solenoid valve	4500	24 V DC	82
		JMEB	5/2-way double solenoid valve	4500		
		MEBH-5/3	5/3-way solenoid valve, mid-position valve	4000		
	Valve with individual plug M12					
		**MDH-5/2**	5/2-way single solenoid valve	4500	24 V DC, 42 V AC, 110 V AC, 230 V AC	97
		JMD	5/2-way double solenoid valve	4500		
		MDH-5/3	5/3-way solenoid valve, mid-position valve	4000		
	Pneumatic valve					
		**VL-5/2**	5/2-way pneumatic valve, monostable	4500	–	123
		J	5/2-way pneumatic valve, bistable	4500		
		VL-5/3	5/3-way pneumatic valve, mid-position valve	4100		
Width 76 mm	**Valve with individual plug M12**					
Working port G3/4		**MDH-5/2**	5/2-way single solenoid valve	6000	24 V DC, 42 V AC, 110 V AC, 230 V AC	102
		JMD	5/2-way double solenoid valve	6000		
		MDH-5/3	5/3-way solenoid valve, mid-position valve	4800		
	Pneumatic valve					
		**VL-5/2**	5/2-way pneumatic valve, monostable	6000	–	127
		J	5/2-way pneumatic valve, bistable	6000		
		VL-5/3	5/3-way pneumatic valve, mid-position valve	4800		

Type code for valves with round plug

001	Series	
VSVA	Standards-based valve VSVA	

002	Directional control valve type	
B	Sub-base valve	

003	Valve function	
T22C	2x2/2-way valve, normally closed	
T32U	2x3/2-way valve, normally open	
T32F	2x3/2-way valve, normally open, reversible	
T32C	2x3/2-way valve, normally closed	
T32N	2x3/2-way valve, normally closed, reversible	
T32H	2x3/2-way valve, 1x normally closed, 1x normally open	
T32W	2x3/2-way valve, 1x normally closed, 1x normally open, reversible	
B52	5/2-way valve, double solenoid/bistable	
M52	5/2-way valve, single solenoid/monostable	
D52	5/2-way valve, double solenoid/bistable, dominant signal	
P53U	5/3-way valve, mid-position pressurised	
P53E	5/3-way valve, mid-position exhausted|	
P53C	5/3-way valve, mid-position closed	

004	Reset method for monostable/single solenoid valves	
	None	
A	Pneumatic spring	
M	Mechanical spring	

005	Pilot air	
	Internal	
Z	External	

006	Manual override	
D	Non-detenting, detenting	
H	Non-detenting	

007	Pneumatic connection	
A2	18 mm (02) ISO 15407-1/-2	
A1	26 mm (01) ISO 15407-1/-2	
D1	42 mm (1) ISO 5599-1/-2	
D2	52 mm (2) ISO 5599-1/-2	

008	Nominal operating voltage	
1	24 V DC	

009	Electrical connection	
R2	Central connector M8	
R5	Central plug M12	

010	Display	
L	LED	

Type codes for valves with square plug type B to industry standard

001	Series	
VSVA	Standards-based valve VSVA	

002	Directional control valve type	
B	Sub-base valve	

003	Design principle	
	Piston spool	
K	Piston spool with sealing ring	

004	Valve function	
B52	5/2-way valve, double solenoid/bistable	
D52	5/2-way valve, double solenoid/bistable, dominant signal	
M52	5/2-way valve, single solenoid/monostable	
P53C	5/3-way valve, mid-position closed	
P53E	5/3-way valve, mid-position exhausted|	
P53U	5/3-way valve, mid-position pressurised	
T22C	2x2/2-way valve, normally closed	
T32C	2x3/2-way valve, normally closed	
T32F	2x3/2-way valve, normally open, reversible	
T32H	2x3/2-way valve, 1x normally closed, 1x normally open	
T32N	2x3/2-way valve, normally closed, reversible	
T32U	2x3/2-way valve, normally open	
T32W	2x3/2-way valve, 1x normally closed, 1x normally open, reversible	

005	Reset method for monostable/single solenoid valves	
	None	
A	Pneumatic spring	
M	Mechanical spring	

006	Pilot air	
	Internal	
Z	External	

007	Manual override	
	None	
D	Non-detenting, detenting	
H	Non-detenting	

008	Pneumatic connection	
A1	26 mm (01) ISO 15407-1/-2	
A2	18 mm (02) ISO 15407-1/-2	
D1	42 mm (1) ISO 5599-1/-2	

009	Nominal operating voltage	
	None	
1	24 V DC	
1A	24 V AC/50-60 Hz	
2A	110 V AC/50-60 Hz	
3A	230 V AC/50-60 Hz	
5	12 V DC	

010	Electrical connection	
B2	Connection pattern type B, industry standard	
C1	Plug pattern type C, to EN 175301-803	
P1	For pilot valves with CNOMO interface size 15 mm to ISO 15218	
R3	Individual plug M12, to EN 61076-2-101	

011	Position sensing	
	None	
APC	Proximity sensor, PNP with open cable ends	
APP	Proximity sensor, PNP with M8 plug	
APX	Proximity sensor, PNP with cable and plug M12	

Type code for valves with armature tube 8 m

001	Series	
VSVA	Standards-based valve VSVA	

002	Directional control valve type	
B	Sub-base valve	

003	Sealing principle	
	Soft seal	

004	Valve function	
B52	5/2-way valve, double solenoid/bistable	
D52	5/2-way valve, double solenoid/bistable, dominant signal	
M52	5/2-way valve, single solenoid/monostable	
P53C	5/3-way valve, mid-position closed	
P53E	5/3-way valve, mid-position exhausted	
P53F	5/3-way valve, mid-position port 2 pressurised, port 4 closed	
P53U	5/3-way valve, mid-position pressurised	
T22C	2x2/2-way valve, normally closed	
T32C	2x3/2-way valve, normally closed	
T32H	2x3/2-way valve, 1x normally closed, 1x normally open	
T32U	2x3/2-way valve, normally open	

005	Additional characteristics	
	None	
D	Switching position 14 detenting, 12 mechanical spring	
P	Switching position 12 detenting, 14 mechanical spring	
V	1x vacuum operation	

006	Reset method for monostable/single solenoid valves	
	None	
A	Pneumatic spring	
M	Mechanical spring	

007	Pilot air	
	Internal	
Z	External	

008	Manual override	
	None	
D	Non-detenting, detenting	
H	Non-detenting	
T	Non-detenting, detenting with accessories	

009	Pneumatic connection	
D1	42 mm (1) ISO 5599-1/-2	
D2	52 mm (2) ISO 5599-1/-2	

010	Valve pilot control interface	
F8	With armature tube 8 mm, long	

011	Nominal operating voltage	
	None	
1	24 V DC	
1A	24 V AC/50-60 Hz	
3W	230 V AC/240 V AC/50-60 Hz	
5	12 V DC	
7	48 V DC	
7A	48 V AC/50-60 Hz	
16B	120 V AC/60 Hz and 110V AC/50-60 Hz	

012	Electrical connection	
	None	
A1	Plug pattern type A, to EN 175301-803	
B2	Connection pattern type B, industry standard	
C1	Plug pattern type C, to EN 175301-803	
R3	Individual plug M12, to EN 61076-2-101	
R4	Individual connector M12, DESINA assignment	


013	Display	
	None	
L	LED	

014	EX certification EU	
	None	
EX2	II 3GD	

Peripherals overview

Valve on individual sub-base

Solenoid valve with solenoid coil MSF




Individual components

		Type	Brief description	→ Page/Internet
[1]	Solenoid coil	MSF...	Solenoid coil	163
[2]	Solenoid valve	MFH-...	Solenoid valve with solenoid coil, hole pattern to ISO 5599-1, corresponding solenoid coils a page 164	30
[3]	Connecting plate	VABS-S1-...	Pneumatic ports on the side	130
	Individual sub-base	NAS-...	Pneumatic ports on the side	130
		NAU-...	Pneumatic ports underneath	133
[4]	Silencer	U-...	For fitting in exhaust ports	silencer
[5]	Push-in fitting	QS-...	For connecting tubing with standard O.D.	qs
[6]	Illuminating seal	MF-LD	For displaying the signal status	164
[7]	Plug socket	MSSD-...	For self-assembly	164
[8]	Connecting cable	KMF-..., NEBV-...	With LED or without LED	164
[9]	Manual override	AHB-...	Tool for detenting manual override	166

Peripherals overview

Valve on individual sub-base
Solenoid valve with 8 mm armature tube




Individual components

		Type	Brief description	→ Page/Internet
[1]	Solenoid coil	VACF	Electrical connection type A, B or C or M12	163
[2]	Solenoid valve	VSVA-...F8...	Solenoid valve with 8 mm armature tube, hole pattern to ISO 5599-1	45
[3]	Connecting plate	VABS-S1-...	Pneumatic ports on the side	130
	Individual sub-base	NAS-...	Pneumatic ports on the side	130
		NAU-...	Pneumatic ports underneath	133
[4]	Silencer	U-...	For fitting in exhaust ports	silencer
[5]	Push-in fitting	QS-...	For connecting tubing with standard O.D.	qs
[6]	Illuminating seal	M...	For displaying the signal status	165
[7]	Plug socket	MSSD...	For self-assembly	165
[8]	Connecting cable	NEBV-...	–	165

Peripherals overview

Valve on individual sub-base

Solenoid valve with square plug type B to industry standard




Individual components

		Type	Brief description	→ Page/Internet
[1]	Solenoid valve	VSVA-BK...	Solenoid valve with square plug type B to industry standard, hole pattern to ISO 5599-1	67
[2]	Cover cap	VAMC-...	For manual override non-detenting or covered	166
[3]	Illuminating seal	MF-LD	For displaying the signal status	164
[4]	Plug socket	MSSD-F-...	For self-assembly	164
[5]	Connecting cable	KMF-...	–	164
[6]	Connecting plate	VABS-S1-...	Pneumatic ports on the side	130
	Individual sub-base	NAS-...	Pneumatic ports on the side	130
		NAU-...	Pneumatic ports underneath	133
[7]	Silencer	U-...	For fitting in exhaust ports	silencer
[8]	Push-in fitting	QS-...	For connecting tubing with standard O.D.	qs

Peripherals overview

Valve on individual sub-base

Solenoid valve with central plug M12, 3-pin




Peripherals overview

Individual components

		Type	Brief description	→ Page/Internet
[1]	Connecting plate	VABS-S1-...	Pneumatic ports on the side	130
	Individual sub-base	NAS-...	Pneumatic ports on the side	130
		NAU-...	Pneumatic ports underneath	133
[2]	Solenoid valve	VSVA-B...	Solenoid valve with central plug M12, 3-pin, hole pattern to ISO 5599-1	71
[3]	Push-in fitting	QS-...	For connecting tubing with standard O.D.	qs
[4]				
[5]	Connecting cable	NEBA-...	–	166
[6]				
[7]	Silencer	U-...	For fitting in exhaust ports	silencer
[8]	Plug socket	NECB-...	For self-assembly	166

Peripherals overview

Accessories




Peripherals overview

Individual components

		Type	Brief description	→ Page/Internet
[1]	Solenoid valve	MFH-...	Solenoid valve with solenoid coil, hole pattern to ISO 5599-1, corresponding solenoid coils a page 164	30
		VSVA-B...	Solenoid valve with 8 mm armature tube	45
		VSVA-BK...	Solenoid valve with square plug type B to industry standard, hole pattern to ISO 5599-1	67
		VSVA-B...	Solenoid valve with central plug M12, 3-pin, hole pattern to ISO 5599-1	71
[2]	Cover cap	VAMC-...	For manual override non-detenting or covered	166
[3]	Connecting cable	KMF-1...	With LED	164
[4]	Illuminating seal	MF-LD	For displaying the signal status	164
[5]	Socket	MSSD-F	Plug pattern type B, industry standard	164
[6]	Connecting cable	NEBA-...	Angled socket, M12x1, 5-pin,	166
[7]	Connecting cable	NEBA-...	Straight socket, M12x1, 5-pin	166
[8]	Socket	NECB-...	For self-assembly	166
[9]	Pressure gauge	PAGN-...	With push-in connector	166
[10]	Illuminating seal	MC-LD	For electrical connection type A according to EN 175301-803	165
		MF-LD	For electrical connection type B	165
[11]	Socket	MSSD-C	For electrical connection type A according to EN 175301-803	165
		MSSD-F	For electrical connection type B	165
		MSSD-EB	For electrical connection type C according to EN 175301-803	165
[12]	Connecting cable	KMC-1...	For electrical connection type A according to EN 175301-803	165
		NEBV-A1W3		
		KMF-1	For electrical connection type B	165
		NEBV-B2W3		
		NEBV-C1SW	For electrical connection type C according to EN 175301-803	165
[13]	Connecting cable	KMF-1	For solenoid coil MSF	164
		NEBV-B2W3		
		KMC-1...	For solenoid coil MSN1 and MD	164
		NEBV-A1W3		
[14]	Illuminating seal	MC-LD	For electrical connection type A according to EN 175301-803	164
		MF-LD	For electrical connection type B	
[15]	Socket	MSSD-C	For electrical connection type A according to EN 175301-803	164
		MSSD-F	For electrical connection type B	
		MSSD-EB	For electrical connection type C according to EN 175301-803	
[16]	Push-in fitting	QS-...	For connecting tubing with standard O.D.	qs
[17]	Silencer	U-...	For fitting in exhaust ports	silencer
[18]	Blanking plug	B-...	For sealing ports that are not required	b

System overview

Manifold assembly




System overview

Individual components

		Type	Brief description	→ Page/Internet
[1]	Solenoid valve	VSVA-BK...	Solenoid valve with square plug type B to industry standard	67
[2]	Solenoid valve	VSVA-...	With central plug M12, 3-pin	71
		MEBH-...	With central plug M12, 4-pin	82
		JMEBH-...	With central plug M12, 4-pin	82
		JMEBDH-...	With central plug M12, 4-pin	82
[3]	Solenoid valve	VSVA-...F8...	Solenoid valve with 8 mm armature tube	45
[4]	Solenoid valve	MFH-...	With armature tube for solenoid coil MSF	30
		JMFH-...	With armature tube for solenoid coil MSF	30
		JMFDH-...	With armature tube for solenoid coil MSF	30
		MDH-...	With solenoid coil MD with round plug M12x1	87
		JMDH-...	With solenoid coil MD with round plug M12x1	87
		JMDDH-...	With solenoid coil MD with round plug M12x1	87
[5]	Regulator plate	LR-ZP-...	Pressure regulator for manually setting a particular pressure in the regulated port upstream or downstream of the valve	157
[6]		VABF-S1-...-R...	Pressure regulator for manually setting a particular pressure in the regulated port upstream or downstream of the valve	157
[7]				
[8]	Vertical pressure shut-off plate	VABF-S1-...-L1D1-C	For blocking duct 1 and duct 14 upstream of a valve	155
[9]	Vertical supply plate	VABF-S1-...-P1A3-G38	Alternative compressed air supply for port 1 of the mounted valve	153
[10]	Throttle plate	VABF-S1-...-F1B1-C	Restricts the flow of exhaust air in ducts 3 and 5	150
		GRO-ZP-...	Restricts the flow of exhaust air in ducts 3 and 5	150
[11]	Cover plate	NDV-...	For sealing unused manifold sub-bases	145
[12]	End plate	VABE-S1-...	With ports for air supply 1 and exhausts 3 and 5 and pilot air supply 12 and 14	142
[13]	Manifold sub-base	VABV-S1-...	With ports 2 and 4 underneath	135
[14]	Supply plate	VABF-S1-1-...	With ports for air supply 1 and exhausts 3 and 5	137
[15]	Duct separation	VABD-S1-1-...	For sealing ducts 1, 3, 5, 12 and 14 between end plate and manifold sub-base, e.g. to create pressure zones	146

System overview

Manifold assembly




System overview

Individual components

		Type	Brief description	→ Page/Internet
[1]	Solenoid valve	VSVA-BK...	Solenoid valve with square plug type B to industry standard	67
[2]	Solenoid valve	VSVA-...	With central plug M12, 3-pin	71
		MEBH-...	With central plug M12, 4-pin	82
		JMEBH-...	With central plug M12, 4-pin	82
		JMEBDH-...	With central plug M12, 4-pin	82
[3]	Solenoid valve	VSVA-...F8...	With 8 mm armature tube	45
[4]	Solenoid valve	MFH-...	With armature tube for solenoid coil MSF	30
		JMFH-...	With armature tube for solenoid coil MSF	30
		JMFDH-...	With armature tube for solenoid coil MSF	30
		MDH-...	With solenoid coil MD with round plug M12x1	87
		JMDH-...	With solenoid coil MD with round plug M12x1	87
		JMDDH-...	With solenoid coil MD with round plug M12x1	87
[5]	Regulator plate	LR-ZP-...	Pressure regulator for manually setting a particular pressure in the regulated port upstream or downstream of the valve	157
[6]		VABF-S1-...-R...	Pressure regulator for manually setting a particular pressure in the regulated port upstream or downstream of the valve	157
[7]				
[8]	Vertical pressure shut-off plate	VABF-S1-...-L1D1-C	For blocking duct 1 and duct 14 upstream of a valve	155
[9]	Vertical supply plate	VABF-S1-...-P1A3-G38	Alternative compressed air supply for port 1 of the mounted valve	153
[10]	Throttle plate	VABF-S1-...-F1B1-C	Restricts the flow of exhaust air in ducts 3 and 5	150
		GRO-ZP-...	Restricts the flow of exhaust air in ducts 3 and 5	150
[11]	Cover plate	NDV-...	For sealing unused manifold sub-bases	145
[12]	End plate kit	NEV-...	With ports for air supply 1 and exhausts 3 and 5	141
[13]	Manifold sub-base	NAV-...	With ports 2 and 4 underneath	135
[14]	Isolating disc	NSC-...	For sealing ducts 1, 3, 5 between end plate and manifold sub-base, e.g. to create pressure zones	145

Datasheet – Width 42 mm

- Flow rate
1200 l/min



General technical data				
Type			MFH- ... -C, JMF- ... -C	MFH- ... -EX, JMF- ... -EX
Design			Piston spool	Piston spool
Sealing principle			Soft	Soft
Actuation type			Electrical	Electrical
Type of control			Piloted	Piloted
Flow direction	With external pilot air supply		Reversible	Reversible
	With internal pilot air supply		Not reversible	Not reversible
Suitable for vacuum	With external pilot air supply		Yes	Yes
	With internal pilot air supply		No	No
Exhaust air function			Can be throttled	Can be throttled
Manual override			Non-detenting, detenting via accessory	Non-detenting, detenting via accessory
Type of mounting			On sub-base, with through-hole	
Mounting position			Any	Any
Nominal width		[mm]	8	8
Overlap			Positive overlap	Positive overlap
Width		[mm]	42	42
Grid dimension		[mm]	43	43
Noise level		[dB (A)]	85	85
Conforms to standard			ISO 5599-1	ISO 5599-1

Pneumatic ports				
		5/2-way valve	5/2-way valve, double solenoid	5/3-way valve
Pneumatic connection	1, 2, 4, 3, 5	Sub-base size 1 to ISO 5599-1		
	12/14	Sub-base size 1 to ISO 5599-1		
Pilot exhaust air port	82	–	M5	M5
	84	M5	M5	M5

Flow rates				
Valve function		5/2-way valve	5/2-way valve, double solenoid	5/3-way valve
Standard nominal flow rate	[l/min]	1200		

Datasheet – Width 42 mm

Switching times [ms]

		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
5/2-way valve, single solenoid	MFH-5/2-...	23	35	–	–
	MFH-5/2-D-1-FR-...	16	45	–	–
5/2-way valve, double solenoid	JMFH-...	–	–	16	–
	JMFDH-...	–	–	16	13
5/3-way valve	MFH-5/3G-D-1-C	18	35	–	–
	MFH-5/3G-D-1-C-EX	18	35	–	–
	MFH-5/3G-D-1-S-C	18	36	–	–
	MFH-5/3G-D-1-S-C-EX	18	36	–	–
	MFH-5/3E-D-1-C	18	36	–	–
	MFH-5/3E-D-1-C-EX	18	36	–	–
	MFH-5/3E-D-1-S-C	18	36	–	–
	MFH-5/3E-D-1-S-C-EX	18	36	–	–
	MFH-5/3B-D-1-C	18	36	–	–
	MFH-5/3B-D-1-C-EX	18	36	–	–
	MFH-5/3B-D-1-S-C	18	36	–	–
	MFH-5/3B-D-1-S-C-EX	18	36	–	–

ATEX

Type		MFH- ... -EX, JMFH- ... -EX, JMFDH- ... -EX
ATEX category for gas		II 2G
Type of ignition protection for gas		Ex h IIC T4 Gb
ATEX category for dust		II 2D
Type of (ignition) protection for dust		Ex h IIIC T105°C Db
Explosion-proof ambient temperature	[°C]	–5 <= Ta <= +40
Explosion protection certification outside EU		EPL Db (GB)
		EPL Gb (GB)
CE marking (see declaration of conformity)[1]		To EU Explosion Protection Directive (ATEX)
UKCA marking (see declaration of conformity)[1]		To UK explosion regulations

1) More information www.festo.com/catalogue/... → Support/Downloads.

Operating and environmental conditions

Reset method			Pneumatic spring	Mechanical spring
Operating medium			Compressed air to ISO 8573-1:2010 [7:4:4]	
Pilot medium			Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on the operating/pilot medium			Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure	Internal pilot air supply	[bar]	2 ... 10	3 ... 10
	External pilot air supply	[bar]	–0.9 ... +16	–0.9 ... +16
Pilot pressure		[bar]	2 ... 10	3 ... 10
Ambient temperature		[°C]	–5 ... +40	
Temperature of medium	MFH- ... -C, JMF- ... -C	[°C]	–10 ... +60	
	MFH- ... -EX, JMF- ... -EX	[°C]	–5 ... +40	

Safety characteristics


Max. positive test pulse with 0 signal	[µs]	2200
Max. negative test pulse with logic 1	[µs]	3700
Shock resistance		Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Vibration resistant		Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6

Datasheet – Width 42 mm

Electrical data	
Electrical connection	Via F coil, to be ordered separately
Degree of protection to EN 60529	IP65

Materials	
Housing	Die-cast aluminium
Seals	HNBR, NBR
Note on materials	RoHs-compliant
LABS (PWIS) conformity	VDMA24364-B1/B2-L

Dimensions – 5/2-way valves, single solenoid Download CAD data ➔ www.festo.com




[1] Manual override [2] Captive retaining screws [3] Slot for inscription label

Type	B1	B2	B3	B4	D1	D2	H1	H2	H3	H4	H5	H6	L1	L2	L3	L4	L5	L6
MFH-5/2- ...	42	28	6	30	M5	M5	100	70.3	38	9	46.5	13.5	115	87.6	43.8	36	18	89
MFH-5/2- ... -FR- ...													125.6	98				

Datasheet – Width 42 mm

Dimensions – 5/2-way valves, double solenoid, 5/3-way valves

Download CAD data ➔ www.festo.com



[1] Manual override














[2] Captive retaining screws

[3] Slot for inscription label

Type	B1	B2	B3	B4	D1	D2	H1	H2	H3	H4	H5	H6	L1	L2	L3	L4	L5	L6
JMFH-5/2- ...	42	28	6	30	M5	M5	100	70.3	38	9	–	13.5	142.6	87.6	43.8	36	18	89
JMFDH-5/2- ...														87.6	43.8			
MFH-5/3...														108.4	54.2			

Ordering data – Width 42 mm


Ordering data – Valves with armature tube for solenoid coil MSF1)

Circuit symbol	Description	Pilot air supply	Weight [g]	ISO code		Part no.	Type
5/2-way valve, single solenoid							
	Pneumatic spring return	Internal	390	151	–	**150981**	**MFH-5/2-D-1-C**
					ATEX category a page 31	**535954**	**MFH-5/2-D-1-C-EX**
	Pneumatic spring return	External	390	164	–	**152562**	**MFH-5/2-D-1-S-C**
					ATEX category a page 31	**535957**	**MFH-5/2-D-1-S-C-EX**
	Mechanical spring return	Internal	390	152	–	**151016**	**MFH-5/2-D-1-FR-C**
					ATEX category a page 31	**535960**	**MFH-5/2-D-1-FR-C-EX**
	Mechanical spring return	External	390	169	–	**188510**	**MFH-5/2-D-1-FR-S-C**
5/2-way valve, double solenoid							
	–	Internal	490	155	–	**150980**	**JMFH-5/2-D-1-C**
					ATEX category a page 31	**535963**	**JMFH-5/2-D-1-C-EX**
	–	External	490	169	–	**152563**	**JMFH-5/2-D-1-S-C**
					ATEX category a page 31	**535966**	**JMFH-5/2-D-1-S-C-EX**
	With dominant signal at 14	Internal	490	169	–	**151019**	**JMFDH-5/2-D-1-C**
					ATEX category a page 31	**536071**	**JMFDH-5/2-D-1-C-EX**
5/3-way valve							
	Normally closed, Mechanical spring return	Internal	520	156	–	**150982**	**MFH-5/3G-D-1-C**
					ATEX category a page 31	**535969**	**MFH-5/3G-D-1-C-EX**
	Normally closed, Mechanical spring return	External	520	169	–	**152564**	**MFH-5/3G-D-1-S-C**
					ATEX category a page 31	**535972**	**MFH-5/3G-D-1-S-C-EX**
	Normally exhausted, Mechanical spring return	Internal	520	157	–	**150983**	**MFH-5/3E-D-1-C**
					ATEX category a page 31	**535975**	**MFH-5/3E-D-1-C-EX**
	Normally exhausted, Mechanical spring return	External	520	169	–	**152565**	**MFH-5/3E-D-1-S-C**
					ATEX category a page 31	**535978**	**MFH-5/3E-D-1-S-C-EX**
	Normally open, Mechanical spring return	Internal	520	158	–	**150984**	**MFH-5/3B-D-1-C**
					ATEX category a page 31	**535981**	**MFH-5/3B-D-1-C-EX**
	Normally open, Mechanical spring return	External	520	169	–	**152566**	**MFH-5/3B-D-1-S-C**
					ATEX category a page 31	**535984**	**MFH-5/3B-D-1-S-C-EX**

1) Solenoid coils a page 163

Datasheet – Width 52 mm

- Flow rate
2300 l/min



General technical data				
Type			MFH- ... -C, JMF- ... -C	MFH- ... -EX, JMF- ... -EX
Design			Piston spool	Piston spool
Sealing principle			Soft	Soft
Actuation type			Electrical	Electrical
Type of control			Piloted	Piloted
Flow direction	With external pilot air supply		Reversible	Reversible
	With internal pilot air supply		Not reversible	Not reversible
Suitable for vacuum	With external pilot air supply		Yes	Yes
	With internal pilot air supply		No	No
Exhaust air function			Can be throttled	Can be throttled
Manual override			Non-detenting, detenting via accessory	Non-detenting, detenting via accessory
Type of mounting			On sub-base, with through-hole and screw	
Mounting position			Any	Any
Nominal width		[mm]	11.5	11.5
Overlap			Positive overlap	Positive overlap
Width		[mm]	52	52
Grid dimension		[mm]	56	56
Noise level		[dB (A)]	85	85
Conforms to standard			ISO 5599-1	ISO 5599-1

Pneumatic ports with external pilot air supply				
		5/2-way valve	5/2-way valve, double solenoid	5/3-way valve
Pneumatic connection	1, 2, 4, 3, 5	Sub-base size 2 to ISO 5599-1		
	12	–	Sub-base size 2 to ISO 5599-1	
	14	Sub-base size 2 to ISO 5599-1		
Pilot exhaust air port	82	–	M5	M5
	84	M5	M5	M5

Pneumatic ports with internal pilot air supply				
		5/2-way valve	5/2-way valve, double solenoid	5/3-way valve
Pneumatic connection	1, 2, 4, 3, 5	Sub-base size 2 to ISO 5599-1		
	12	–		
	14	–		
Pilot exhaust air port	82	–	M5	M5
	84	M5	M5	M5

Flow rates				
Valve function		5/2-way valve	5/2-way valve, double solenoid	5/3-way valve
Standard nominal flow rate	[l/min]	2300		

Datasheet – Width 52 mm

Switching times [ms]					
		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
5/2-way valve, single solenoid	MFH-5/2-...	48	71	–	–
	MFH-5/2-D-2-FR-...	27	73	–	–
5/2-way valve, double solenoid	JMFH-...	–	–	18	–
	JMFDH-...	–	–	18	18
5/3-way valve	MFH-5/3G-...	33	63	–	–
	MFH-5/3E-...	35	67	–	–
	MFH-5/3B-...	35	69	–	–

ATEX		
Type		MFH- ... -EX, JMFH- ... -EX, JMFDH- ... -EX
ATEX category for gas		II 2G
Type of ignition protection for gas		Ex h IIC T4 Gb
ATEX category for dust		II 2D
Type of (ignition) protection for dust		Ex h IIIC T105°C Db
Explosion-proof ambient temperature	[°C]	–5 <= Ta <= +40
Explosion protection certification outside EU		EPL Db (GB)
		EPL Gb (GB)
CE marking (see declaration of conformity)[1)]		To EU Explosion Protection Directive (ATEX)
UKCA marking (see declaration of conformity) 1)		To UK explosion regulations

1) More information www.festo.com/catalogue/... ➔ Support/Downloads.

Operating and environmental conditions				
Reset method			Pneumatic spring	Mechanical spring
Operating medium			Compressed air to ISO 8573-1:2010 [7:4:4]	
Pilot medium			Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on the operating/pilot medium			Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure	Internal pilot air supply	[MPa]	0.2 ... 1	0.3 ... 1
		[bar]	2 ... 10	3 ... 10
	External pilot air supply	[MPa]	–0.09 ... +1.6	–0.09 ... +1.6
		[bar]	–0.9 ... +16	–0.9 ... +16
Pilot pressure		[bar]	2 ... 10	3 ... 10
Ambient temperature		[°C]	–5 ... +40	
Temperature of medium		[°C]	–10 ... +60	

Safety characteristics		
Max. positive test pulse with 0 signal	[µs]	2200
Max. negative test pulse with logic 1	[µs]	3700
Shock resistance		Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Vibration resistant		Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6


Electrical data	
Electrical connection	Via F coil, to be ordered separately
Degree of protection to EN 60529	IP65

Materials	
Housing	Die-cast aluminium
Seals	HNBR, NBR
Note on materials	RoHs-compliant
LABS (PWIS) conformity	VDMA24364-B1/B2-L

Datasheet – Width 52 mm

Dimensions – 5/2-way valves, single solenoid

Download CAD data ➔ www.festo.com



[1] Manual override

[2] Captive retaining screws


[3] Slot for inscription label

Type	B1	B2	B3	B4	D1	D2	H1	H2	H3	H4	H5	H6	L1	L2	L3	L4	L5	L6
MFH-5/2- ...	54	38	9	30	M6	M5	110	80.3	48	9.5	56.5	13.5	142	123.4	61.7	48	24	98
MFH-5/2- ... -FR- ...													159.4	140.7				

Datasheet – Width 52 mm

Dimensions – 5/2-way valves, double solenoid, 5/3-way valves

Download CAD data ➔ www.festo.com



[1] Manual override













[2] Captive retaining screws

[3] Slot for inscription label

Type	B1	B2	B3	B4	D1	D2	H1	H2	H3	H4	H5	H6	L1	L2	L3	L4	L5	L6
JMFH-5/2- ...	54	38	9	30	M6	M5	110	80.3	48	9.5	–	13.5	160.4	123.4	61.7	48	24	97
JMFDH-5/2- ...													160.4	123.4	61.7			97
MFH-5/3...													160	158	79			98

Ordering data – Width 52 mm


Ordering data – Valves with armature tube for solenoid coil MSF1)

Circuit symbol	Description	Pilot air supply	Weight [g]	ISO code		Part no.	Type
5/2-way valve, single solenoid							
	Pneumatic spring return	Internal	650	251	–	**151851**	**MFH-5/2-D-2-C**
					ATEX category a page 36	**535955**	**MFH-5/2-D-2-C-EX**
	Pneumatic spring return	External	650	264	–	**151022**	**MFH-5/2-D-2-S-C**
					ATEX category a page 36	**535958**	**MFH-5/2-D-2-S-C-EX**
	Mechanical spring return	Internal	650	252	–	**151709**	**MFH-5/2-D-2-FR-C**
					ATEX category a page 36	**535961**	**MFH-5/2-D-2-FR-C-EX**
5/2-way valve, double solenoid							
	–	Internal	820	255	–	**151852**	**JMFH-5/2-D-2-C**
					ATEX category a page 36	**535964**	**JMFH-5/2-D-2-C-EX**
	–	External	820	269	–	**151023**	**JMFH-5/2-D-2-S-C**
					ATEX category a page 36	**535967**	**JMFH-5/2-D-2-S-C-EX**
	With dominant signal at 14	Internal	820	269	–	**151853**	**JMFDH-5/2-D-2-C**
					ATEX category a page 36	**536072**	**JMFDH-5/2-D-2-C-EX**
5/3-way valve							
	Normally closed, Mechanical spring return	Internal	820	256	–	**151854**	**MFH-5/3G-D-2-C**
					ATEX category a page 36	**535970**	**MFH-5/3G-D-2-C-EX**
	Normally closed, Mechanical spring return	External	820	269	–	**151024**	**MFH-5/3G-D-2-S-C**
					ATEX category a page 36	**535973**	**MFH-5/3G-D-2-S-C-EX**
	Normally exhausted, Mechanical spring return	Internal	820	257	–	**151855**	**MFH-5/3E-D-2-C**
					ATEX category a page 36	**535976**	**MFH-5/3E-D-2-C-EX**
	Normally exhausted, Mechanical spring return	External	820	269	–	**151025**	**MFH-5/3E-D-2-S-C**
					ATEX category a page 36	**535979**	**MFH-5/3E-D-2-S-C-EX**
	Normally open, Mechanical spring return	Internal	820	258	–	**151856**	**MFH-5/3B-D-2-C**
					ATEX category a page 36	**535982**	**MFH-5/3B-D-2-C-EX**
	Normally open, Mechanical spring return	External	820	269	–	**151026**	**MFH-5/3B-D-2-S-C**
					ATEX category a page 36	**535985**	**MFH-5/3B-D-2-S-C-EX**

1) Solenoid coils a page 163

Datasheet – Width 65 mm

- - Flow rate
Up to 4600 l/min



General technical data			
Type			
Design			Piston spool
Sealing principle			Soft
Actuation type			Electrical
Type of control			Piloted
Flow direction	With external pilot air supply		Reversible
	With internal pilot air supply		Not reversible
Suitable for vacuum	External pilot air supply		Yes
	External pilot air supply		No
Exhaust air function			Can be throttled
Manual override			Non-detenting, detenting via accessory
Type of mounting			On sub-base, with through-hole and screw
Mounting position			Any
Nominal width		[mm]	14.5
Overlap			Positive overlap
Width		[mm]	65
Grid dimension		[mm]	71
Noise level		[dB (A)]	85
Conforms to standard			ISO 5599-1

Pneumatic ports with external pilot air supply				
		5/2-way valve	5/2-way valve, double solenoid	5/3-way valve
Pneumatic connection	1, 2, 4, 3, 5	Sub-base size 3 to ISO 5599-1		
	12	–	Sub-base size 3 to ISO 5599-1	
	14	Sub-base size 3 to ISO 5599-1		
Pilot exhaust air port	82	–	M5	M5
	84	M5	M5	M5

Pneumatic ports with internal pilot air supply				
		5/2-way valve	5/2-way valve, double solenoid	5/3-way valve
Pneumatic connection	1, 2, 4, 3, 5	Sub-base size 3 to ISO 5599-1		
	12	–		
	14	–		
Pilot exhaust air port	82	–	M5	M5
	84	M5	M5	M5

Datasheet – Width 65 mm

Flow rates						
Valve function			5/2-way valve	5/3-way valve		
				Normally closed	Normally exhausted	Normally open
Standard nominal flow rate		[l/min]	4500	4100	4600	4000

Switching times [ms]					
		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
5/2-way valve, single solenoid	MFH-5/2-...	60	66	–	–
	MFH-5/2-...-S-C	33	74	–	–
	MFH-5/2-D-1-FR-...	28	79	–	–
5/2-way valve, double solenoid	JMFH-...	–	–	18	–
	JMFDH-...	–	–	18	18
	JMFDH-5/2-D-3-S-C	–	–	24	21
5/3-way valve	MFH-5/3G-...	36	77	–	–
	MFH-5/3E-...	37	78	–	–
	MFH-5/3B-...	36	75	–	–

ATEX		
Type		MFH- ... -EX, JMFH- ... -EX, JMFDH- ... -EX
ATEX category for gas		II 2G
Type of ignition protection for gas		Ex h IIC T4 Gb
ATEX category for dust		II 2D
Type of (ignition) protection for dust		Ex h IIIC T105°C Db
Explosion-proof ambient temperature	[°C]	–5 <= Ta <= +40
Explosion protection certification outside EU		EPL Db (GB)
		EPL Gb (GB)
CE marking (see declaration of conformity)[1)]		To EU Explosion Protection Directive (ATEX)
UKCA marking (see declaration of conformity) 1)		To UK explosion regulations

1) More information www.festo.com/catalogue/... ➔ Support/Downloads.

Operating and environmental conditions				
Reset method			Pneumatic spring	Mechanical spring
Operating medium			Compressed air to ISO 8573-1:2010 [7:4:4]	
Pilot medium			Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on the operating/pilot medium			Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure	Internal pilot air supply	[MPa]	0.2 ... 1	0.3 ... 1
		[bar]	2 ... 10	3 ... 10
	External pilot air supply	[MPa]	–0.09 ... +1.6	–0.09 ... +1.6
		[bar]	–0.9 ... +16	–0.9 ... +16
Pilot pressure		[bar]	2 ... 10	3 ... 10
Ambient temperature		[°C]	–5 ... +40	
	JMFDH-5/2-D-3-S-C	[°C]	–5 ... +50	
	MFH-5/2-D-3-FR-S-C	[°C]	–5 ... +50	
Temperature of medium		[°C]	–10 ... +60	
	JMFDH-5/2-D-3-S-C	[°C]	–5 ... +50	
	MFH-5/2-D-3-FR-S-C	[°C]	–5 ... +50	

Safety characteristics		
Max. positive test pulse with 0 signal	[µs]	2200
Max. negative test pulse with logic 1	[µs]	3700
Shock resistance		Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Vibration resistant		Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6

Datasheet – Width 65 mm


Safety characteristics – JMFDH-5/2-D-3-SC and MFH-5/2-D-3-FR-SC		
Max. positive test pulse with 0 signal	[µs]	3700
Max. negative test pulse with logic 1	[µs]	4600
Shock resistance		Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Vibration resistant		Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6

Electrical data		
Electrical connection		Via F coil, to be ordered separately
	JMFDH-5/2-D-3-S-C MFH-5/2-D-3-FR-S-C	Via N1 coil, to be ordered separately
Degree of protection to EN 60529		IP65

Materials	
Housing	Die-cast aluminium
Seals	HNBR, NBR
Note on materials	RoHs-compliant
LABS (PWIS) conformity	VDMA24364-B1/B2-L

Dimensions – 5/2-way valve, single solenoid

Download CAD data ➔ www.festo.com




[1] Manual override [2] Captive retaining screws [3] Slot for inscription label

Type	B1	B2	B3	B4	D1	D2	H1	H2	H3	H4	H5	H6	L1	L2	L3	L4	L5	L6
MFH-5/2- ...	65	48	12	30	M8	M5	117	87.3	55	12	63.5	13.5	163	145.4	72.7	64	32	109
MFH-5/2- ... -FR- ...													182	164.7				

Datasheet – Width 65 mm

Dimensions – 5/2-way valves, double solenoid, 5/3-way valves

Download CAD data ➔ www.festo.com



[1] Manual override















[2] Captive retaining screws

[3] Slot for inscription label

Type	B1	B2	B3	B4	D1	D2	H1	H2	H3	H4	H5	H6	L1	L2	L3	L4	L5	L6
JMFH-5/2- ...	65	48	12	30	M8	M5	117	87.3	55	12	–	13.5	181	145.4	72.7	64	32	109
JMFDH-5/2- ...														145.4	72.7			
MFH-5/3...														184	92			

Ordering data – Width 65 mm


Ordering data – Valves with armature tube for solenoid coil MSF1)

Circuit symbol	Description	Pilot air supply	Weight [g]	ISO code		Part no.	Type
5/2-way valve, single solenoid							
	Pneumatic spring return	Internal	960	351	–	**151870**	**MFH-5/2-D-3-C**
					ATEX category a page 41	**535956**	**MFH-5/2-D-3-C-EX**
	Pneumatic spring return	External	960	364	–	**151032**	**MFH-5/2-D-3-S-C**
					ATEX category a page 41	**535959**	**MFH-5/2-D-3-S-C-EX**
	Mechanical spring return	Internal	960	352	–	**151711**	**MFH-5/2-D-3-FR-C**
					ATEX category a page 41	**535962**	**MFH-5/2-D-3-FR-C-EX**
	Mechanical spring return	External	1000	369	–	**8221574**	**MFH-5/2-D-3-FR-S-C**
5/2-way valve, double solenoid							
	–	Internal	1060	355	–	**151871**	**JMFH-5/2-D-3-C**
					ATEX category a page 41	**535965**	**JMFH-5/2-D-3-C-EX**
	–	External	1060	369	–	**151033**	**JMFH-5/2-D-3-S-C**
					ATEX category a page 41	**535968**	**JMFH-5/2-D-3-S-C-EX**
	With dominant signal at 14	Internal	1060	369	–	**151872**	**JMFDH-5/2-D-3-C**
					ATEX category a page 41	**536073**	**JMFDH-5/2-D-3-C-EX**
	With dominant signal at 14	External	1090	369	–	**8221573**	**JMFDH-5/2-D-3-S-C**
5/3-way valve							
	Normally closed, Mechanical spring return	Internal	1040	356	–	**151873**	**MFH-5/3G-D-3-C**
					ATEX category a page 41	**535971**	**MFH-5/3G-D-3-C-EX**
	Normally closed, Mechanical spring return	External	1040	369	–	**151034**	**MFH-5/3G-D-3-S-C**
					ATEX category a page 41	**535974**	**MFH-5/3G-D-3-S-C-EX**
	Normally exhausted, Mechanical spring return	Internal	1040	357	–	**151874**	**MFH-5/3E-D-3-C**
					ATEX category a page 41	**535977**	**MFH-5/3E-D-3-C-EX**
	Normally exhausted, Mechanical spring return	External	1040	369	–	**151035**	**MFH-5/3E-D-3-S-C**
					ATEX category a page 41	**535980**	**MFH-5/3E-D-3-S-C-EX**
	Normally open, Mechanical spring return	Internal	1040	358	–	**151875**	**MFH-5/3B-D-3-C**
					ATEX category a page 41	**535983**	**MFH-5/3B-D-3-C-EX**
	Normally open, Mechanical spring return	External	1040	369	–	**151036**	**MFH-5/3B-D-3-S-C**
					ATEX category a page 41	**535986**	**MFH-5/3B-D-3-S-C-EX**

1) Solenoid coils a page 163

Datasheet – Width 42 mm

- - Flow rate
1800 l/min



General technical data			
Design			Piston spool
Sealing principle			Soft
Actuation type			Electrical
Type of control			Piloted
Flow direction	External pilot air supply		Reversible
	Internal pilot air supply		Not reversible
Suitable for vacuum	External pilot air supply, pneumatic spring return or double solenoid		Yes
	External pilot air supply, pneumatic spring return		No
	Internal pilot air supply		No
Exhaust air function			Can be throttled, via individual sub-base
Type of mounting			On sub-base
Mounting position			Any
Max. tightening torque for valve mounting		[Nm]	1
Nominal width		[mm]	8
Overlap			Positive overlap
Width		[mm]	42
Grid dimension		[mm]	43
Noise level		[dB (A)]	85
Conforms to standard			ISO 5599-1
Pilot interface			To ISO 15218

Pneumatic ports		
Pneumatic connection	1, 2, 4, 3, 5	Sub-base size 1 to ISO 5599-1
	12	Sub-base size 1 to ISO 5599-1
	14	Sub-base size 1 to ISO 5599-1
Pilot exhaust air port	82	M5, not ducted
	84	M5, not ducted

Datasheet – Width 42 mm

Flow rate values – 2x2/2-way valves

		Mechanical spring return	Pneumatic spring return	1x vacuum operation
Nominal flow rate standardised according to ISO 8778	[l/min]	1700	1600	1500
Flow rate of valve	[l/min]	1500	1500	1400
Flow rate of valve on individual sub-base	[l/min]	1300	1300	1200
Flow rate of pneumatically linked valve	[l/min]	1300	1200	1200
Optimised flow rate of pneumatically linked valve	[l/min]	1500	1500	1400
b value		0.18	0.15	0.151
C value	[l/sbar]	6.503	7.015	6.343

Flow rate values – 2x3/2-way valves

		Normally closed		Normally open	
		Mechanical spring return	Pneumatic spring return	Mechanical spring return	Pneumatic spring return
Nominal flow rate standardised according to ISO 8778	[l/min]	1400	1300	1400	1300
Flow rate of valve	[l/min]	1300	1300	1300	1200
Flow rate of valve on individual sub-base	[l/min]	1100	1200	1100	1100
Flow rate of pneumatically linked valve	[l/min]	1100	1200	1100	1000
Optimised flow rate of pneumatically linked valve	[l/min]	1200	1300	1200	1100
b value		0.18	0.23	0.21	0.13
C value	[l/sbar]	5.293	5.597	5.511	5.347

Flow rate values – 2x3/2-way valves

		Normally open, normally closed	
		Mechanical spring return	Pneumatic spring return
Nominal flow rate standardised according to ISO 8778	[l/min]	1400	1400
Flow rate of valve	[l/min]	1300	1300
Flow rate of valve on individual sub-base	[l/min]	1100	1100
Flow rate of pneumatically linked valve	[l/min]	1100	1100
Optimised flow rate of pneumatically linked valve	[l/min]	1200	1200
b value		0.2	0.180
C value	[l/sbar]	5.479	5.477

Flow rate values – 5/2-way valve, single solenoid

		Mechanical spring return	Pneumatic spring return
Nominal flow rate standardised according to ISO 8778	[l/min]	1800	1800
Flow rate of valve	[l/min]	1700	1700
Flow rate of valve on individual sub-base	[l/min]	1400	1400
Flow rate of pneumatically linked valve	[l/min]	1400	1400
Optimised flow rate of pneumatically linked valve	[l/min]	1600	1600
b value		1.7	1.6
C value	[l/sbar]	7.718	7.707

Flow rate values – 5/2-way valve, double solenoid

		Bistable	Double solenoid with dominant signal
Nominal flow rate standardised according to ISO 8778	[l/min]	1800	1800
Flow rate of valve	[l/min]	1700	1700
Flow rate of valve on individual sub-base	[l/min]	1400	1400
Flow rate of pneumatically linked valve	[l/min]	1400	1400
Optimised flow rate of pneumatically linked valve	[l/min]	1600	1600
b value		1.6	1.5
C value	[l/sbar]	7.697	7.663

Datasheet – Width 42 mm

Flow rate values – 5/3-way valve

		Mid-position closed	Mid-position exhausted		
			–	Switching position 14 detenting	Switching position 12 detenting
Nominal flow rate standardised according to ISO 8778	[l/min]	1800	1800	1300	1200
Flow rate of valve	[l/min]	1600	1600	1200	1100
Flow rate of valve on individual sub-base	[l/min]	1400	1400	1100	1000
Flow rate of pneumatically linked valve	[l/min]	1300	1300	1100	1000
Optimised flow rate of pneumatically linked valve	[l/min]	1500	1500	1100	1100
b value		0.14	0.24	0.42	0.43
C value	[l/sbar]	7.482	7.141	4.578	4.489

Flow rate values – 5/3-way valve

		Mid-position pressurised	Mid-position port 2 pressurised, port 4 closed
Nominal flow rate standardised according to ISO 8778	[l/min]	1600	1700
Flow rate of valve	[l/min]	1500	1600
Flow rate of valve on individual sub-base	[l/min]	1300	1400
Flow rate of pneumatically linked valve	[l/min]	1200	1300
Optimised flow rate of pneumatically linked valve	[l/min]	1400	1450
b value		0.14	0.14
C value	[l/sbar]	6.799	7.141

Switching times

		Switching time on [ms]	Switching time off [ms]	Switching time changeover [ms]	Maximum switching frequency [Hz]
2x2/2-way valves		18	28	–	5
2x3/2-way valve, single solenoid	Mechanical spring return	22	25	–	5
	Pneumatic spring return	18	38	–	5
5/2-way valve, single solenoid	Mechanical spring return	21	52	–	1
	Pneumatic spring return	28	40	–	5
5/2-way valve, double solenoid		–	–	16	5
5/2-way valve, bistable, with dominant signal		–	–	16	5
5/3-way valve	Mid-position closed	18	55	32	5
	Mid-position exhausted	20	55	30	5
	Mid-position exhausted, switching position 14 detenting	18	40	28	5
	Mid-position exhausted, switching position 12 detenting	18	40	28	5
	Mid-position pressurised	22	55	27	5
	Mid-position port 2 pressurised Port 4 closed	20	55	30	5

Operating and environmental conditions – 2x2/2-way valves

		Internal pilot air	External pilot air
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure	[MPa]	0.3 ... 1	–0.09 ... 1
	[bar]	3 ... 10	–0.9 ... 10
Pilot pressure	[MPa]	0.3 ... 1	
	[bar]	3 ... 10	
Ambient temperature	[°C]	–10 ... +50	
Temperature of medium	[°C]	–10 ... +50	
Relative humidity	[%]	0 ... 90	

Datasheet – Width 42 mm

Operating and environmental conditions – 2x3/2-way valves				
		Internal pilot air	External pilot air	
			Pneumatic spring return	Mechanical spring return
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]		
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]		
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)		
Operating pressure	[MPa]	0.3 ... 1	0.3 ... 1	–0.09 ... 1
	[bar]	3 ... 10	3 ... 10	–0.9 ... 10
Pilot pressure	[MPa]	0.3 ... 1		
	[bar]	3 ... 10		
Ambient temperature	[°C]	–10 ... +50		
Temperature of medium	[°C]	–10 ... +50		
Relative humidity	[%]	0 ... 90		

Operating and environmental conditions – 5/2-way valves			
		Internal pilot air	External pilot air
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure	[MPa]	0.3 ... 1	–0.09 ... 1.6
	[bar]	3 ... 10	–0.9 ... 16
Pilot pressure	[MPa]	0.3 ... 1	
	[bar]	3 ... 10	
Ambient temperature	[°C]	–10 ... +50	
Temperature of medium	[°C]	–10 ... +50	
Relative humidity	[%]	0 ... 90	

Operating and environmental conditions – 5/3-way valves			
		Internal pilot air	External pilot air
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure	[MPa]	0.3 ... 1	–0.09 ... 1.6
	[bar]	3 ... 10	–0.9 ... 16
Pilot pressure	[MPa]	0.3 ... 1	
	[bar]	3 ... 10	
Ambient temperature	[°C]	–10 ... +50	
Temperature of medium	[°C]	–10 ... +50	
Relative humidity	[%]	0 ... 90	

Datasheet – Width 42 mm

Electrical data					
Electrical connection			With 8 mm armature tube	M12x1, A-coded To EN 61076-2-101	M12x1, A-coded to EN 61076-2-101, assignment to DESINA
Characteristic coil values	Without holding current reduction		–	24 V DC: 3.4 W	
	With holding current reduction		–	24 V DC: low-current phase 1.0 W, high-current phase 3.3 W	
Permissible voltage fluctuations		[%]	–	±10	
Duty cycle		[%]	100	100	
Degree of protection			IP65	IP65	
			NEMA 4	NEMA 4	

Electrical data			
Electrical connection			Type A To EN 175301-803
Characteristic coil values	Nominal operating voltage 12 V DC		12 V DC: 2.8 W
	Nominal operating voltage 24 V DC		24 V DC: 2.6 W
	Nominal operating voltage 48 V DC		48 V DC: 2.8 W
	Nominal operating voltage 24 V AC		24 V AC: 50/60 Hz, pick-up power: 2.5 VA, holding power: 1.7 VA
	Nominal operating voltage 48 V AC		48 V AC: 50/60 Hz, pick-up power: 2.5 VA, holding power: 1.7 VA
	Nominal operating voltage 110 V AC		110/120 V AC: 50/60 Hz, pick-up power 2.7 VA, holding power 1.9 VA
	Nominal operating voltage 230 V AC		230/240 V AC: 50/60 Hz, pick-up power 3.9 VA, holding power 2.8 VA
Permissible voltage fluctuations		[%]	±10
Duty cycle		[%]	100
Degree of protection			IP65
			NEMA 4


Electrical data				
Electrical connection			Type B	Type C To EN 175301-803
Characteristic coil values	Nominal operating voltage 12 V DC		12 V DC: 3.4 W	
	Nominal operating voltage 24 V DC		24 V DC: 3.3 W	
	Nominal operating voltage 48 V DC		48 V DC: 3.4 W	
	Nominal operating voltage 24 V AC		24 V AC: 50/60 Hz, pick-up power: 3.9 VA, holding power: 2.6 VA	
	Nominal operating voltage 48 V AC		48 V AC: 50/60 Hz, pick-up power: 3.9 VA, holding power: 2.7 VA	
	Nominal operating voltage 110 V AC		110/120 V AC: 50/60 Hz, pick-up power 4.4 VA, holding power 3.3 VA	
	Nominal operating voltage 230 V AC		230/240 V AC: 50/60 Hz, pick-up power 5.8 VA, holding power 4.6 VA	
Permissible voltage fluctuations		[%]	±10	
Duty cycle		[%]	100	
Degree of protection			IP65	
			NEMA 4	

Materials	
Housing	Die-cast aluminium
Seals	NBR
Screws	Steel
Note on materials	RoHs-compliant
LABS (PWIS) conformity	VDMA24364-B1/B2-L

Datasheet – Width 42 mm

Dimensions – 2x2/2- and 2x3/2- and double solenoid 5/2-way valves and 5/3-way valves, with solenoid coil

Download CAD data ➔ www.festo.com




[1] Manual override

	B1	B2	H1	L1	L2	L4	L5
VSVA-B-B...-D1-F8-1A1	43.1	28	83.8	146.1	106	36	18
VSVA-B-D...-D1-F8-1A1							
VSVA-B-T...-D1-F8-1A1							
VSVA-B-B...-D1-F8-1B2							
VSVA-B-D...-D1-F8-1B2							
VSVA-B-T...-D1-F8-1B2							

Datasheet – Width 42 mm

Dimensions – 2x2/2- and 2x3/2- and double solenoid 5/2-way valves and 5/3-way valves, without solenoid coil

Download CAD data ➔ www.festo.com




[1] Manual override

	B1	B2	H2	H3	L1	L2	L4	L5
VSVA-B-B...-D1-F8	43.1	28	71.3	53.8	143.2	106	36	18
VSVA-B-D...-D1-F8								
VSVA-B-T...-D1-F8								

Datasheet – Width 42 mm


Dimensions – 5/2-way valve, single solenoid, with solenoid coil Download CAD data ➔ www.festo.com



[1] Manual override

	B1	B2	H1	L1	L2	L4	L5
VSVA-B-M...-D1-F8-1A1	43.1	28	83.8	126.6	106	36	18
VSVA-B-M...-D1-F8-1B2							

Dimensions – 5/2-way valves, single solenoid, without solenoid coil Download CAD data ➔ www.festo.com















[1] Manual override

	B1	B2	H2	H3	L1	L2	L4	L5
VSVA-B-M...-D1-F8	43.1	28	71.3	53.8	124.6	106	36	18









Ordering data – Width 42 mm

Ordering data – Valves with 8 mm armature tube

Circuit symbol	Pilot air supply	Electrical connection	Manual override	Weight [g]	Part no.	Type
2x2/2-way valve, single solenoid, mechanical spring return, normally closed						
	Internal	–	Non-detenting	400	**8198565**	**VSVA-B-T22C-MH-D1-F8**
			Detenting	400	**8198539**	**VSVA-B-T22C-MD-D1-F8**
	External	–	Non-detenting	400	**8198578**	**VSVA-B-T22C-MZH-D1-F8**
			Detenting	400	**8198552**	**VSVA-B-T22C-MZD-D1-F8**
2x3/2-way valve, single solenoid, mechanical spring return, normally closed						
	Internal	Type B	Non-detenting	457	**8033718**	**VSVA-B-T32C-MH-D1-F8-1B2**
		–	Non-detenting	400	**8198562**	**VSVA-B-T32C-MH-D1-F8**
			Detenting	400	**8198536**	**VSVA-B-T32C-MD-D1-F8**
	External	Type B	Non-detenting	457	**8033728**	**VSVA-B-T32C-MZH-D1-F8-1B2**
		–	Non-detenting	400	**8198575**	**VSVA-B-T32C-MZH-D1-F8**
			Detenting	400	**8198549**	**VSVA-B-T32C-MZD-D1-F8**
2x3/2-way valve, single solenoid, pneumatic spring return, normally closed						
	Internal	–	Non-detenting	400	**8198560**	**VSVA-B-T32C-AH-D1-F8**
			Detenting	400	**8198534**	**VSVA-B-T32C-AD-D1-F8**
	External	–	Non-detenting	400	**8198573**	**VSVA-B-T32C-AZH-D1-F8**
			Detenting	400	**8198547**	**VSVA-B-T32C-AZD-D1-F8**
2x3/2-way valve, single solenoid, mechanical spring return, normally open						
	Internal	Type B	Non-detenting	457	**8033719**	**VSVA-B-T32U-MH-D1-F8-1B2**
		–	Non-detenting	400	**8198563**	**VSVA-B-T32U-MH-D1-F8**
			Detenting	400	**8198537**	**VSVA-B-T32U-MD-D1-F8**
	External	Type B	Non-detenting	457	**8033729**	**VSVA-B-T32U-MZH-D1-F8-1B2**
		–	Non-detenting	400	**8198576**	**VSVA-B-T32U-MZH-D1-F8**
			Detenting	400	**8198550**	**VSVA-B-T32U-MZD-D1-F8**
2x3/2-way valve, single solenoid, pneumatic spring return, normally open						
	Internal	–	Non-detenting	400	**8198561**	**VSVA-B-T32U-AH-D1-F8**
			Detenting	400	**8198535**	**VSVA-B-T32U-AD-D1-F8**
	External	–	Non-detenting	400	**8198574**	**VSVA-B-T32U-AZH-D1-F8**
			Detenting	400	**8198548**	**VSVA-B-T32U-AZD-D1-F8**
2x3/2-way valve, single solenoid, mechanical spring return, normally open/closed						
	Internal	Type B	Non-detenting	457	**8033720**	**VSVA-B-T32H-MH-D1-F8-1B2**
		–	Non-detenting	400	**8198564**	**VSVA-B-T32H-MH-D1-F8**
			Detenting	400	**8198538**	**VSVA-B-T32H-MD-D1-F8**
	External	Type B	Non-detenting	457	**8033730**	**VSVA-B-T32H-MZH-D1-F8-1B2**
		–	Non-detenting	400	**8198577**	**VSVA-B-T32H-MZH-D1-F8**
			Detenting	400	**8198551**	**VSVA-B-T32H-MZD-D1-F8**







Ordering data – Width 42 mm

Ordering data – Valves with 8 mm armature tube

Circuit symbol	Pilot air supply	Electrical connection	Manual override	Weight [g]	Part no.	Type
5/2-way valve, single solenoid, mechanical spring return						
	Internal	Type A to EN 175301-803	Non-detenting	433	**8033734**	**VSVA-B-M52-MH-D1-F8-1A1**
			Detenting	433	**8033694**	**VSVA-B-M52-MD-D1-F8-1A1**
		Type B	Non-detenting	407	**8033714**	**VSVA-B-M52-MH-D1-F8-1B2**
			Detenting	407	**8033674**	**VSVA-B-M52-MD-D1-F8-1B2**
		–	Non-detenting	350	**8198553**	**VSVA-B-M52-MH-D1-F8**
			Detenting	350	**8198527**	**VSVA-B-M52-MD-D1-F8**
			Detenting via accessory	350	**8033660**	**VSVA-B-M52-MT-D1-F8**
	External	Type B	Non-detenting	407	**8033724**	**VSVA-B-M52-MZH-D1-F8-1B2**
		–	Non-detenting	350	**8198566**	**VSVA-B-M52-MZH-D1-F8**
			Detenting	350	**8198540**	**VSVA-B-M52-MZD-D1-F8**
			Detenting via accessory	350	**8033667**	**VSVA-B-M52-MZT-D1-F8**
5/2-way valve, single solenoid, pneumatic spring return						
	Internal	Type A to EN 175301-803	Non-detenting	433	**8033733**	**VSVA-B-M52-AH-D1-F8-1A1**
			Detenting	433	**8033693**	**VSVA-B-M52-AD-D1-F8-1A1**
		Type B	Non-detenting	407	**8033713**	**VSVA-B-M52-AH-D1-F8-1B2**
			Detenting	407	**8033673**	**VSVA-B-M52-AD-D1-F8-1B2**
		–	Non-detenting	350	**8198554**	**VSVA-B-M52-AH-D1-F8**
			Detenting	350	**8198528**	**VSVA-B-M52-AD-D1-F8**
			Detenting via accessory	350	**8033659**	**VSVA-B-M52-AT-D1-F8**
	External	Type B	Non-detenting	407	**8033723**	**VSVA-B-M52-AZH-D1-F8-1B2**
		–	Non-detenting	350	**8198567**	**VSVA-B-M52-AZH-D1-F8**
			Detenting	350	**8198541**	**VSVA-B-M52-AZD-D1-F8**
			Detenting via accessory	350	**8033666**	**VSVA-B-M52-AZT-D1-F8**
5/2-way valve, double solenoid						
	Internal	Type A to EN 175301-803	Non-detenting	473	**8033731**	**VSVA-B-B52-H-D1-F8-1A1**
			Detenting	473	**8033691**	**VSVA-B-B52-D-D1-F8-1A1**
		Type B	Non-detenting	447	**8033711**	**VSVA-B-B52-H-D1-F8-1B2**
			Detenting	447	**8033671**	**VSVA-B-B52-D-D1-F8-1B2**
		–	Non-detenting	390	**8198555**	**VSVA-B-B52-H-D1-F8**
			Detenting	390	**8198529**	**VSVA-B-B52-D-D1-F8**
			Detenting via accessory	390	**8033657**	**VSVA-B-B52-T-D1-F8**
	External	Type B	Non-detenting	447	**8033721**	**VSVA-B-B52-ZH-D1-F8-1B2**
		–	Non-detenting	390	**8198568**	**VSVA-B-B52-ZH-D1-F8**
			Detenting	390	**8198542**	**VSVA-B-B52-ZD-D1-F8**
			Detenting via accessory	390	**8033664**	**VSVA-B-B52-ZT-D1-F8**
5/2-way valve, bistable, with dominant signal						
	Internal	Type B	Non-detenting	447	**8033712**	**VSVA-B-D52-H-D1-F8-1B2**
		–	Non-detenting	390	**8198556**	**VSVA-B-D52-H-D1-F8**
			Detenting	390	**8198530**	**VSVA-B-D52-D-D1-F8**
			Detenting via accessory	390	**8033658**	**VSVA-B-D52-T-D1-F8**
	External	Type B	Non-detenting	447	**8033722**	**VSVA-B-D52-ZH-D1-F8-1B2**
		–	Non-detenting	390	**8198569**	**VSVA-B-D52-ZH-D1-F8**
			Detenting	390	**8198543**	**VSVA-B-D52-ZD-D1-F8**
			Detenting via accessory	390	**8033665**	**VSVA-B-D52-ZT-D1-F8**


Ordering data – Width 42 mm

Ordering data – Valves with 8 mm armature tube

Circuit symbol	Pilot air supply	Electrical connection	Manual override	Weight [g]	Part no.	Type
5/3-way valve, mid-position closed, mechanical spring return						
	Internal	Type A to EN 175301-803	Non-detenting	488	**8033735**	**VSVA-B-P53C-H-D1-F8-1A1**
			Detenting	488	**8033695**	**VSVA-B-P53C-D-D1-F8-1A1**
		Type B	Non-detenting	462	**8033715**	**VSVA-B-P53C-H-D1-F8-1B2**
			Detenting	462	**8033675**	**VSVA-B-P53C-D-D1-F8-1B2**
		–	Non-detenting	405	**8198559**	**VSVA-B-P53C-H-D1-F8**
			Detenting	405	**8198533**	**VSVA-B-P53C-D-D1-F8**
			Detenting via accessory	405	**8033661**	**VSVA-B-P53C-T-D1-F8**
	External	Type B	Non-detenting	462	**8033725**	**VSVA-B-P53C-ZH-D1-F8-1B2**
		–	Non-detenting	405	**8198572**	**VSVA-B-P53C-ZH-D1-F8**
			Detenting	405	**8198546**	**VSVA-B-P53C-ZD-D1-F8**
			Detenting via accessory	405	**8033668**	**VSVA-B-P53C-ZT-D1-F8**
5/3-way valve, mid-position exhausted, mechanical spring return						
	Internal	Type A to EN 175301-803	Non-detenting	488	**8033736**	**VSVA-B-P53E-H-D1-F8-1A1**
			Detenting	488	**8033696**	**VSVA-B-P53E-D-D1-F8-1A1**
		Type B	Non-detenting	462	**8033716**	**VSVA-B-P53E-H-D1-F8-1B2**
			Detenting	462	**8033676**	**VSVA-B-P53E-D-D1-F8-1B2**
		–	Non-detenting	405	**8198558**	**VSVA-B-P53E-H-D1-F8**
			Detenting	405	**8198532**	**VSVA-B-P53E-D-D1-F8**
			Detenting via accessory	405	**8033662**	**VSVA-B-P53E-T-D1-F8**
	External	Type B	Non-detenting	462	**8033726**	**VSVA-B-P53E-ZH-D1-F8-1B2**
		–	Non-detenting	405	**8198571**	**VSVA-B-P53E-ZH-D1-F8**
			Detenting	405	**8198545**	**VSVA-B-P53E-ZD-D1-F8**
			Detenting via accessory	405	**8033669**	**VSVA-B-P53E-ZT-D1-F8**
5/3-way valve, mid-position pressurised, mechanical spring return						
	Internal	Type A to EN 175301-803	Non-detenting	488	**8033737**	**VSVA-B-P53U-H-D1-F8-1A1**
			Detenting	488	**8033697**	**VSVA-B-P53U-D-D1-F8-1A1**
		Type B	Non-detenting	462	**8033717**	**VSVA-B-P53U-H-D1-F8-1B2**
			Detenting	462	**8033677**	**VSVA-B-P53U-D-D1-F8-1B2**
		–	Non-detenting	405	**8198557**	**VSVA-B-P53U-H-D1-F8**
			Detenting	405	**8198531**	**VSVA-B-P53U-D-D1-F8**
			Detenting via accessory	405	**8033663**	**VSVA-B-P53U-T-D1-F8**
	External	Type B	Non-detenting	462	**8033727**	**VSVA-B-P53U-ZH-D1-F8-1B2**
		–	Non-detenting	405	**8198570**	**VSVA-B-P53U-ZH-D1-F8**
			Detenting	405	**8198544**	**VSVA-B-P53U-ZD-D1-F8**
			Detenting via accessory	405	**8033670**	**VSVA-B-P53U-ZT-D1-F8**

Datasheet – Width 52 mm

- Flow rate
4100 l/min



General technical data			
Design			Piston spool
Sealing principle			Soft
Actuation type			Electrical
Type of control			Piloted
Flow direction	External pilot air supply		Reversible
	Internal pilot air supply		Not reversible
Suitable for vacuum	External pilot air supply, pneumatic spring return or double solenoid		Yes
	External pilot air supply, pneumatic spring return		No
	Internal pilot air supply		No
Exhaust air function			Can be throttled, via individual sub-base
Type of mounting			On sub-base
Mounting position			Any
Max. tightening torque for valve mounting		[Nm]	2
Nominal width		[mm]	11.5
Overlap			Positive overlap
Width		[mm]	52
Grid dimension		[mm]	53
Noise level		[dB (A)]	85
Conforms to standard			ISO 5599-1
Pilot interface			To ISO 15218

Pneumatic ports		
Pneumatic connection	1, 2, 4, 3, 5	Sub-base size 2 to ISO 5599-1
	12	Sub-base size 2 to ISO 5599-1
	14	Sub-base size 2 to ISO 5599-1
Pilot exhaust air port	82	M5, not ducted
	84	M5, not ducted

Flow rate values – 2x2/2-way valves			
		Mechanical spring return	Pneumatic spring return
Nominal flow rate standardised according to ISO 8778	[l/min]	2100	–
Flow rate of valve	[l/min]	2000	–
Flow rate of valve on individual sub-base	[l/min]	1500	3100
Flow rate of pneumatically linked valve	[l/min]	1700	–
Optimised flow rate of pneumatically linked valve	[l/min]	–	–
b value		0.78	–
C value	[l/sbar]	3.098	–

Datasheet – Width 52 mm

Flow rate values – 2x3/2-way valves

		Normally closed		Normally open	
		Mechanical spring return	Pneumatic spring return	Mechanical spring return	Pneumatic spring return
Nominal flow rate standardised according to ISO 8778	[l/min]	2100	3100	2000	2900
Flow rate of valve	[l/min]	1900	2900	1800	2700
Flow rate of valve on individual sub-base	[l/min]	1700	2500	1800	2300
Flow rate of pneumatically linked valve	[l/min]	1100	2300	1700	2200
Optimised flow rate of pneumatically linked valve	[l/min]	–			
b value		0.57	0.34	0.69	0.32
C value	[l/sbar]	3.631	6.267	3.167	7.598

Flow rate values – 2x3/2-way valves

		Normally open, normally closed	
		Mechanical spring return	Pneumatic spring return
Nominal flow rate standardised according to ISO 8778	[l/min]	1900	3100
Flow rate of valve	[l/min]	1800	2900
Flow rate of valve on individual sub-base	[l/min]	1800	2400
Flow rate of pneumatically linked valve	[l/min]	1700	2200
Optimised flow rate of pneumatically linked valve	[l/min]	–	
b value		0.65	0.33
C value	[l/sbar]	3.208	6.257

Flow rate values – 5/2-way valve, single solenoid

		Mechanical spring return	Pneumatic spring return
Nominal flow rate standardised according to ISO 8778	[l/min]	4100	4100
Flow rate of valve	[l/min]	3800	3800
Flow rate of valve on individual sub-base	[l/min]	3200	3100
Flow rate of pneumatically linked valve	[l/min]	2700	2600
Optimised flow rate of pneumatically linked valve	[l/min]	–	
b value		0.3	0.31
C value	[l/sbar]	8.168	8.221

Flow rate values – 5/2-way valve, double solenoid

		Bistable	Double solenoid with dominant signal
Nominal flow rate standardised according to ISO 8778	[l/min]	4000	4000
Flow rate of valve	[l/min]	3700	3700
Flow rate of valve on individual sub-base	[l/min]	3100	3100
Flow rate of pneumatically linked valve	[l/min]	2600	2700
Optimised flow rate of pneumatically linked valve	[l/min]	–	
b value		0.2	0.26
C value	[l/sbar]	8.578	8.272

Flow rate values – 5/3-way valve

		Mid-position closed	Mid-position exhausted	Mid-position pressurised	Mid-position port 2 pressurised, port 4 closed
Nominal flow rate standardised according to ISO 8778	[l/min]	3700	3600	3500	3600
Flow rate of valve	[l/min]	3500	3400	3300	3400
Flow rate of valve on individual sub-base	[l/min]	2800	2700	2900	2900
Flow rate of pneumatically linked valve	[l/min]	2600	2500	2500	2600
Optimised flow rate of pneumatically linked valve	[l/min]	–			
b value		0.26	0.23	0.33	0.3
C value	[l/sbar]	7.696	7.667	7.069	7.383

Datasheet – Width 52 mm

Switching times

		Switching time on [ms]	Switching time off [ms]	Switching time changeover [ms]	Maximum switching frequency [Hz]
2x2/2-way valves	Mechanical spring return	23	45	–	5
	Pneumatic spring return	18	52	–	
2x3/2-way valve, single solenoid	Mechanical spring return	33	38	–	5
	Pneumatic spring return	25	50	–	5
5/2-way valve, single solenoid	Mechanical spring return	23	83	–	1
	Pneumatic spring return	56	64	–	5
5/2-way valve, double solenoid		–	–	23	5
5/2-way valve, bistable, with dominant signal		–	–	22	5
5/3-way valve	Mid-position closed	25	78	40	5
	Mid-position exhausted	26	82	40	5
	Mid-position pressurised	26	80	34	5
	Mid-position port 2 pressurised Port 4 closed	26	79	37	5

Operating and environmental conditions – 2x2/2-way valves

		Internal pilot air	External pilot air
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure	[MPa]	0.3 ... 1	–0.09 ... 1
	[bar]	3 ... 10	–0.9 ... 10
Pilot pressure	[MPa]	0.3 ... 1	
	[bar]	3 ... 10	
Ambient temperature	[°C]	–10 ... +50	
Temperature of medium	[°C]	–10 ... +50	
Relative humidity	[%]	0 ... 90	

Operating and environmental conditions – 2x3/2-way valves

		Internal pilot air	External pilot air	
			Pneumatic spring return	Mechanical spring return
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]		
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]		
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)		
Operating pressure	[MPa]	0.3 ... 1	0.3 ... 1	–0.09 ... 1
	[bar]	3 ... 10	3 ... 10	–0.9 ... 10
Pilot pressure	[MPa]	0.3 ... 1		
	[bar]	3 ... 10		
Ambient temperature	[°C]	–10 ... +50		
Temperature of medium	[°C]	–10 ... +50		
Relative humidity	[%]	0 ... 90		

Operating and environmental conditions – 5/2-way valves

		Internal pilot air	External pilot air
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure	[MPa]	0.3 ... 1	–0.09 ... 1.6
	[bar]	3 ... 10	–0.9 ... 16
Pilot pressure	[MPa]	0.3 ... 1	
	[bar]	3 ... 10	
Ambient temperature	[°C]	–10 ... +50	
Temperature of medium	[°C]	–10 ... +50	
Relative humidity	[%]	0 ... 90	

Datasheet – Width 52 mm

Operating and environmental conditions – 5/3-way valves				
			Internal pilot air	External pilot air
Operating medium			Compressed air to ISO 8573-1:2010 [7:4:4]	
Pilot medium			Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on the operating/pilot medium			Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure		[MPa]	0.3 ... 1	–0.09 ... 1.6
		[bar]	3 ... 10	–0.9 ... 16
Pilot pressure		[MPa]	0.3 ... 1	
		[bar]	3 ... 10	
Ambient temperature		[°C]	–10 ... +50	
Temperature of medium		[°C]	–10 ... +50	
Relative humidity		[%]	0 ... 90	

Electrical data					
Electrical connection			With 8 mm armature tube	M12x1, A-coded To EN 61076-2-101	M12x1, A-coded to EN 61076-2-101, assignment to DESINA
Characteristic coil values	Without holding current reduction		–	24 V DC: 3.4 W	
	With holding current reduction		–	24 V DC: low-current phase 1.0 W, high-current phase 3.3 W	
Permissible voltage fluctuations		[%]	–	±10	
Duty cycle		[%]	100	100	
Degree of protection			IP65	IP65	
			NEMA 4	NEMA 4	

Electrical data			
Electrical connection			Type A To EN 175301-803
Characteristic coil values	Nominal operating voltage 12 V DC		12 V DC: 2.8 W
	Nominal operating voltage 24 V DC		24 V DC: 2.6 W
	Nominal operating voltage 48 V DC		48 V DC: 2.8 W
	Nominal operating voltage 24 V AC		24 V AC: 50/60 Hz, pick-up power: 2.5 VA, holding power: 1.7 VA
	Nominal operating voltage 48 V AC		48 V AC: 50/60 Hz, pick-up power: 2.5 VA, holding power: 1.7 VA
	Nominal operating voltage 110 V AC		110/120 V AC: 50/60 Hz, pick-up power 2.7 VA, holding power 1.9 VA
	Nominal operating voltage 230 V AC		230/240 V AC: 50/60 Hz, pick-up power 3.9 VA, holding power 2.8 VA
Permissible voltage fluctuations		[%]	±10
Duty cycle		[%]	100
Degree of protection			IP65
			NEMA 4


Electrical data				
Electrical connection			Type B	Type C To EN 175301-803
Characteristic coil values	Nominal operating voltage 12 V DC		12 V DC: 3.4 W	
	Nominal operating voltage 24 V DC		24 V DC: 3.3 W	
	Nominal operating voltage 48 V DC		48 V DC: 3.4 W	
	Nominal operating voltage 24 V AC		24 V AC: 50/60 Hz, pick-up power: 3.9 VA, holding power: 2.6 VA	
	Nominal operating voltage 48 V AC		48 V AC: 50/60 Hz, pick-up power: 3.9 VA, holding power: 2.7 VA	
	Nominal operating voltage 110 V AC		110/120 V AC: 50/60 Hz, pick-up power 4.4 VA, holding power 3.3 VA	
	Nominal operating voltage 230 V AC		230/240 V AC: 50/60 Hz, pick-up power 5.8 VA, holding power 4.6 VA	
Permissible voltage fluctuations		[%]	±10	
Duty cycle		[%]	100	
Degree of protection			IP65	
			NEMA 4	

Materials	
Housing	Die-cast aluminium
Seals	NBR
Screws	Steel
Note on materials	RoHs-compliant
LABS (PWIS) conformity	VDMA24364-B1/B2-L

Datasheet – Width 52 mm

Dimensions – 2x2/2- and 2x3/2- and double solenoid 5/2-way valves and 5/3-way valves, with solenoid coil

Download CAD data ➔ www.festo.com




[1] Manual override

	B1	B2	H1	L1	L2	L4	L5
VSVA-B-B...-D2-F8-1A1	54.8	38	93.8	162.9	134.3	48	24
VSVA-B-D...-D2-F8-1A1							
VSVA-B-T...-D2-F8-1A1							
VSVA-B-B...-D2-F8-1B2							
VSVA-B-D...-D2-F8-1B2							
VSVA-B-T...-D2-F8-1B2							

Datasheet – Width 52 mm

Dimensions – 2x2/2- and 2x3/2- and double solenoid 5/2-way valves and 5/3-way valves, without solenoid coil

Download CAD data ➔ www.festo.com




[1] Manual override

	B1	B2	H2	H3	L1	L2	L4	L5
VSVA-B-B...-D2-F8	54.8	38	81.3	63.8	161	134.3	48	24
VSVA-B-D...-D2-F8								
VSVA-B-T...-D2-F8								

Datasheet – Width 52 mm

Dimensions – 5/2-way valve, single solenoid, with solenoid coil Download CAD data ➔ www.festo.com




[1] Manual override

	B1	B2	H1	L1	L2	L4	L5
VSVA-B-M...-D2-F8-1A1	54.8	38	93.8	148.6	134.3	48	24
VSVA-B-M...-D2-F8-1B2							

Datasheet – Width 52 mm

Dimensions – 5/2-way valves, single solenoid, without solenoid coil Download CAD data ➔ www.festo.com















[1] Manual override

	B1	B2	H2	H3	L1	L2	L4	L5
VSVA-B-M...-D2-F8	54.8	38	81.3	63.8	147.6	134.3	48	24










Ordering data – Width 52 mm

Ordering data – Valves with 8 mm armature tube

Circuit symbol	Pilot air supply	Electrical connection	Manual override	Weight [g]	Part no.	Type
2x2/2-way valve, single solenoid, mechanical spring return, normally closed						
	Internal	–	Non-detenting	685	**8198624**	**VSVA-B-T22C-MH-D2-F8**
			Detenting	685	**8198598**	**VSVA-B-T22C-MD-D2-F8**
	External	–	Non-detenting	685	**8198637**	**VSVA-B-T22C-MZH-D2-F8**
			Detenting	685	**8198611**	**VSVA-B-T22C-MZD-D2-F8**
2x3/2-way valve, single solenoid, mechanical spring return, normally closed						
	Internal	Type B	Non-detenting	737	**8033812**	**VSVA-B-T32C-MH-D2-F8-1B2**
		–	Non-detenting	680	**8198621**	**VSVA-B-T32C-MH-D2-F8**
			Detenting	680	**8198595**	**VSVA-B-T32C-MD-D2-F8**
	External	Type B	Non-detenting	737	**8033822**	**VSVA-B-T32C-MZH-D2-F8-1B2**
		–	Non-detenting	680	**8198634**	**VSVA-B-T32C-MZH-D2-F8**
			Detenting	680	**8198608**	**VSVA-B-T32C-MZD-D2-F8**
2x3/2-way valve, single solenoid, pneumatic spring return, normally closed						
	Internal	–	Non-detenting	680	**8198619**	**VSVA-B-T32C-AH-D2-F8**
			Detenting	680	**8198593**	**VSVA-B-T32C-AD-D2-F8**
	External	–	Non-detenting	680	**8198632**	**VSVA-B-T32C-AZH-D2-F8**
			Detenting	680	**8198606**	**VSVA-B-T32C-AZD-D2-F8**
2x3/2-way valve, single solenoid, mechanical spring return, normally open						
	Internal	Type B	Non-detenting	737	**8033813**	**VSVA-B-T32U-MH-D2-F8-1B2**
		–	Non-detenting	680	**8198622**	**VSVA-B-T32U-MH-D2-F8**
			Non-detenting	680	**8198596**	**VSVA-B-T32U-MD-D2-F8**
	External	Type B	Non-detenting	737	**8033823**	**VSVA-B-T32U-MZH-D2-F8-1B2**
		–	Detenting	680	**8198609**	**VSVA-B-T32U-MZD-D2-F8**
	External	–	Non-detenting	680	**8198635**	**VSVA-B-T32U-MZH-D2-F8**
2x3/2-way valve, single solenoid, pneumatic spring return, normally open						
	Internal	–	Non-detenting	680	**8198620**	**VSVA-B-T32U-AH-D2-F8**
			Detenting	680	**8198594**	**VSVA-B-T32U-AD-D2-F8**
	External	–	Non-detenting	680	**8198633**	**VSVA-B-T32U-AZH-D2-F8**
	External	–	Detenting	680	**8198607**	**VSVA-B-T32U-AZD-D2-F8**









Ordering data – Width 52 mm

Ordering data – Valves with 8 mm armature tube

Circuit symbol	Pilot air supply	Electrical connection	Manual override	Weight [g]	Part no.	Type
2x3/2-way valve, single solenoid, mechanical spring return, normally open/closed						
	Internal	Type B	Non-detenting	737	**8033814**	**VSVA-B-T32H-MH-D2-F8-1B2**
		–	Non-detenting	680	**8198623**	**VSVA-B-T32H-MH-D2-F8**
			Detenting	680	**8198597**	**VSVA-B-T32H-MD-D2-F8**
	External	Type B	Non-detenting	737	**8033824**	**VSVA-B-T32H-MZH-D2-F8-1B2**
		–	Detenting	680	**8198610**	**VSVA-B-T32H-MZD-D2-F8**
	External	–	Non-detenting	680	**8198636**	**VSVA-B-T32H-MZH-D2-F8**
5/2-way valve, single solenoid, mechanical spring return						
	Internal	Type A to EN 175301-803	Non-detenting	713	**8033828**	**VSVA-B-M52-MH-D2-F8-1A1**
			Detenting	713	**8033788**	**VSVA-B-M52-MD-D2-F8-1A1**
		Type B	Non-detenting	687	**8033808**	**VSVA-B-M52-MH-D2-F8-1B2**
			Detenting	687	**8033768**	**VSVA-B-M52-MD-D2-F8-1B2**
		–	Non-detenting	630	**8198612**	**VSVA-B-M52-MH-D2-F8**
			Detenting	630	**8198586**	**VSVA-B-M52-MD-D2-F8**
			Detenting via accessory	630	**8033754**	**VSVA-B-M52-MT-D2-F8**
	External	Type B	Non-detenting	687	**8033818**	**VSVA-B-M52-MZH-D2-F8-1B2**
		–	Non-detenting	630	**8198625**	**VSVA-B-M52-MZH-D2-F8**
			Detenting	630	**8198599**	**VSVA-B-M52-MZD-D2-F8**
			Detenting via accessory	630	**8033761**	**VSVA-B-M52-MZT-D2-F8**
5/2-way valve, single solenoid, pneumatic spring return						
	Internal	Type A to EN 175301-803	Non-detenting	713	**8033827**	**VSVA-B-M52-AH-D2-F8-1A1**
			Detenting	713	**8033787**	**VSVA-B-M52-AD-D2-F8-1A1**
		Type B	Non-detenting	687	**8033807**	**VSVA-B-M52-AH-D2-F8-1B2**
			Detenting	687	**8033767**	**VSVA-B-M52-AD-D2-F8-1B2**
		–	Non-detenting	630	**8198613**	**VSVA-B-M52-AH-D2-F8**
			Detenting	630	**8198587**	**VSVA-B-M52-AD-D2-F8**
			Detenting via accessory	630	**8033753**	**VSVA-B-M52-AT-D2-F8**
	External	Type B	Non-detenting	687	**8033817**	**VSVA-B-M52-AZH-D2-F8-1B2**
		–	Non-detenting	630	**8198626**	**VSVA-B-M52-AZH-D2-F8**
			Detenting	630	**8198600**	**VSVA-B-M52-AZD-D2-F8**
			Detenting via accessory	630	**8033760**	**VSVA-B-M52-AZT-D2-F8**
5/2-way valve, double solenoid						
	Internal	Type A to EN 175301-803	Non-detenting	748	**8033825**	**VSVA-B-B52-H-D2-F8-1A1**
			Detenting	748	**8033785**	**VSVA-B-B52-D-D2-F8-1A1**
		Type B	Non-detenting	722	**8033805**	**VSVA-B-B52-H-D2-F8-1B2**
			Detenting	722	**8033765**	**VSVA-B-B52-D-D2-F8-1B2**
		–	Non-detenting	665	**8198614**	**VSVA-B-B52-H-D2-F8**
			Detenting	665	**8198588**	**VSVA-B-B52-D-D2-F8**
			Detenting via accessory	665	**8033751**	**VSVA-B-B52-T-D2-F8**
	External	Type B	Non-detenting	722	**8033815**	**VSVA-B-B52-ZH-D2-F8-1B2**
		–	Non-detenting	665	**8198627**	**VSVA-B-B52-ZH-D2-F8**
			Detenting	665	**8198601**	**VSVA-B-B52-ZD-D2-F8**
			Detenting via accessory	665	**8033758**	**VSVA-B-B52-ZT-D2-F8**

Ordering data – Width 52 mm


Ordering data – Valves with 8 mm armature tube

Circuit symbol	Pilot air supply	Electrical connection	Manual override	Weight [g]	Part no.	Type
5/2-way valve, bistable, with dominant signal						
	Internal	Type B	Non-detenting	722	**8033806**	**VSVA-B-D52-H-D2-F8-1B2**
		–	Non-detenting	665	**8198615**	**VSVA-B-D52-H-D2-F8**
			Detenting	665	**8198589**	**VSVA-B-D52-D-D2-F8**
			Detenting via accessory	665	**8033752**	**VSVA-B-D52-T-D2-F8**
	External	Type B	Non-detenting	722	**8033816**	**VSVA-B-D52-ZH-D2-F8-1B2**
		–	Non-detenting	665	**8198628**	**VSVA-B-D52-ZH-D2-F8**
			Detenting	665	**8198602**	**VSVA-B-D52-ZD-D2-F8**
			Detenting via accessory	665	**8033759**	**VSVA-B-D52-ZT-D2-F8**
5/3-way valve, mid-position closed, mechanical spring return						
	Internal	Type A to EN 175301-803	Non-detenting	803	**8033829**	**VSVA-B-P53C-H-D2-F8-1A1**
			Detenting	803	**8033789**	**VSVA-B-P53C-D-D2-F8-1A1**
		Type B	Non-detenting	777	**8033809**	**VSVA-B-P53C-H-D2-F8-1B2**
			Detenting	777	**8033769**	**VSVA-B-P53C-D-D2-F8-1B2**
		–	Non-detenting	720	**8198618**	**VSVA-B-P53C-H-D2-F8**
			Detenting	720	**8198592**	**VSVA-B-P53C-D-D2-F8**
			Detenting via accessory	720	**8033755**	**VSVA-B-P53C-T-D2-F8**
	External	Type B	Non-detenting	777	**8033819**	**VSVA-B-P53C-ZH-D2-F8-1B2**
		–	Non-detenting	720	**8198631**	**VSVA-B-P53C-ZH-D2-F8**
			Detenting	720	**8198605**	**VSVA-B-P53C-ZD-D2-F8**
			Detenting via accessory	720	**8033762**	**VSVA-B-P53C-ZT-D2-F8**
5/3-way valve, mid-position exhausted, mechanical spring return						
	Internal	Type A to EN 175301-803	Non-detenting	803	**8033830**	**VSVA-B-P53E-H-D2-F8-1A1**
			Detenting	803	**8033790**	**VSVA-B-P53E-D-D2-F8-1A1**
		Type B	Non-detenting	777	**8033810**	**VSVA-B-P53E-H-D2-F8-1B2**
			Detenting	777	**8033770**	**VSVA-B-P53E-D-D2-F8-1B2**
		–	Non-detenting	720	**8198617**	**VSVA-B-P53E-H-D2-F8**
			Detenting	720	**8198591**	**VSVA-B-P53E-D-D2-F8**
			Detenting via accessory	720	**8033756**	**VSVA-B-P53E-T-D2-F8**
	External	Type B	Non-detenting	777	**8033820**	**VSVA-B-P53E-ZH-D2-F8-1B2**
		–	Non-detenting	720	**8198630**	**VSVA-B-P53E-ZH-D2-F8**
			Detenting	720	**8198604**	**VSVA-B-P53E-ZD-D2-F8**
			Detenting via accessory	720	**8033763**	**VSVA-B-P53E-ZT-D2-F8**
5/3-way valve, mid-position pressurised, mechanical spring return						
	Internal	Type A to EN 175301-803	Non-detenting	803	**8033831**	**VSVA-B-P53U-H-D2-F8-1A1**
			Detenting	803	**8033791**	**VSVA-B-P53U-D-D2-F8-1A1**
		Type B	Non-detenting	777	**8033811**	**VSVA-B-P53U-H-D2-F8-1B2**
			Detenting	777	**8033771**	**VSVA-B-P53U-D-D2-F8-1B2**
		–	Non-detenting	720	**8198616**	**VSVA-B-P53U-H-D2-F8**
			Detenting	720	**8198590**	**VSVA-B-P53U-D-D2-F8**
			Detenting via accessory	720	**8033757**	**VSVA-B-P53U-T-D2-F8**
	External	Type B	Non-detenting	777	**8033821**	**VSVA-B-P53U-ZH-D2-F8-1B2**
		–	Non-detenting	720	**8198629**	**VSVA-B-P53U-ZH-D2-F8**
			Detenting	720	**8198603**	**VSVA-B-P53U-ZD-D2-F8**
			Detenting via accessory	720	**8033764**	**VSVA-B-P53U-ZT-D2-F8**

Datasheet – Width 38 mm

- Flow rate
  max. 1343 l/min

- Voltage
  24 V DC



General technical data					
Valve function		5/2-way, single solenoid		5/2-way, double solenoid	5/3-way, exhausted
Reset method		Pneumatic spring	Mechanical spring	–	Mechanical spring
Design		Piston spool with sealing ring			
Overlap		Negative overlap			
Sealing principle		Soft			
Actuation type		Electrical			
Type of control		Piloted			
Pilot air supply		Internal			
Flow direction		Not reversible			
Exhaust air function		Can be throttled			
Manual override		Non-detenting; detenting			
Type of mounting		On sub-base			
Mounting position		Any			
Nominal width	[mm]	6.3			
Valve size	[mm]	42			
Width	[mm]	38			
Grid dimension	[mm]	43			
b value		0.26	0.26	0.26	0.26
C value	[l/sbar]	5.87	5.88	5.91	5.63
Maximum assembly torque for valve mounting	[Nm]	5			
Product weight	[g]	321	324	400	402
Conforms to standard		ISO 5599-1			
ISO code		151	152	155	157

Pneumatic ports		
Pneumatic connection	1, 2, 4, 3, 5	Sub-base size 1 to ISO 5599-1
	12	–
	14	–
Pilot exhaust air port	82	–
	84	–
Connection for venting hole		Not ducted

Flow rates					
Valve function		5/2-way, single solenoid		5/2-way, double solenoid	5/3-way, exhausted
Reset method		Pneumatic spring	Mechanical spring	–	Mechanical spring
Flow rate of valve	[l/min]	1342	1343	1341	1289
Flow rate of valve on individual sub-base	[l/min]	1341	1342	1341	1289
Flow rate of pneumatically linked valve	[l/min]	1313	1313	1313	1283
Standard nominal flow rate	[l/min]	1200	1200	1200	1200

Datasheet – Width 38 mm

Switching times					
Valve function		5/2-way, single solenoid		5/2-way, double solenoid	5/3-way, exhausted
Reset method		Pneumatic spring	Mechanical spring	–	Mechanical spring
Switching time on	[ms]	17.3	19.9	–	12.4
Switching time off	[ms]	20.7	20.9	–	37.4
Switching time changeover	[ms]	–	–	10.5	18.9

Safety characteristics		
Max. positive test pulse with 0 signal	[µs]	2500
Max. negative test pulse with logic 1	[µs]	1100
Shock resistance		Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Vibration resistant		Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6

Operating and environmental conditions		
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)
Operating pressure	[MPa]	0.3 ... 0.8
	[bar]	3 ... 8
Ambient temperature	[°C]	–5 ... +50
Temperature of medium	[°C]	–5 ... +50
Corrosion resistance class CRC[1)]		1 - low corrosion stress

1) More information www.festo.com/x/topic/crc


Electrical data		
Electrical connection		Type B
		To industry standard (11 mm)
Nominal operating voltage	[V DC]	24
Characteristic coil values		24 V DC: 3.3 W
Permissible voltage fluctuations	[%]	±10
Duty cycle	[%]	100
Degree of protection		IP65
		With plug socket
		To IEC 60529
Signal status indication		With accessories

Materials	
Housing	Wrought aluminium alloy
Seals	NBR, HNBR
Piston spool	Wrought aluminium alloy
Screws	Galvanised steel
Note on materials	RoHs-compliant
LABS (PWIS) conformity	VDMA24364-Zone III

Datasheet – Width 38 mm

Dimensions – 5/2-way valve, single solenoid

Download CAD data ➔ www.festo.com




[1] Retaining screws M5

Type	B1	B2	H1	H4	H6	L2	L16
VSVA-BK-M52...	38	28	37.2	47.7	7.5	137.6	27

Datasheet – Width 38 mm





Dimensions - 5/2-way valves, double solenoid, 5/3-way valves Download CAD data ➔ www.festo.com



[1] Retaining screws M5

Type	B1	B2	H1	H4	H6	L1	L16
VSVA-BK-B52...	38	28	37.2	47.7	7.5	186.1	27
VSVA-BK-P53...							


Ordering data

Code	Circuit symbol			Part no.	Type
5/2-way single solenoid valve					
–		Mechanical spring	Internal pilot air supply	**8166594**	**VSVA-BK-M52-MD-D1-1B2**
–		Pneumatic spring	Internal pilot air supply	**8166593**	**VSVA-BK-M52-AD-D1-1B2**
5/2-way double solenoid valve					
–		–	Internal pilot air supply	**8166592**	**VSVA-BK-B52-D-D1-1B2**
5/3-way solenoid valve					
–		Mid-position exhausted	Internal pilot air supply	**8166595**	**VSVA-BK-P53E-D-D1-1B2**

Datasheet – Width 42 mm

- Flow rate
Up to 1300 l/min

- Voltage
24 V DC



General technical data			
Design			Piston spool
Sealing principle			Soft
Actuation type			Electrical
Type of control			Piloted
Exhaust air function			Can be throttled, via throttle plate, via individual sub-base
Manual override			Non-detenting, detenting
Type of mounting			On sub-base
Mounting position			Any
Nominal width		[mm]	11
Overlap			Positive overlap
Width		[mm]	42
Grid dimension		[mm]	43
Conforms to standard			ISO 5599-1
Certification			c UL us – Recognized (OL)
	Timer valve		–

Pneumatic ports			
		Internal pilot air supply	External pilot air supply
Pneumatic connection	1, 2, 4, 3, 5	Sub-base size 1 to ISO 5599-1	Sub-base size 1 to ISO 5599-1
Pilot air port	12/14	–	Sub-base size 1 to ISO 5599-1
Pilot exhaust air port	82/84	–	Either: Not ducted as per standard, or ducted

Flow rates						
Valve function			2/2-way valve	3/2-way valve	5/2-way valve	5/3-way valve
Standard nominal flow rate (standardised to DIN 1343)		[l/min]	1300	1100	1300	1300
Valve			1600	1600	2000	1900
Valve on individual sub-base			1400	1200	1400	1400
Pneumatically linked valve			1300	1100	1300	1400

Switching times [ms]					
		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
2x 2/2-way valve	VSVA-B-T22...	20	38	–	–
2x 3/2-way valve	VSVA-B-T32...	20	38	–	–
2x 3/2-way valve, reversible	VSVA-B-T32...	34	28	–	–
5/2-way valve, single solenoid	VSVA-B-M52-A...	27	45	–	–
	VSVA-B-M52-M...	22	60	–	–
5/2-way valve, double solenoid	VSVA-B-B52...	–	–	16	–
	VSVA-B-TR1-B52...	–	–	16	–
	VSVA-B-D52...	–	–	–	19
5/3-way valve	VSVA-B-P53...	22	65	–	–

Datasheet – Width 42 mm

Operating and environmental conditions								
Valve function			2x 2/2-way valve	2x 3/2-way valve	2x 3/2-way valve, reversible	5/2-way valve	5/2-way valve, timer valve	5/3-way valve
Operating medium			Compressed air to ISO 8573-1:2010 [7:4:4]					
Pilot medium			Compressed air to ISO 8573-1:2010 [7:4:4]					
Note on the operating/pilot medium			Lubricated operation possible (in which case lubricated operation will always be required)					
Operating pressure	Internal pilot air supply	[MPa]	0.3 ... 1	0.3 ... 1	–	0.3 ... 1	–	0.3 ... 1
		[bar]	3 ... 10	3 ... 10	–	3 ... 10	–	3 ... 10
	External pilot air supply	[MPa]	0.3 ... 1	0.3 ... 1	–0.09 ... +1	–0.09 ... +1.6	–0.09 ... +1.6	–0.09 ... +1.6
		[bar]	3 ... 10	3 ... 10	–0.9 ... +10	–0.9 ... +16	–0.9 ... +16	–0.9 ... +16
Pilot pressure	Internal pilot air supply	[MPa]	–					
		[bar]	–					
	External pilot air supply	[MPa]	0.3 ... 1					
		[bar]	3 ... 10					
Ambient temperature		[°C]	–5 ... +50					
Temperature of medium		[°C]	–5 ... +50					
Relative humidity		[%]	0 ... 90					
Corrosion resistance class CRC[1]			0 - no corrosion stress					
CE marking (see declaration of conformity)[2]			–	–	–	–	To EU EMC Directive[3] To EU RoHS Directive	–
UKCA marking (see declaration of conformity)[2]			–	–	–	–	To UK EMC regulations To UK RoHS regulations	–
KC marking			–	–	–	–	KC EMC	–

1) More information www.festo.com/x/topic/crc
2) More information www.festo.com/catalogue/... ➔ Support/Downloads.
3) For information about the area of use, see the EC declaration of conformity at: www.festo.com/catalogue/... d Support/Downloads.
If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

Safety characteristics					
Valve function		2x 3/2-way valve	5/2-way valve	5/2-way valve, with dominant signal at 14	5/3-way valve
Max. positive test pulse with 0 signal	[µs]	1600	1400	1600	1400
Max. negative test pulse with logic 1	[µs]	1100	900	1100	900
Shock resistance		Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27			
Vibration resistant		Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6			

Electrical data							
Valve function			2x 2/2-way valve	2x 3/2-way valve	5/2-way valve	5/2-way valve, timer valve	5/3-way valve
Electrical connection			Central plug, round design M12x1, 3-pin				
Signal status indication			LED				
Characteristic coil values	Voltage	[V DC]	24				
	Power	[W]	1.3	1.3	1.6	1.6	1.6
Permissible voltage fluctuations		[%]	±10				
Switch-off time		[h]	–			< 4.5	–
Charging time		[min]	–			> 2	–
Current consumption			–			Max. 130 mA for up to 4 s during charging	–
			–			Max. 65 mA after 4 s during charging	–
			–			6 mA after charging	–
Duty cycle		[%]	100				
Degree of protection to EN 60529			IP65, NEMA4 (in combination with a plug socket)				


Datasheet – Width 42 mm

Materials	
Housing	Die-cast aluminium, PA
Seals	NBR, FPM, HNBR
Screws	Galvanised steel
Note on materials	RoHs-compliant
LABS (PWIS) conformity	VDMA24364-B1/B2-L


Product weight		
2x 2/2-way valve	[g]	442
2x 3/2-way valve	[g]	442
5/2-way valve, single solenoid	[g]	426
5/2-way valve, double solenoid	[g]	439
5/2-way valve, double solenoid, timer valve	[g]	460
5/3-way valve	[g]	456

Pilot pressure p12/14 as a function of working pressure p1

2x 2/2-way valve and 2x 3/2-way valve




5/2-way valve and 5/3-way valve, external pilot air supply



Holding time t1 as a function of charging time t2

5/2-way valve, timer valve



The timer valve automatically switches pilot control 12 after a time that can be adjusted.
This means that pilot control 14 must have switched first and that the switching pulse continues to be present (see table opposite).
The time until the pilot controls are switched automatically is set on the valve before it is mounted on the manifold sub-base.


Even when the valve or system is de-energised, automatic switching will still happen.

Datasheet – Width 42 mm


Protective circuit

Each solenoid coil VSVA is provided with a spark arresting protective circuit and protected against polarity reversal.

24 V DC version




M12x1 – Pin allocation on the valve





2 Signal (+) Solenoid 12
3 com (–)
4 Signal (+) Solenoid 14

Dimensions

Download CAD data ➔ www.festo.com



















[1] Plug, 3-pin
[2] Manual override
[3] Captive screws M5x48
[4] Slot for inscription label
[5] LED
















Type	B1	B2	D1	H1	H2	H3	H4	H5	L1	L2	L3	L4	L5
VSVA-B -...-D1-1R5L	42	28	M5	58.3	48	0.25	46.6	55.3	137.8	32	36	18	69.3

Ordering data – Width 42 mm

Ordering data

Circuit symbol	Description	Flow direction	Pilot air supply	Part no.	Type
2x 2/2-way valve					
	2x normally closed, Pneumatic spring return	Not reversible	Internal	Order via online configurator a Internet: vsva	
	2x normally closed, Pneumatic spring return	Not reversible	External		
	2x normally closed, vacuum operation possible at 3 and 5, Pneumatic spring return	Any	Internal		
2x 3/2-way valve					
	2x normally closed, Pneumatic spring return	Not reversible	Internal	**561359**	**VSVA-B-T32C-AD-D1-1R5L**
	2x normally closed, Pneumatic spring return	Not reversible	External	**561369**	**VSVA-B-T32C-AZD-D1-1R5L**
	2x normally open, Pneumatic spring return	Not reversible	Internal	**561360**	**VSVA-B-T32U-AD-D1-1R5L**
	2x normally open, Pneumatic spring return	Not reversible	External	**561370**	**VSVA-B-T32U-AZD-D1-1R5L**
	1x normally closed, 1x normally open, Pneumatic spring return	Not reversible	Internal	**561361**	**VSVA-B-T32H-AD-D1-1R5L**
	1x normally closed, 1x normally open, Pneumatic spring return	Not reversible	External	**561371**	**VSVA-B-T32H-AZD-D1-1R5L**
2x 3/2-way valve, reversible					
	2x normally closed, Pneumatic spring return	Only reversible	External	Order via online configurator a Internet: vsva	
	2x normally open, Pneumatic spring return	Only reversible	External		
	1x normally closed, 1x normally open, Pneumatic spring return	Only reversible	External		


Ordering data – Width 42 mm

Ordering data Circuit symbol	Description	Flow direction	Pilot air supply	Part no.	Type
5/2-way valve, single solenoid					
	Pneumatic spring return	Not reversible	Internal	**561362**	**VSVA-B-M52-AD-D1-1R5L**
	Mechanical spring return	Not reversible	Internal	**561363**	**VSVA-B-M52-MD-D1-1R5L**
	Pneumatic spring return	Any	External	**561372**	**VSVA-B-M52-AZD-D1-1R5L**
	Mechanical spring return	Any	External	**561373**	**VSVA-B-M52-MZD-D1-1R5L**
5/2-way valve, double solenoid					
	Dominance at 1st signal	Not reversible	Internal	**561364**	**VSVA-B-B52-D-D1-1R5L**
	Dominance at 1st signal	Any	External	**561374**	**VSVA-B-B52-ZD-D1-1R5L**
	With dominant signal at 14	Not reversible	Internal	**561365**	**VSVA-B-D52-D-D1-1R5L**
	With dominant signal at 14	Any	External	**561375**	**VSVA-B-D52-ZD-D1-1R5L**
	Timer valve; port 12 switches automatically after a specific time that can be set on the valve	Any	External	**8037117**	**VSVA-B-TR1-B52-ZD-D1-1R5L**
5/3-way valve					
	Normally closed, Mechanical spring return	Not reversible	Internal	**561366**	**VSVA-B-P53C-D-D1-1R5L**
	Normally closed, Mechanical spring return	Any	External	**561376**	**VSVA-B-P53C-ZD-D1-1R5L**
	Normally open, Mechanical spring return	Not reversible	Internal	**561368**	**VSVA-B-P53U-D-D1-1R5L**
	Normally open, Mechanical spring return	Any	External	**561378**	**VSVA-B-P53U-ZD-D1-1R5L**
	Normally exhausted, Mechanical spring return	Not reversible	Internal	**561367**	**VSVA-B-P53E-D-D1-1R5L**
	Normally exhausted, Mechanical spring return	Any	External	**561377**	**VSVA-B-P53E-ZD-D1-1R5L**

Datasheet – Width 52 mm

- Flow rate
Up to 2800 l/min

- Voltage
24 V DC



General technical data		
Design		Piston spool
Sealing principle		Soft
Actuation type		Electrical
Type of control		Piloted
Exhaust air function		Can be throttled, externally or via vertically stacked throttle plate
Manual override		Non-detenting, detenting
Type of mounting		On sub-base
Mounting position		Any
Nominal width	[mm]	15
Overlap		Positive overlap
Width	[mm]	52
Grid dimension	[mm]	59
Conforms to standard		ISO 5599-1
Certification		c CSA us (OL)
		c UL us – Recognized (OL)
		C-Tick

Pneumatic ports			
		Internal pilot air supply	External pilot air supply
Pneumatic connection	1, 2, 4, 3, 5	Sub-base size 2 to ISO 5599-1	Sub-base size 2 to ISO 5599-1
Pilot air port	12/14	–	Sub-base size 2 to ISO 5599-1
Pilot exhaust air port	82/84	–	Either: Not ducted as per standard, or ducted

Flow rates					
Valve function		2/2-way valve	3/2-way valve	5/2-way valve	5/3-way valve
Standard nominal flow rate	[l/min]	2800	2200	2800	2700
Valve		4000	3000	4000	3600
Valve on individual sub-base		2400	2000	2400	2300
Pneumatically linked valve		2800	2200	2800	2700

Switching times [ms]					
		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
2x 2/2-way valve	VSVA-B-T22...	14	35	–	–
2x 3/2-way valve	VSVA-B-T32...	20	35	–	–
2x 3/2-way valve, reversible	VSVA-B-T32...	30	30	–	–
5/2-way valve, single solenoid	VSVA-B-M52-A...	40	45	–	–
	VSVA-B-M52-M...	20	60	–	–
5/2-way valve, double solenoid	VSVA-B-B52...	–	–	18	–
	VSVA-B-D52...	–	–	–	18
5/3-way valve	VSVA-B-P53...	23	60	–	–

Datasheet – Width 52 mm

Operating and environmental conditions							
Valve function			2x 2/2-way valve	2x 3/2-way valve	2x 3/2-way valve, reversible	5/2-way valve	5/3-way valve
Operating medium			Compressed air to ISO 8573-1:2010 [7:4:4]				
Pilot medium			Compressed air to ISO 8573-1:2010 [7:4:4]				
Note on the operating/pilot medium			Lubricated operation possible (in which case lubricated operation will always be required)				
Operating pressure	Internal pilot air supply	[MPa]	0.3 ... 1	0.3 ... 1	–	0.3 ... 1	0.3 ... 1
		[bar]	3 ... 10	3 ... 10	–	3 ... 10	3 ... 10
	External pilot air supply	[MPa]	0.3 ... 1	0.3 ... 1	–0.09 ... +1	–0.09 ... +1.6	–0.09 ... +1.6
		[bar]	3 ... 10	3 ... 10	–0.9 ... +10	–0.9 ... +16	–0.9 ... +16
Pilot pressure		[MPa]	0.3 ... 1				
		[bar]	3 ... 10				
Ambient temperature		[°C]	–5 ... +50				
Relative humidity		[%]	0 ... 90				
CE marking (see declaration of conformity)			To EU EMC Directive[1]				
UKCA marking (see declaration of conformity)[1]			To UK EMC regulations				
			To UK RoHS regulations				
KC marking			KC EMC				

1) For information about the area of use, see the EC declaration of conformity at: www.festo.com/catalogue/... d Support/Downloads.
If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

Safety characteristics		
Max. positive test pulse with 0 signal	[µs]	1000
Max. negative test pulse with logic 1	[µs]	3500
Shock resistance		Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Vibration resistant		Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6

Electrical data			
Electrical connection			Central plug, round design M12x1, 3-pin
Signal status indication			LED
Characteristic coil values	Voltage	[V DC]	24
	Power	[W]	4.6
Permissible voltage fluctuations		[%]	±10
Nominal pick-up current per solenoid coil		[mA]	165
Nominal current with current reduction		[mA]	35
Time until current reduction		[ms]	30
Duty cycle		[%]	100
Degree of protection to EN 60529			IP65, NEMA4 (in combination with a plug socket)


Materials	
Housing	Die-cast aluminium, PA
Seals	HNBR, NBR, FPM
Screws	Galvanised steel
Note on materials	RoHs-compliant
LABS (PWIS) conformity	VDMA24364-B1/B2-L

Product weight		
2x 2/2-way valve	[g]	740
2x 3/2-way valve	[g]	740
5/2-way valve, single solenoid	[g]	702
5/2-way valve, double solenoid	[g]	732
5/3-way valve	[g]	780


Datasheet – Width 52 mm

Pilot pressure p12/14 as a function of working pressure p1

2x 2/2-way valve and 2x 3/2-way valve




5/2-way valve and 5/3-way valve, external pilot air supply



Protective circuit


Each solenoid coil VSVA is provided with a spark arresting protective circuit and protected against polarity reversal.

24 V DC version



[1] Holding current reduction


M12x1 – Pin allocation on the valve



2 Signal (+) Solenoid 12
3 com (–)
4 Signal (+) Solenoid 14

Dimensions












Download CAD data ➔ www.festo.com



[1] Plug, 3-pin
[2] Manual override
[3] Captive screws M6x60
[4] Slot for inscription label
[5] LED















Type	B1	B2	D1	H1	H2	H3	H4	H5	L1	L2	L3	L4	L5
VSVA-B -...-D2-1R5L	52	38	M6	58.3	60	0.3	56.4	55.3	160.7	40.9	48	24	64.3

Ordering data – Width 52 mm

Ordering data Circuit symbol	Description	Flow direction	Pilot air supply	Part no.	Type
2x 2/2-way valve					
	2x normally closed, Pneumatic spring return	Not reversible	Internal	Order via online configurator a Internet: vsva	
	2x normally closed, Pneumatic spring return	Not reversible	External		
2x 3/2-way valve					
	2x normally closed, Pneumatic spring return	Not reversible	Internal	**566990**	**VSVA-B-T32C-AD-D2-1R5L**
	2x normally closed, Pneumatic spring return	Not reversible	External	**567000**	**VSVA-B-T32C-AZD-D2-1R5L**
	2x normally open, Pneumatic spring return	Not reversible	Internal	**566991**	**VSVA-B-T32U-AD-D2-1R5L**
	2x normally open, Pneumatic spring return	Not reversible	External	**567001**	**VSVA-B-T32U-AZD-D2-1R5L**
	1x normally closed, 1x normally open, Pneumatic spring return	Not reversible	Internal	**566992**	**VSVA-B-T32H-AD-D2-1R5L**
	1x normally closed, 1x normally open, Pneumatic spring return	Not reversible	External	**567002**	**VSVA-B-T32H-AZD-D2-1R5L**
2x 3/2-way valve, reversible					
	2x normally closed, Pneumatic spring return	Reversible	External	Order via online configurator a Internet: vsva	
	2x normally open, Pneumatic spring return	Reversible	External		
	1x normally closed, 1x normally open, Pneumatic spring return	Reversible	External		

Ordering data – Width 52 mm


Ordering data

Circuit symbol	Description	Flow direction	Pilot air supply	Part no.	Type
5/2-way valve, single solenoid					
	Pneumatic spring return	Not reversible	Internal	**566993**	**VSVA-B-M52-AD-D2-1R5L**
	Pneumatic spring return	Reversible	External	**567003**	**VSVA-B-M52-AZD-D2-1R5L**
	Mechanical spring return	Not reversible	Internal	**566994**	**VSVA-B-M52-MD-D2-1R5L**
	Mechanical spring return	Reversible	External	**567004**	**VSVA-B-M52-MZD-D2-1R5L**
5/2-way valve, double solenoid					
	Dominance at 1st signal	Not reversible	Internal	**566995**	**VSVA-B-B52-D-D2-1R5L**
	Dominance at 1st signal	Reversible	External	**567005**	**VSVA-B-B52-ZD-D2-1R5L**
	With dominant signal at 14	Not reversible	Internal	**566996**	**VSVA-B-D52-D-D2-1R5L**
	With dominant signal at 14	Reversible	External	**567006**	**VSVA-B-D52-ZD-D2-1R5L**
5/3-way valve					
	Normally closed, Mechanical spring return	Not reversible	Internal	**566997**	**VSVA-B-P53C-D-D2-1R5L**
	Normally closed, Mechanical spring return	Reversible	External	**567007**	**VSVA-B-P53C-ZD-D2-1R5L**
	Normally open, Mechanical spring return	Not reversible	Internal	**566999**	**VSVA-B-P53U-D-D2-1R5L**
	Normally open, Mechanical spring return	Reversible	External	**567009**	**VSVA-B-P53U-ZD-D2-1R5L**
	Normally exhausted, Mechanical spring return	Not reversible	Internal	**566998**	**VSVA-B-P53E-D-D2-1R5L**
	Normally exhausted, Mechanical spring return	Reversible	External	**567008**	**VSVA-B-P53E-ZD-D2-1R5L**

Datasheet – Width 65 mm

- Flow rate
Up to 4600 l/min

- Voltage
24 V DC



General technical data		
Design		Piston spool
Sealing principle		Soft
Actuation type		Electrical
Type of control		Piloted
Flow direction		Not reversible
Exhaust air function		Can be throttled
Manual override		Non-detenting
Type of mounting		With through-hole
Mounting position		Any
Nominal width	[mm]	14.5
Width	[mm]	65
Grid dimension	[mm]	71
Conforms to standard		ISO 5599-1

Pneumatic ports				
		5/2-way valve	5/2-way valve, double solenoid	5/3-way valve
Pneumatic connection	1, 2, 4, 3, 5	Sub-base size 3 to ISO 5599-1	Sub-base size 3 to ISO 5599-1	Sub-base size 3 to ISO 5599-1
Pilot exhaust air port	82	–	Not ducted	Not ducted
	84	Not ducted	Not ducted	Not ducted

Flow rates					
Valve function		5/2-way valve	5/3-way valve		
			Normally closed	Normally exhausted	Normally open
Standard nominal flow rate	[l/min]	4500	4100	4600	4000

Switching times [ms]					
		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
5/2-way valve, single solenoid	MEBH-5/2-...	59	87	–	–
	MEBH-5/2-D-1-ZSR-FR-...	28	109	–	–
5/2-way valve, double solenoid	JMEBH-...	–	–	16	–
	JMEBDH-...	–	–	–	20
5/3-way valve	MEBH-5/3G-...	38	130	–	–
	MEBH-5/3E-...	38	130	–	–
	MEBH-5/3B-...	38	130	–	–

Datasheet – Width 65 mm


Operating and environmental conditions				
Reset method			Pneumatic spring	Mechanical spring
Operating medium			Compressed air to ISO 8573-1:2010 [7:4:4]	
Pilot medium			Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on the operating/pilot medium			Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure		[MPa]	0.2 ... 1	0.3 ... 1
		[bar]	2 ... 10	3 ... 10
Ambient temperature		[°C]	–5 ... +50	
Temperature of medium		[°C]	–5 ... +50	
Relative humidity		[%]	0 ... 90	


Electrical data			
Electrical connection			Central plug, round design M12x1, 4-pin
Characteristic coil values	Voltage	[V DC]	24
	Power	[W]	2.5
Degree of protection to EN 60529			IP65

Materials	
Housing	Die-cast aluminium
Seals	NBR
LABS (PWIS) conformity	VDMA24364-B1/B2-L

Datasheet – Width 65 mm

Dimensions – 5/2-way valves, single solenoid Download CAD data ➔ www.festo.com






[1] Plug socket mounting adjustable by 3x30°
[2] Manual override
[3] Captive retaining screws
[4] LED indicator
[5] Angled plug socket NECB d page 166

Type	B1	B2	B3	B4	D1	D2	H1	H2	H3	H4	H5	L1	L2	L3	L4	L5	L6
MEBH-5/2 ...	65	48	12	17.5	M8	M12	130	97.8	55	12	93.1	158.7	145.4	72.7	64	32	86
MEBH-5/2- ... -FR-C												178	164.7				

Datasheet – Width 65 mm

Dimensions - 5/2-way valves, double solenoid, 5/3-way valves

Download CAD data ➔ www.festo.com



[1] Plug socket mounting adjustable by 3x30°

[2] Manual override

[3] Captive retaining screws

[4] LED indicator


[5] Angled plug socket NECB d page 166

Type	B1	B2	B3	B4	D1	D2	H1	H2	H3	H4	H5	L1	L2	L3	L4	L5	L6
JMEBH-5/2- ...	65	48	12	17.5	M8	M12	130	97.8	55	12	93.1	171.9	145.4	72.7	64	32	86
JMEBDH-5/2- ...													145.4	72.7			
MEBH-5/3...													184	92			

Ordering data – Width 65 mm


Central plug M12 – Pin allocation

5/2-way valve, single solenoid










1 Not assigned
2 Not assigned
3 com (–)
4 Signal (+) Solenoid 14

5/2-way valve, double solenoid, and 5/3-way valve



1 Not assigned
2 Signal (+) Solenoid 12
3 com (–)
4 Signal (+) Solenoid 14


Ordering data

Circuit symbol	Description	Pilot air supply	Weight [g]	Part no.	Type
5/2-way valve, single solenoid					
	Pneumatic spring return	Internal	1000	**184507**	**MEBH-5/2-D-3-ZSR-C**
	Mechanical spring return	Internal	1000	**184508**	**MEBH-5/2-D-3-ZSR-FR-C**
5/2-way valve, double solenoid					
	–	Internal	1080	**184509**	**JMEBH-5/2-D-3-ZSR-C**
	With dominant signal at 14	Internal	1080	**184510**	**JMEBDH-5/2-D-3-ZSR-C**
5/3-way valve					
	Normally closed, Mechanical spring return	Internal	1120	**184512**	**MEBH-5/3G-D-3-ZSR-C**
	Normally exhausted, Mechanical spring return	Internal	1120	**184511**	**MEBH-5/3E-D-3-ZSR-C**
	Normally open, Mechanical spring return	Internal	1120	**184513**	**MEBH-5/3B-D-3-ZSR-C**

Datasheet – Width 42 mm

- Flow rate
Up to 1200 l/min

- Voltage
24 V DC



General technical data			
Design			Piston spool
Sealing principle			Soft
Actuation type			Electrical
Type of control			Piloted
Flow direction	With external pilot air supply		Reversible
	With internal pilot air supply		Not reversible
Exhaust air function			Can be throttled
Manual override			Non-detenting
Type of mounting			On sub-base with through-hole
Mounting position			Any
Nominal width		[mm]	8
Overlap			Positive overlap
Width		[mm]	42
Grid dimension		[mm]	43
Noise level		[dB (A)]	85
Conforms to standard			ISO 5599-1

Pneumatic ports			
		Internal pilot air supply	External pilot air supply
Pneumatic connection	1, 2, 4, 3, 5	Sub-base size 1 to ISO 5599-1	Sub-base size 1 to ISO 5599-1
Pilot air port	12	–	Connecting plate
	14	–	Connecting plate
Pilot exhaust air port	82	–	–
	84	–	–

Flow rates			
Standard nominal flow rate		[l/min]	1200

Switching times [ms]					
		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
5/2-way valve, single solenoid	MDH-5/2-...	25	36	–	–
	MDH-5/2-...-FR-...	20	42	–	–
5/2-way valve, double solenoid	JMDH-...	–	–	18	–
	JMDDH-...	–	–	18	18
5/3-way valve	MDH-5/3G-...	25	55	–	–
	MDH-5/3E-...	25	55	–	–
	MDH-5/3B-...	25	55	–	–

Datasheet – Width 42 mm

Operating and environmental conditions				
Reset method			Pneumatic spring	Mechanical spring
Operating medium			Compressed air to ISO 8573-1:2010 [7:4:4]	
Pilot medium			Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on the operating/pilot medium			Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure	Internal pilot air supply	[bar]	2 ... 10	3 ... 10
	External pilot air supply	[bar]	–0.9 ... +16	–0.9 ... +16
Pilot pressure	Internal pilot air supply	[bar]	2 ... 10	3 ... 10
	External pilot air supply	[bar]	3 ... 10	3 ... 10
Ambient temperature		[°C]	–10 ... +50	
Temperature of medium		[°C]	–10 ... +50	

Safety characteristics		
Max. positive test pulse with 0 signal	[µs]	3800
Max. negative test pulse with logic 1	[µs]	4900
Shock resistance		Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Vibration resistant		Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6


Electrical data			
Electrical connection			M12x1
Characteristic coil values	Voltage	[V DC]	24
	Power	[W]	2.7
Permissible voltage fluctuations		[%]	±10
Duty cycle		[%]	100
Degree of protection to EN 60529			IP65


Materials	
Housing	Die-cast aluminium
Seals	HNBR, NBR
LABS (PWIS) conformity	VDMA24364-B1/B2-L

Datasheet – Width 42 mm

Dimensions – 5/2-way valves, single solenoid

Download CAD data ➔ www.festo.com






[1] Solenoid coil can be turned 90° regardless of the manual override
[2] Manual override
[3] Captive retaining screws
[4] Slot for inscription label
[5] LED indicator
[6] Device plug M12x1
2-pin coil to VDMA
4-pin coil to Desina

Type	B1	B2	B3	B4	D1	H1	H2	H3	H4	H5	L1	L2	L3	L4	L5	L6
MDH-5/2 ...	42	28	6	30	M5	87.2	77.2	38	9	46.5	121.8	87.6	43.8	36	18	–
MDH-5/2- ... -FR-...											132.2	98				

Datasheet – Width 42 mm

Dimensions - 5/2-way valves, double solenoid, 5/3-way valves

Download CAD data ➔ www.festo.com



[1] Solenoid coil can be turned 90° regardless of the manual override

[2] Manual override

[3] Captive retaining screws

[4] LED indicator


[5] Device plug M12x1
2-pin coil to VDMA
4-pin coil to Desina

Type	B1	B2	B3	B4	D1	H1	H2	H3	H4	H5	L1	L2	L3	L4	L5	L6
JMDH-5/2- ...	42	28	6	30	M5	87.2	77.2	38	9	–	148	87.6	43.8	36	18	108.5
JMDDH-5/2- ...												87.6	43.8			
MDH-5/3...												108.4	54.3			

Ordering data – Width 42 mm


Terminal assignment

M12 plug – 2-pin to VDMA












1 Not assigned
2 Not assigned
3 com (–)
4 Signal (+)

M12 plug – 4-pin to Desina



1 Connected to 2
2-Connected to 1
3 com (–)
4 Signal (+)


Ordering data – Solenoid valves

Circuit symbol	Description	Coil	Pilot air supply	Weight [g]	Part no.	Type
5/2-way valve, single solenoid						
	Pneumatic spring return	2-pin to VDMA	Internal	420	**197125**	**MDH-5/2-D-1-M12-C**
		4-pin to Desina	Internal	420	**540803**	**MDH-5/2-D-1-M12D-C**
	Pneumatic spring return	2-pin to VDMA	External	420	**533332**	**MDH-5/2-D-1-S-M12-C**
		4-pin to Desina	External	420	**540810**	**MDH-5/2-D-1-S-M12D-C**
	Mechanical spring return	2-pin to VDMA	Internal	420	**533010**	**MDH-5/2-D-1-FR-M12-C**
		4-pin to Desina	Internal	420	**540804**	**MDH-5/2-D-1-FR-M12D-C**
	Mechanical spring return	2-pin to VDMA	External	420	**533761**	**MDH-5/2-D-1-S-FR-M12-C**
		4-pin to Desina	External	420	**540811**	**MDH-5/2-D-1-S-FR-M12D-C**
5/2-way valve, double solenoid						
	–	2-pin to VDMA	Internal	550	**532687**	**JMDH-5/2-D-1-M12-C**
		4-pin to Desina	Internal	550	**540809**	**JMDH-5/2-D-1-M12D-C**
	With dominant signal at 14	2-pin to VDMA	Internal	550	**539079**	**JMDDH-5/2-D-1-M12-C**
		4-pin to Desina	Internal	550	**540808**	**JMDDH-5/2-D-1-M12D-C**
5/3-way valve						
	Normally closed, mechanical spring return	2-pin to VDMA	Internal	580	**525307**	**MDH-5/3G-D-1-M12-C**
		4-pin to Desina	Internal	580	**540806**	**MDH-5/3G-D-1-M12D-C**
	Normally exhausted, Mechanical spring return	2-pin to VDMA	Internal	580	**197126**	**MDH-5/3E-D-1-M12-C**
		4-pin to Desina	Internal	580	**540805**	**MDH-5/3E-D-1-M12D-C**
	Normally open, Mechanical spring return	2-pin to VDMA	Internal	580	**533005**	**MDH-5/3B-D-1-M12-C**
		4-pin to Desina	Internal	580	**540807**	**MDH-5/3B-D-1-M12D-C**

Datasheet – Width 52 mm

- Flow rate
Up to 2300 l/min

- Voltage
24 V DC



General technical data		
Design		Piston spool
Sealing principle		Soft
Actuation type		Electrical
Type of control		Piloted
Flow direction		Not reversible
Exhaust air function		Can be throttled
Manual override		Non-detenting
Type of mounting		On sub-base with through-hole and screw
Mounting position		Any
Nominal width	[mm]	11.5
Overlap		Positive overlap
Width	[mm]	52
Grid dimension	[mm]	56
Noise level	[dB (A)]	85
Conforms to standard		ISO 5599-1

Pneumatic ports		5/2-way valve	5/2-way valve, double solenoid	5/3-way valve
Pneumatic connection	1, 2, 4, 3, 5	Sub-base size 2 to ISO 5599-1	Sub-base size 2 to ISO 5599-1	Sub-base size 2 to ISO 5599-1
Pilot exhaust air port	82	–	M5	M5
	84	M5	M5	M5

Flow rates		
Standard nominal flow rate	[l/min]	2300

Switching times [ms]		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
5/2-way valve, single solenoid	MDH-5/2-...	45	60	–	–
	MDH-5/2-...-FR-...	25	60	–	–
5/2-way valve, double solenoid	JMDH-...	–	–	20	–
	JMDDH-...	–	–	20	20
5/3-way valve	MDH-5/3G-...	35	70	–	–
	MDH-5/3E-...	35	70	–	–
	MDH-5/3B-...	35	70	–	–

Datasheet – Width 52 mm

Operating and environmental conditions				
Reset method			Pneumatic spring	Mechanical spring
Operating medium			Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on the operating/pilot medium			Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure		[bar]	2 ... 10	3 ... 10
Ambient temperature		[°C]	–10 ... +50	
Temperature of medium		[°C]	–10 ... +50	

Safety characteristics			
Max. positive test pulse with 0 signal		[µs]	3800
Max. negative test pulse with logic 1		[µs]	4900
Shock resistance			Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Vibration resistant			Transport application test with severity level 1 to FN 942017-4 and EN 60068-26


Electrical data			
Electrical connection			M12x1
Characteristic coil values	Voltage	[V DC]	24
	Power	[W]	2.7
Permissible voltage fluctuations		[%]	±10
Duty cycle		[%]	100
Degree of protection to EN 60529			IP65


Materials	
Housing	Die-cast aluminium
Seals	HNBR, NBR
Note on materials	RoHs-compliant
LABS (PWIS) conformity	VDMA24364-B1/B2-L

Datasheet – Width 52 mm

Dimensions – 5/2-way valves, single solenoid

Download CAD data ➔ www.festo.com






[1] Solenoid coil can be turned 90° regardless of the manual override
[2] Manual override
[3] Captive retaining screws
[4] Slot for inscription label
[5] LED indicator
[6] Device plug M12x1
2-pin coil to VDMA
4-pin coil to Desina

Type	B1	B2	B3	B4	D1	H1	H2	H3	H4	H5	L1	L2	L3	L4	L5	L6
MDH-5/2 ...	54	38	9	30	M6	97.2	87.2	48	9.5	56.5	144.6	123.4	61.7	48	24	–
MDH-5/2- ... -FR-...											161.9	140.6				

Datasheet – Width 52 mm

Dimensions - 5/2-way valves, double solenoid, 5/3-way valves

Download CAD data ➔ www.festo.com



[1] Solenoid coil can be turned 90° regardless of the manual override

[2] Manual override

[3] Captive retaining screws

[4] LED indicator


[5] Device plug M12x1
2-pin coil to VDMA
4-pin coil to Desina

Type	B1	B2	B3	B4	D1	H1	H2	H3	H4	H5	L1	L2	L3	L4	L5	L6
JMDH-5/2- ...	54	38	9	30	M6	97.2	87.2	48	9.5	–	165.8	123.4	61.7	48	24	126.3
JMDDH-5/2- ...												123.4	61.7			
MDH-5/3...												158	79			

Ordering data – Width 52 mm


Terminal assignment

M12 plug – 2-pin to VDMA










1 Not assigned
2 Not assigned
3 com (–)
4 Signal (+)

M12 plug – 4-pin to Desina



1 Connected to 2
2-Connected to 1
3 com (–)
4 Signal (+)


Ordering data

Circuit symbol	Description	Coil	Pilot air supply	Weight [g]	Part no.	Type
5/2-way valve, single solenoid						
	Pneumatic spring return	2-pin to VDMA	Internal	810	**533008**	**MDH-5/2-D-2-M12-C**
		4-pin to Desina	Internal	810	**540812**	**MDH-5/2-D-2-M12D-C**
	Mechanical spring return	2-pin to VDMA	Internal	810	**533011**	**MDH-5/2-D-2-FR-M12-C**
		4-pin to Desina	Internal	810	**540813**	**MDH-5/2-D-2-FR-M12D-C**
5/2-way valve, double solenoid						
	–	2-pin to VDMA	Internal	940	**533013**	**JMDH-5/2-D-2-M12-C**
		4-pin to Desina	Internal	940	**540818**	**JMDH-5/2-D-2-M12D-C**
	With dominant signal at 14	2-pin to VDMA	Internal	940	**539077**	**JMDDH-5/2-D-2-M12-C**
		4-pin to Desina	Internal	940	**540817**	**JMDDH-5/2-D-2-M12D-C**
5/3-way valve						
	Normally closed, mechanical spring return	2-pin to VDMA	Internal	1000	**539078**	**MDH-5/3G-D-2-M12-C**
		4-pin to Desina	Internal	1000	**540815**	**MDH-5/3G-D-2-M12D-C**
	Normally exhausted, Mechanical spring return	2-pin to VDMA	Internal	1000	**533016**	**MDH-5/3E-D-2-M12-C**
		4-pin to Desina	Internal	1000	**540814**	**MDH-5/3E-D-2-M12D-C**
	Normally open, Mechanical spring return	2-pin to VDMA	Internal	1000	**533006**	**MDH-5/3B-D-2-M12-C**
		4-pin to Desina	Internal	1000	**540816**	**MDH-5/3B-D-2-M12D-C**

Datasheet – Width 65 mm

- Flow rate
Up to 4500 l/min

- Voltage
24 V DC



General technical data		
Design		Piston spool
Sealing principle		Soft
Actuation type		Electrical
Type of control		Piloted
Flow direction		Not reversible
Exhaust air function		Can be throttled
Manual override		Non-detenting
Type of mounting		On sub-base with through-hole and screw
Mounting position		Any
Nominal width	[mm]	14.5
Overlap		Positive overlap
Width	[mm]	65
Grid dimension	[mm]	71
Noise level	[dB (A)]	85
Conforms to standard		ISO 5599-1

Pneumatic ports		5/2-way valve	5/2-way valve, double solenoid	5/3-way valve
Pneumatic connection	1, 2, 4, 3, 5	Sub-base size 3 to ISO 5599-1	Sub-base size 3 to ISO 5599-1	Sub-base size 3 to ISO 5599-1
Pilot exhaust air port	82	–	M5	M5
	84	M5	M5	M5

Flow rates					
Valve function		5/2-way valve	5/3-way valve		
			Normally closed	Normally exhausted	Normally open
Standard nominal flow rate	[l/min]	4500	4100	4600	4000

Switching times [ms]		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
5/2-way valve, single solenoid	MDH-5/2-...	54	57	–	–
	MDH-5/2-...-FR-...	28	68	–	–
5/2-way valve, double solenoid	JMDH-...	–	–	21	–
	JMDDH-...	–	–	23	23
5/3-way valve	MDH-5/3G-...	35	79	–	–
	MDH-5/3E-...	36	84	–	–
	MDH-5/3B-...	36	84	–	–

Datasheet – Width 65 mm

Operating and environmental conditions				
Reset method			Pneumatic spring	Mechanical spring
Operating medium			Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on the operating/pilot medium			Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure		[bar]	2 ... 10	3 ... 10
Ambient temperature		[°C]	–10 ... +50	
Temperature of medium		[°C]	–10 ... +50	

Safety characteristics			
Max. positive test pulse with 0 signal		[µs]	3800
Max. negative test pulse with logic 1		[µs]	4900
Shock resistance			Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Vibration resistant			Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6


Electrical data			
Electrical connection			M12x1
Characteristic coil values	Voltage	[V DC]	24
	Power	[W]	2.7
Permissible voltage fluctuations		[%]	±10
Duty cycle		[%]	100
Degree of protection to EN 60529			IP65


Materials	
Housing	Die-cast aluminium
Seals	HNBR, NBR
Note on materials	RoHs-compliant
LABS (PWIS) conformity	VDMA24364-B1/B2-L

Datasheet – Width 65 mm

Dimensions – 5/2-way valves, single solenoid

Download CAD data ➔ www.festo.com






[1] Solenoid coil can be turned 90° regardless of the manual override
[2] Manual override
[3] Captive retaining screws
[4] Slot for inscription label
[5] LED indicator
[6] Device plug M12x1
2-pin coil to VDMA
4-pin coil to Desina

Type	B1	B2	B3	B4	D1	H1	H2	H3	H4	H5	L1	L2	L3	L4	L5	L6
MDH-5/2 ...	65	48	12	30	M8	104.2	94.2	55	12	62.5	165.9	145.4	72.7	64	32	–
MDH-5/2- ... -FR-...											182.5	140.6				

Datasheet – Width 65 mm

Dimensions - 5/2-way valves, double solenoid, 5/3-way valves

Download CAD data ➔ www.festo.com



[1] Solenoid coil can be turned 90° regardless of the manual override

[2] Manual override

[3] Captive retaining screws

[4] LED indicator


[5] Device plug M12x1
2-pin coil to VDMA
4-pin coil to Desina

Type	B1	B2	B3	B4	D1	H1	H2	H3	H4	H5	L1	L2	L3	L4	L5	L6
JMDH-5/2- ...	65	48	12	30	M8	104.2	94.2	55	12	–	186.4	145.4	72.7	64	32	146.9
JMDDH-5/2- ...												145.4	72.7			
MDH-5/3...												184	92			

Ordering data – Width 65 mm


Terminal assignment

M12 plug – 2-pin to VDMA










1 Not assigned
2 Not assigned
3 com (–)
4 Signal (+)

M12 plug – 4-pin to Desina



1 Connected to 2
2-Connected to 1
3 com (–)
4 Signal (+)

Ordering data

Circuit symbol	Description	Coil	Pilot air supply	Weight [g]	Part no.	Type
5/2-way valve, single solenoid						
	Pneumatic spring return	2-pin to VDMA	Internal	1000	**533009**	**MDH-5/2-D-3-M12-C**
		4-pin to Desina	Internal	1000	**540819**	**MDH-5/2-D-3-M12D-C**
	Mechanical spring return	2-pin to VDMA	Internal	1000	**533012**	**MDH-5/2-D-3-FR-M12-C**
		4-pin to Desina	Internal	1000	**540820**	**MDH-5/2-D-3-FR-M12D-C**
5/2-way valve, double solenoid						
	–	2-pin to VDMA	Internal	1100	**533015**	**JMDH-5/2-D-3-M12-C**
		4-pin to Desina	Internal	1100	**540825**	**JMDH-5/2-D-3-M12D-C**
	With dominant signal at 14	2-pin to VDMA	Internal	1100	**539081**	**JMDDH-5/2-D-3-M12-C**
		4-pin to Desina	Internal	1100	**540824**	**JMDDH-5/2-D-3-M12D-C**
5/3-way valve						
	Normally closed, mechanical spring return	2-pin to VDMA	Internal	1120	**539080**	**MDH-5/3G-D-3-M12-C**
		4-pin to Desina	Internal	1120	**540822**	**MDH-5/3G-D-3-M12D-C**
	Normally exhausted, Mechanical spring return	2-pin to VDMA	Internal	1120	**533017**	**MDH-5/3E-D-3-M12-C**
		4-pin to Desina	Internal	1120	**540821**	**MDH-5/3E-D-3-M12D-C**
	Normally open, Mechanical spring return	2-pin to VDMA	Internal	1120	**533007**	**MDH-5/3B-D-3-M12-C**
		4-pin to Desina	Internal	1120	**540823**	**MDH-5/3B-D-3-M12D-C**

Datasheet – Width 76 mm

- Flow rate
Up to 6000 l/min

- Repair service

- Voltage
24 V DC
48 V AC



General technical data		
Design		Piston spool
Sealing principle		Soft
Actuation type		Electrical
Type of control		Piloted
Flow direction		Not reversible
Exhaust air function		Can be throttled
Manual override		Non-detenting
Type of mounting		On sub-base with through-hole and screw
Mounting position		Any
Nominal width	[mm]	18
Overlap		Positive overlap
Width	[mm]	76
Grid dimension	[mm]	82
Noise level	[dB (A)]	85
Conforms to standard		ISO 5599-1

Pneumatic ports				
		5/2-way valve	5/2-way valve, double solenoid	5/3-way valve
Pneumatic connection	1, 2, 4, 3, 5	Sub-base size 4 to ISO 5599-1	Sub-base size 4 to ISO 5599-1	Sub-base size 4 to ISO 5599-1
Pilot exhaust air port	82	–	M5	M5
	84	M5	M5	M5

Flow rates			
Valve function		5/2-way valve	5/3-way valve
Standard nominal flow rate	[l/min]	6000	4800

Switching times [ms]				
		Switching time on	Switching time off	Switching time changeover
5/2-way valve	Monostable	120	160	–
	Bistable	–	–	40
5/3-way valve		85	290	–

Datasheet – Width 76 mm

Operating and environmental conditions				
Valve function			MDH-...-D-4-24DC, JMDH-...-D-4-24DC	MDH-...-D-4, JMDH-...-D-4
Operating medium			Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on the operating/pilot medium			Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure	5/2-way valve, single solenoid	[bar]	3 ... 16	
	5/2-way valve, double solenoid	[bar]	2 ... 16	
	5/3-way valve	[bar]	3 ... 16	
Ambient temperature		[°C]	–10 ... +50	
Temperature of medium		[°C]	–10 ... +60	
CE marking (see declaration of conformity)[1]			To EU Low Voltage Directive	–
UKCA marking (see declaration of conformity)[1]			To UK regulations for electrical equipment	–

1) More information www.festo.com/catalogue/... ➔ Support/Downloads.

Safety characteristics			
Type		MDH-...-D-4-24DC, JMDH-...-D-4-24DC	MDH-...-D-4, JMDH-...-D-4
Max. positive test pulse with 0 signal	[µs]	4300	–
Max. negative test pulse with logic 1	[µs]	2100	–

Electrical data – MDH-...-24DC, JMDH-...-24DC				
			DC voltage	Alternating voltage
Electrical connection			To DIN EN 175301-803	
Characteristic coil values	Voltage	[V DC]	24	–
		[V AC]	–	48
	Frequency	[Hz]	–	5 0/60
	Power	[W]	6.8	–
	Pick-up power	[VA]	–	14.5
	Holding power	[VA]	–	9.9
Duty cycle		[%]	100	
Degree of protection to EN 60529			IP65	


Electrical data – Pilot valve MDH-3/2-...												
Type			MDH-3/2-24DC			MDH-3/2-24DC/42AC			MDH-3/2-110AC		MDH-3/2-230AC	
Electrical connection			Plug, square design to EN 175301-803, type A									
Characteristic coil values	Voltage	[V DC]	24	–	–	24	–	–	–	–	110	–	–
		[V AC]	–	48	53	–	42	42	110	110	–	230	230
	Frequency	[Hz]	–	50	60	–	50	60	50	60	–	50	60
	Power	[W]	6.8	–	–	8.4	–	–	–	–	6.3	–	–
	Pick-up power	[VA]	–	14.5	15	–	14	12	14.5	12	–	14.5	12
	Holding power	[VA]	–	9.9	9.3	–	10	7	10.5	7.6	–	10.5	7.6
Permissible voltage fluctuations		[%]	±10	±10	±10	±10	±10	±10	±10	±10	±10	±10	±10
Permissible frequency fluctuations		[%]	–	–	–	±10	±10	±10	±10	±10	±10	±10	±10
Duty cycle		[%]	100										
Degree of protection to EN 60529			IP65										


Materials	
Housing	Aluminium
Seals	NBR
Note on materials	RoHs-compliant
LABS (PWIS) conformity	VDMA24364-B1/B2-L

Datasheet – Width 76 mm

Dimensions – 5/2-way valves, single solenoid

Download CAD data ➔ www.festo.com





[1] Connection for plug socket with plug pattern to EN 175301-803, type A d page 165

[2] Manual override

[3] Captive retaining screws


[4] Solenoid coil can be turned 90° regardless of the manual override


Type	B1	B2	D1	H1	H2	H3	H4	L1	L2	L3	L4	L5
MDH-5/2 ...	76	58	M8	139	110.5	74	14	182	67.5	80	40	81

Datasheet – Width 76 mm

Dimensions - 5/2-way valves, double solenoid, 5/3-way valves

Download CAD data ➔ www.festo.com





[1] Connection for plug socket with plug pattern to EN 175301-803, type A d page 165






[2] Manual override

[3] Captive retaining screws

[4] Solenoid coil can be turned 90° regardless of the manual override

Type	B1	B2	D1	H1	H2	H3	H4	L1	L2	L3	L4	L5
JMDH-5/2- ...	76	58	M8	139	110.5	74	14	182	135	80	40	162
MDH-5/3...												


Ordering data – Width 76 mm

Ordering data Circuit symbol	Description	Voltage	Pilot air supply	Weight [g]	Part no.	Type
5/2-way valve, single solenoid						
	Pneumatic spring return	24 V DC	Internal	2600	**12457**	**MDH-5/2-3/4-D-4-24DC**
		–	Internal	2600	**14544**	**MDH-5/2-3/4-D-4**[1]
5/2-way valve, double solenoid						
	–	24 V DC	Internal	2600	**12458**	**JMDH-5/2-3/4-D-4-24DC**
		–	Internal	2600	**14545**	**JMDH-5/2-3/4-D-4**[1]
5/3-way valve						
	Normally closed, mechanical spring return	24 V DC	Internal	2600	**12459**	**MDH-5/3G-3/4-D-4-24DC**
		–	Internal	2600	**14546**	**MDH-5/3G-3/4-D-4**[1]
	Normally exhausted, Mechanical spring return	24 V DC	Internal	2600	**12460**	**MDH-5/3E-3/4-D-4-24DC**
		–	Internal	2600	**14547**	**MDH-5/3E-3/4-D-4**[1]
Usable pilot valves						
	Electrical connection to EN 175301-803 type A	24 V DC	–	140	**119600**	**MDH-3/2-24DC**
		24 V DC/ 42 V AC	–	140	**119603**	**MDH-3/2-24DC/42AC**
		110 V AC	–	140	**119601**	**MDH-3/2-110AC**
		110 V DC/ 230 V AC	–	140	**119602**	**MDH-3/2-230AC**

1) Without pilot valve. The part number of the pilot valve must be added after the type code when ordering.
Order example: 14546 MDH-5/3G-3/4-D-4-119602 (for MDH-3/2-230AC with part no. 119602)

Peripherals overview

Valve on individual sub-base




Individual components

		Type	Brief description	→ Page/Internet
[1]	Connecting plate	VABS-S1-...	Pneumatic ports on the side	130
	Individual sub-base	NAS-...	Pneumatic ports on the side	130
		NAU-...	Pneumatic ports underneath	133
[2]	Silencer	U-...	For fitting in exhaust ports	silencer
[3]	Push-in fitting	QS-...	For connecting tubing with standard O.D.	qs
[4]	Pneumatic valve	VL-...	Hole pattern to ISO 5599-1	111
		J-...	Hole pattern to ISO 5599-1	111
		JD-...	Hole pattern to ISO 5599-1	111

Peripherals overview

Manifold assembly




Individual components

		Type	Brief description	→ Page/Internet
[1]	End plates	VABE-S1-...	For sealing the manifold sub-bases	142
[2]	Manifold sub-base	VABV-S1-...	With ports 2 and 4	135
[3]	Duct separation	VABD-S1-1-...	For sealing ducts 1, 3, 5, 12 and 14 between end plate and manifold sub-base, e.g. to create pressure zones	146
[4]	Supply plate	VABF-S1-1-...	With ports for air supply 1 and exhausts 3 and 5	137
[5]	Silencer	U-...	For fitting in exhaust ports	silencer
[6]	Push-in fitting	QS-...	For connecting tubing with standard O.D.	qs
[7]	Regulator plate	VABF-S1-...-R...	Pressure regulator for manually setting a particular pressure in the regulated port upstream or downstream of the valve	157
		LR-ZP-...	Pressure regulator for manually setting a particular pressure in the regulated port upstream or downstream of the valve	157
[8]	Pneumatic valve	VL-...	Hole pattern to ISO 5599-1	111
		J-...	Hole pattern to ISO 5599-1	111
		JD-...	Hole pattern to ISO 5599-1	111
[9]		VSPA	Hole pattern to ISO 5599-1	111
[10]	Cover plate	NDV-...	For sealing unused manifold sub-bases	145
[11]	Throttle plate	VABF-S1-...-F1B1-C	Restricts the flow of exhaust air in ducts 3 and 5	150
		GRO-ZP-...	Restricts the flow of exhaust air in ducts 3 and 5	150

Peripherals overview

Manifold assembly




Peripherals overview

Individual components

		Type	Brief description	→ Page/Internet
[1]	End plate kit	NEV-...	For sealing the manifold sub-bases	141
[2]	Manifold sub-base	NAV-...	With ports 2 and 4 underneath	135
[3]	Intermediate plate	NZV-...	For connecting manifold sub-bases of different sizes	147
[4]	Isolating disc	NSC-...	For sealing ducts 1, 3, 5 between end plate and manifold sub-base, e.g. to create pressure zones	145
[5]	Manifold sub-base with angled connections	NAW-...	For routing ports 2 and 4 to the front	140
[6]	Push-in fitting	QS-...	For connecting tubing with standard O.D.	qs
[7]	Manifold sub-base with angled connections	NAVW-...	With ports 2 and 4 either underneath or at the front	140
[8]	Silencer	U-...	For fitting in exhaust ports	silencer
[9]	Regulator plate	VABF-S1-...-R...	Pressure regulator for manually setting a particular pressure in the regulated port upstream or downstream of the valve	157
		LR-ZP-...	Pressure regulator for manually setting a particular pressure in the regulated port upstream or downstream of the valve	157
[10]	Pneumatic valve	VL-...	Hole pattern to ISO 5599-1	111
		J-...	Hole pattern to ISO 5599-1	111
		JD-...	Hole pattern to ISO 5599-1	111
[11]		VSPA	Hole pattern to ISO 5599-1	111
[12]	Throttle plate	VABF-S1-...-F1B1-C	Restricts the flow of exhaust air in ducts 3 and 5	150
		GRO-ZP-...	Restricts the flow of exhaust air in ducts 3 and 5	150
[13]	Cover plate	NDV-...	For sealing unused manifold sub-bases	145

Datasheet – Width 42 mm

- Flow rate
  1200 l/min
  1400 ... 1800 l/min



General technical data

Type		VL- ... -C, J ... -C	VL- ... -EX, J ... -EX	VSPA
Design		Piston spool	Piston spool	Piston spool
Sealing principle		Soft	Soft	Soft
Actuation type		Pneumatic	Pneumatic	Pneumatic
Type of control		Direct	Direct	Direct
Pilot air supply		–	–	External
Flow direction		Reversible	Reversible	Reversible
		VL-5/2-D-1-C: non-reversible	VL-5/2-D-1-C-EX: non-reversible	3/2-way valves: not reversible
Exhaust air function		Can be throttled	Can be throttled	Via individual sub-base
Suitable for vacuum		–	–	Yes
				Pneumatic spring return: none
Manual override		None	None	–
Type of mounting		On sub-base with through-hole	On sub-base with through-hole	On sub-base
Mounting position		Any	Any	Any
Max. tightening torque for valve mounting	[Nm]	–	–	1
Nominal width	[mm]	8	8	8
Overlap		Positive overlap	Positive overlap	Positive overlap
Width	[mm]	42	42	42
Grid dimension	[mm]	43	43	–
Pneumatic ports		Sub-base size 1 to ISO 5599-1	Sub-base size 1 to ISO 5599-1	Sub-base size 1 to ISO 5599-1
Noise level	[dB (A)]	85	85	85
Conforms to standard		ISO 5599-1	ISO 5599-1	–

Flow rates

		Standard nominal flow rate (standardised to DIN 1343) [l/min]	Nominal flow rate standardised according to ISO 8778 [l/min]	Flow rate of valve [l/min]	Flow rate of valve on individual sub-base [l/min]	b value	C value [l/sbar]
VL- ... -C		1200	–	–	–	–	–
J ... -C		1200	–	–	–	–	–
VL- ... -EX		1200	–	–	–	–	–
J ... -EX		1200	–	–	–	–	–
VSPA	2x 3/2-way valve, normally closed	–	1400	1300	1100	0.18	5293
	2x 3/2-way valve, normally open	–	1400	1300	1100	0.21	5511
	2x3/2-way valve, normally open/closed	–	1400	1300	1100	0.2	5479
	5/2-way valve, single solenoid, pneumatic spring	–	1800	1700	1400	1.6	7706
	5/2-way valve, single solenoid, mechanical spring	–	1800	1700	1400	1.7	7718
	5/2-way valve, double solenoid	–	1800	1700	1400	1.6	7697
	5/2-way valve, bistable, with dominant signal	–	1800	1700	1400	1.5	7663
	5/3-way valve, mid-position closed	–	1800	1600	1400	0.14	7482
	5/3-way valve, mid-position exhausted	–	1800	1600	1400	0.24	7141
	5/3-way valve, mid-position pressurised	–	1600	1500	1300	0.14	6799

Datasheet – Width 42 mm

Switching times [ms]

		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
2x3/2-way valve	VSPA	–	–	–	–
5/2-way valve, single solenoid	VL-5/2-D-1-C	9	18	–	–
	VL-5/2-D-1-C-EX	9	18	–	–
	VL-5/2-D-1-FR-C	6	23	–	–
	VL-5/2-D-1-FR-C-EX	6	23	–	–
	VSPA	–	–	–	–
5/2-way valve, double solenoid	J-5/2-D-1-C	–	–	6	–
	J-5/2-D-1-C-EX	–	–	6	–
	JD-5/2-D-1-C	–	–	6	4
	JD-5/2-D-1-C-EX	–	–	6	4
	VSPA	–	–	–	–
5/3-way valve	VL-5/3G-D-1-C	7	44	–	–
	VL-5/3G-D-1-C-EX	7	44	–	–
	VL-5/3E-D-1-C	7	45	–	–
	VL-5/3E-D-1-C-EX	7	45	–	–
	VL-5/3B-D-1-C	7	44	–	–
	VL-5/3B-D-1-C-EX	7	44	–	–
	VSPA	–	–	–	–

ATEX

Type		VL- ... -EX, J ... -EX
ATEX category for gas		II 2G
Type of ignition protection for gas		Ex h IIC T4 Gb
ATEX category for dust		II 2D
Type of (ignition) protection for dust		Ex h IIIC T130°C Db
Explosion-proof ambient temperature	[°C]	–10 <= Ta <= +60
Explosion protection certification outside EU		EPL Db (GB)
		EPL Gb (GB)
CE marking (see declaration of conformity)[1)]		To EU Explosion Protection Directive (ATEX)
UKCA marking (see declaration of conformity) 1)		To UK explosion regulations

1) More information www.festo.com/catalogue/... ➔ Support/Downloads.

Safety characteristics

Type	VL- ... -C, J ... -C	VL- ... -EX, J ... -EX	VSPA
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27		
Vibration resistant	Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6	Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6

Materials

Type	VL- ... -C, J ... -C	VL- ... -EX, J ... -EX	VSPA
Housing	Die-cast aluminium	Die-cast aluminium	Die-cast aluminium
Seals	HNBR, NBR	HNBR, NBR	NBR
Screws	–	–	Galvanised steel
Note on materials	RoHs-compliant	RoHs-compliant	RoHs-compliant
LABS (PWIS) conformity	VDMA24364-B1/B2-L	VDMA24364-B1/B2-L	VDMA24364-B1/B2-L

Datasheet – Width 42 mm

Operating and environmental conditions – 2x3/2-way valves		
Type		VSPA
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)
Operating pressure	[MPa]	–0.09 ... +1
	[bar]	–0.9 ... +10
Pilot pressure	[MPa]	0.3 ... 1.6
	[bar]	3 ... 16
Ambient temperature	[°C]	–
Temperature of medium	[°C]	–10 ... +60
Corrosion resistance class CRC[1)]		0 - no corrosion stress

1) More information www.festo.com/x/topic/crc

Operating and environmental conditions – 5/2-way valves, monostable					
Type		VL		VSPA	
		Mechanical spring return	Pneumatic spring return	Mechanical spring return	Pneumatic spring return
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]			
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]			
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)			
Operating pressure	[MPa]	–0.09 ... +1.6	0.2 ... 1.6	–0.09 ... +1.6	0.3 ... 1.6
	[bar]	–0.9 ... +16	2 ... 16	–0.9 ... +16	3 ... 16
Pilot pressure	[MPa]	–	–	0.3 ... 1.6	
	[bar]	3 ... 16	2 ... 16	3 ... 16	
Ambient temperature	[°C]	–10 ... +60		–	
Temperature of medium	[°C]	–10 ... +60		–10 ... +60	
Corrosion resistance class CRC[1)]		–		0 - no corrosion stress	

1) More information www.festo.com/x/topic/crc

Operating and environmental conditions – 5/2-way valves, bistable			
Type		J	VSPA
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure	[MPa]	–0.09 ... +1.6	–0.09 ... +1.6
	[bar]	–0.9 ... +16	–0.9 ... +16
Pilot pressure	[MPa]	–	0.3 ... 1.6
	[bar]	2 ... 16	3 ... 16
Ambient temperature	[°C]	–10 ... +60	–
Temperature of medium	[°C]	–10 ... +60	–10 ... +60
Corrosion resistance class CRC[1)]		–	0 - no corrosion stress

1) More information www.festo.com/x/topic/crc


Operating and environmental conditions – 5/3-way valves			
Type		VL	VSPA
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure	[MPa]	–0.09 ... +1.6	–0.09 ... +1.6
	[bar]	–0.9 ... +16	–0.9 ... +16
Pilot pressure	[MPa]	–	0.3 ... 1.6
	[bar]	3 ... 16	3 ... 16
Ambient temperature	[°C]	–10 ... +60	–
Temperature of medium	[°C]	–10 ... +60	–10 ... +60
Corrosion resistance class CRC[1)]		–	0 - no corrosion stress

1) More information www.festo.com/x/topic/crc

Datasheet – Width 42 mm

Dimensions Download CAD data ➔ www.festo.com


5/2-way valves, pneumatic spring return, 5/2-way valves, bistable



[1] Captive retaining screws [2] Slot for inscription label

Type	B1	B2	B3	D1	H3	H4	H5	L2	L3	L4	L5
VL-5/2- ...	42	28	6	M5	38	9	46.5	87.6	43.8	36	18
J-5/2- ...											
JD-5/2- ...											

5/2-way valves, mechanical spring return




[1] Captive retaining screws [2] Slot for inscription label

Type	B1	B2	B3	D1	H3	H4	H5	L2	L3	L4	L5
VL-5/2- ... -FR- ...	42	28	6	M5	38	9	46.5	98	43.8	36	18

Datasheet – Width 42 mm

Dimensions – 5/3-way valves Download CAD data ➔ www.festo.com













[1] Captive retaining screws

[2] Slot for inscription label

Type	B1	B2	B3	D1	H3	H4	H5	L2	L3	L4	L5
VL-5/3...	42	28	6	M5	38	9	46.5	108.4	54.2	36	18


Datasheet – Width 42 mm

Ordering data

Circuit symbol	Description		ISO code	Weight [g]	Part no.	Type
2x3/2-way valve, single solenoid						
	Mechanical spring return	Normally closed	–	360	**8033644**	**VSPA-B-T32C-M-D1**
	Mechanical spring return	Normally open	–	360	**8033645**	**VSPA-B-T32U-M-D1**
	Mechanical spring return	Normally open, normally closed	–	360	**8033646**	**VSPA-B-T32H-M-D1**
5/2-way valve, single solenoid						
	Pneumatic spring return	–	–	340	**8033639**	**VSPA-B-M52-A-D1**
			102	290	**151009**	**VL-5/2-D-1-C**
		ATEX category a page 112	102	290	**536007**	**VL-5/2-D-1-C-EX**
	Mechanical spring return	–	–	340	**8033640**	**VSPA-B-M52-M-D1**
			104	290	**151014**	**VL-5/2-D-1-FR-C**
		ATEX category a page 112	104	290	**536010**	**VL-5/2-D-1-FR-C-EX**
5/2-way valve, double solenoid						
	–	–	–	330	**8033637**	**VSPA-B-B52-D1**
			101	290	**151007**	**J-5/2-D-1-C**
		ATEX category a page 112	101	290	**536013**	**J-5/2-D-1-C-EX**
	With dominant signal at 14	–	–	330	**8033638**	**VSPA-B-D52-D1**
			103	290	**151008**	**JD-5/2-D-1-C**
		ATEX category a page 112	103	290	**536016**	**JD-5/2-D-1-C-EX**
5/3-way valve						
	Mid-position closed	–	–	345	**8033641**	**VSPA-B-P53C-D1**
	Mid-position closed Mechanical spring return	–	106	320	**151010**	**VL-5/3G-D-1-C**
		ATEX category a page 112	106	320	**536019**	**VL-5/3G-D-1-C-EX**
	Mid-position exhausted	–	–	345	**8033642**	**VSPA-B-P53E-D1**
	Mid-position exhausted Mechanical spring return	–	108	320	**151011**	**VL-5/3E-D-1-C**
		ATEX category a page 112	108	320	**536022**	**VL-5/3E-D-1-C-EX**
	Mid-position pressurised	–	–	345	**8033643**	**VSPA-B-P53U-D1**
	Mid-position pressurised Mechanical spring return	–	107	320	**151012**	**VL-5/3B-D-1-C**
		ATEX category a page 112	107	320	**536025**	**VL-5/3B-D-1-C-EX**

Datasheet – Width 52 mm

- Flow rate
  2300 l/min
  1900 ... 4100 l/min



General technical data

Type		VL- ... -C, J ... -C	VL- ... -EX, J ... -EX	VSPA
Design		Piston spool	Piston spool	Piston spool
Sealing principle		Soft	Soft	Soft
Actuation type		Pneumatic	Pneumatic	Pneumatic
Type of control		Direct	Direct	Direct
Pilot air supply		–	–	External
Flow direction		Reversible	Reversible	Reversible
		VL-5/2-D-2-C: not reversible	VL-5/2-D-2-C-EX: not reversible	3/2-way valves: not reversible
Exhaust air function		Can be throttled	Can be throttled	Via individual sub-base
Suitable for vacuum		–	–	Yes
				Pneumatic spring return: none
Manual override		None	None	–
Type of mounting		On sub-base with through-hole and screw	On sub-base with through-hole and screw	On sub-base
Mounting position		Any	Any	Any
Max. tightening torque for valve mounting	[Nm]	–	–	2
Nominal width	[mm]	11.5	11.5	11.5
Overlap		Positive overlap	Positive overlap	Positive overlap
Width	[mm]	54	54	52
Grid dimension	[mm]	56	56	–
Pneumatic ports		Sub-base size 2 to ISO 5599-1	Sub-base size 2 to ISO 5599-1	Sub-base size 2 to ISO 5599-1
Noise level	[dB (A)]	85	85	85
Conforms to standard		ISO 5599-1	ISO 5599-1	–

Flow rates

		Standard nominal flow rate (standardised to DIN 1343) [l/min]	Nominal flow rate standardised according to ISO 8778 [l/min]	Flow rate of valve [l/min]	Flow rate of valve on individual sub-base [l/min]	b value	C value [l/sbar]
VL- ... -C		2300	–	–	–	–	–
J ... -C		2300	–	–	–	–	–
VL- ... -EX		2300	–	–	–	–	–
J ... -EX		2300	–	–	–	–	–
VSPA	2x 3/2-way valve, normally closed	–	2100	1900	1700	0.569	3631
	2x 3/2-way valve, normally open	–	2000	1800	1800	0.69	3167
	2x3/2-way valve, normally open/closed	–	1900	1800	1800	0.65	3208
	5/2-way valve, single solenoid, pneumatic spring	–	4100	3800	3100	0.31	8221
	5/2-way valve, single solenoid, mechanical spring	–	4100	3800	3200	0.3	8167
	5/2-way valve, double solenoid	–	4000	3700	3100	0.2	8577
	5/2-way valve, bistable, with dominant signal	–	4000	3700	3100	0.26	8272
	5/3-way valve, mid-position closed	–	3700	3500	2800	0.26	7695
	5/3-way valve, mid-position exhausted	–	3600	3400	2700	0.23	7667
	5/3-way valve, mid-position pressurised	–	3500	3300	2900	0.33	7069

Datasheet – Width 52 mm

Switching times [ms]

		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
2x3/2-way valve	VSPA	–	–	–	–
5/2-way valve, single solenoid	VL-5/2-D-2-C	23	39	–	–
	VL-5/2-D-2-C-EX	23	39	–	–
	VL-5/2-D-2-FR-C	11	39	–	–
	VL-5/2-D-2-FR-C-EX	11	39	–	–
	VSPA	–	–	–	–
5/2-way valve, double solenoid	J-5/2-D-2-C	–	–	8	–
	J-5/2-D-2-C-EX	–	–	8	–
	JD-5/2-D-2-C	–	–	8	8
	JD-5/2-D-2-C-EX	–	–	8	8
	VSPA	–	–	–	–
5/3-way valve	VL-5/3G-D-2-C	15	56	–	–
	VL-5/3G-D-2-C-EX	15	56	–	–
	VL-5/3E-D-2-C	16	59	–	–
	VL-5/3E-D-2-C-EX	16	59	–	–
	VL-5/3B-D-2-C	15	57	–	–
	VL-5/3B-D-2-C-EX	15	57	–	–
	VSPA	–	–	–	–

ATEX

Type		VL- ... -EX, J ... -EX
ATEX category for gas		II 2G
Type of ignition protection for gas		Ex h IIC T4 Gb
ATEX category for dust		II 2D
Type of (ignition) protection for dust		Ex h IIIC T130°C Db
Explosion-proof ambient temperature	[°C]	–10 <= Ta <= +60
Explosion protection certification outside EU		EPL Db (GB)
		EPL Gb (GB)
CE marking (see declaration of conformity)[1)]		To EU Explosion Protection Directive (ATEX)
UKCA marking (see declaration of conformity) 1)		To UK explosion regulations

1) More information www.festo.com/catalogue/... ➔ Support/Downloads.

Safety characteristics

Type	VL- ... -C, J ... -C	VL- ... -EX, J ... -EX	VSPA
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27		
Vibration resistant	Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6	Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6

Materials

Type	VL- ... -C, J ... -C	VL- ... -EX, J ... -EX	VSPA
Housing	Die-cast aluminium	Die-cast aluminium	Die-cast aluminium
Seals	HNBR, NBR	HNBR, NBR	NBR
Screws	–	–	Galvanised steel
Note on materials	RoHs-compliant	RoHs-compliant	RoHs-compliant
LABS (PWIS) conformity	VDMA24364-B1/B2-L	VDMA24364-B1/B2-L	VDMA24364-B1/B2-L

Datasheet – Width 52 mm

Operating and environmental conditions – 2x3/2-way valves		
Type		VSPA
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)
Operating pressure	[MPa]	–0.09 ... +1
	[bar]	–0.9 ... +10
Pilot pressure	[MPa]	0.3 ... 1.6
	[bar]	3 ... 16
Ambient temperature	[°C]	–
Temperature of medium	[°C]	–10 ... +60
Corrosion resistance class CRC[1)]		0 - no corrosion stress

1) More information www.festo.com/x/topic/crc

Operating and environmental conditions – 5/2-way valves, monostable					
Type		VL		VSPA	
		Mechanical spring return	Pneumatic spring return	Mechanical spring return	Pneumatic spring return
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]			
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]			
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)			
Operating pressure	[MPa]	–0.09 ... +1.6	0.2 ... 1.6	–0.09 ... +1.6	0.3 ... 1.6
	[bar]	–0.9 ... +16	2 ... 16	–0.9 ... +16	3 ... 16
Pilot pressure	[MPa]	–	–	0.3 ... 1.6	
	[bar]	3 ... 16	2 ... 16	3 ... 16	
Ambient temperature	[°C]	–10 ... +60		–	
Temperature of medium	[°C]	–10 ... +60		–10 ... +60	
Corrosion resistance class CRC[1)]		–		0 - no corrosion stress	

1) More information www.festo.com/x/topic/crc

Operating and environmental conditions – 5/2-way valves, bistable			
Type		J	VSPA
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure	[MPa]	–0.09 ... +1.6	–0.09 ... +1.6
	[bar]	–0.9 ... +16	–0.9 ... +16
Pilot pressure	[MPa]	–	0.3 ... 1.6
	[bar]	2 ... 16	3 ... 16
Ambient temperature	[°C]	–10 ... +60	–
Temperature of medium	[°C]	–10 ... +60	–10 ... +60
Corrosion resistance class CRC[1)]		–	0 - no corrosion stress

1) More information www.festo.com/x/topic/crc


Operating and environmental conditions – 5/3-way valves			
Type		VL	VSPA
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure	[MPa]	–0.09 ... +1.6	–0.09 ... +1.6
	[bar]	–0.9 ... +16	–0.9 ... +16
Pilot pressure	[MPa]	–	0.3 ... 1.6
	[bar]	3 ... 16	3 ... 16
Ambient temperature	[°C]	–10 ... +60	–
Temperature of medium	[°C]	–10 ... +60	–10 ... +60
Corrosion resistance class CRC[1)]		–	0 - no corrosion stress

1) More information www.festo.com/x/topic/crc

Datasheet – Width 52 mm

Dimensions Download CAD data ➔ www.festo.com


5/2-way valves, pneumatic spring return, 5/2-way valves, bistable



[1] Captive retaining screws [2] Slot for inscription label

Type	B1	B2	B3	D1	H3	H4	H5	L2	L3	L4	L5
VL-5/2- ...	54	38	9	M6	48	9.5	56.5	123.4	61.7	48	24
J-5/2- ...											
JD-5/2- ...											

5/2-way valves, mechanical spring return




[1] Captive retaining screws [2] Slot for inscription label

Type	B1	B2	B3	D1	H3	H4	H5	L2	L3	L4	L5
VL-5/2- ... -FR- ...	54	38	9	M6	48	9.5	56.5	140.7	61.7	48	24

Datasheet – Width 52 mm

Dimensions – 5/3-way valves Download CAD data ➔ www.festo.com













[1] Captive retaining screws

[2] Slot for inscription label

Type	B1	B2	B3	D1	H3	H4	H5	L2	L3	L4	L5
VL-5/3...	54	38	9	M6	48	9.5	56.5	158	79	48	24


Datasheet – Width 52 mm

Ordering data

Circuit symbol	Description		ISO code	Weight [g]	Part no.	Type
2x3/2-way valve, single solenoid						
	Mechanical spring return	Normally closed	–	680	**8033654**	**VSPA-B-T32C-M-D2**
	Mechanical spring return	Normally open	–	680	**8033655**	**VSPA-B-T32U-M-D2**
	Mechanical spring return	Normally open, normally closed	–	680	**8033656**	**VSPA-B-T32H-M-D2**
5/2-way valve, single solenoid						
	Pneumatic spring return	–	–	600	**8033649**	**VSPA-B-M52-A-D2**
		UL – Recognized (OL)	202	550	**151845**	**VL-5/2-D-2-C**
		ATEX category a page 118	202	550	**536008**	**VL-5/2-D-2-C-EX**
	Mechanical spring return	–	–	600	**8033650**	**VSPA-B-M52-M-D2**
		UL – Recognized (OL)	204	550	**151844**	**VL-5/2-D-2-FR-C**
		ATEX category a page 118	204	550	**536011**	**VL-5/2-D-2-FR-C-EX**
5/2-way valve, double solenoid						
	–	–	–	610	**8033647**	**VSPA-B-B52-D2**
			201	550	**151846**	**J-5/2-D-2-C**
		ATEX category a page 118	201	550	**536014**	**J-5/2-D-2-C-EX**
	With dominant signal at 14	–	–	610	**8033648**	**VSPA-B-D52-D2**
		UL – Recognized (OL)	203	550	**151847**	**JD-5/2-D-2-C**
		ATEX category a page 118	203	550	**536017**	**JD-5/2-D-2-C-EX**
5/3-way valve						
	Mid-position closed	–	–	655	**8033651**	**VSPA-B-P53C-D2**
	Mid-position closed Mechanical spring return	UL – Recognized (OL)	206	825	**151848**	**VL-5/3G-D-2-C**
		ATEX category a page 118	206	825	**536020**	**VL-5/3G-D-2-C-EX**
	Mid-position exhausted	–	–	655	**8033652**	**VSPA-B-P53E-D2**
	Mid-position exhausted Mechanical spring return	UL – Recognized (OL)	208	825	**151849**	**VL-5/3E-D-2-C**
		ATEX category a page 118	208	825	**536023**	**VL-5/3E-D-2-C-EX**
	Mid-position pressurised	–	–	655	**8033653**	**VSPA-B-P53U-D2**
	Mid-position pressurised Mechanical spring return	UL – Recognized (OL)	207	825	**151850**	**VL-5/3B-D-2-C**
		ATEX category a page 118	207	825	**536026**	**VL-5/3B-D-2-C-EX**

Datasheet – Width 65 mm

- Flow rate
Up to 4600 l/min



General technical data			
Type		VL- ... -C, J ... -C	VL- ... -EX, J ... -EX
Design		Piston spool	Piston spool
Sealing principle		Soft	Soft
Actuation type		Pneumatic	Pneumatic
Type of control		Direct	Direct
Flow direction		Reversible	Reversible
		VL-5/2-D-3-C: not reversible	VL-5/2-D-3-C-EX: not reversible
Exhaust air function		Can be throttled	Can be throttled
Manual override		None	None
Type of mounting		On sub-base with through-hole and screw	On sub-base with through-hole and screw
Mounting position		Any	Any
Nominal width	[mm]	14.5	14.5
Overlap		Positive overlap	Positive overlap
Width	[mm]	65	65
Grid dimension	[mm]	71	71
Pneumatic ports		Sub-base size 3 to ISO 5599-1	Sub-base size 3 to ISO 5599-1
Noise level	[dB (A)]	85	85
Conforms to standard		ISO 5599-1	ISO 5599-1

Flow rates					
Valve function		5/2-way valve	5/3-way valve		
			Mid-position closed	Mid-position exhausted	Mid-position pressurised
Standard nominal flow rate	[l/min]	4500	4100	4600	4100

Datasheet – Width 65 mm

Switching times [ms]

		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
5/2-way valve, single solenoid	VL-5/2-D-1-C	29	36	–	–
	VL-5/2-D-1-C-EX	29	36	–	–
	VL-5/2-D-1-FR-C	13	43	–	–
	VL-5/2-D-1-FR-C-EX	13	43	–	–
5/2-way valve, double solenoid	J-5/2-D-1-C	–	–	8	–
	J-5/2-D-1-C-EX	–	–	8	–
	JD-5/2-D-1-C	–	–	8	8
	JD-5/2-D-1-C-EX	–	–	8	8
5/3-way valve	VL-5/3G-D-1-C	17	61	–	–
	VL-5/3G-D-1-C-EX	17	61	–	–
	VL-5/3E-D-1-C	18	63	–	–
	VL-5/3E-D-1-C-EX	18	63	–	–
	VL-5/3B-D-1-C	16	60	–	–
	VL-5/3B-D-1-C-EX	16	60	–	–

ATEX

Type		VL- ... -EX, J ... -EX
ATEX category for gas		II 2G
Type of ignition protection for gas		Ex h IIC T4 Gb
ATEX category for dust		II 2D
Type of (ignition) protection for dust		Ex h IIIC T130°C Db
Explosion-proof ambient temperature	[°C]	–10 <= Ta <= +60
Explosion protection certification outside EU		EPL Db (GB)
		EPL Gb (GB)
CE marking (see declaration of conformity)[1)]		To EU Explosion Protection Directive (ATEX)
UKCA marking (see declaration of conformity) 1)		To UK explosion regulations

1) More information www.festo.com/catalogue/... ➔ Support/Downloads.

Operating and environmental conditions

Valve function		5/2-way valve			5/3-way valve
		Monostable		Bistable	
		Pneumatic spring	Mechanical spring		
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]			
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]			
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)			
Operating pressure	[MPa]	0.2 ... 1.6	–0.09 ... +1.6	–0.09 ... +1.6	–0.09 ... +1.6
	[bar]	2 ... 16	–0.9 ... +16	–0.9 ... +16	–0.9 ... +16
Pilot pressure	[bar]	2 ... 16	3 ... 16	2 ... 16	3 ... 16
Ambient temperature	[°C]	–10 ... +60			
Temperature of medium	[°C]	–10 ... +60			

Safety characteristics

Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Vibration resistant	Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6


Materials

Housing	Die-cast aluminium
Seals	HNBR, NBR
Note on materials	RoHs-compliant

Datasheet – Width 65 mm

Dimensions Download CAD data ➔ www.festo.com


5/2-way valves, pneumatic spring return, 5/2-way valves, bistable



[1] Captive retaining screws [2] Slot for inscription label

Type	B1	B2	B3	D1	H3	H4	H5	L2	L3	L4	L5
VL-5/2- ...	65	48	12	M8	55	12	63.5	145.4	72.7	64	32
J-5/2- ...											
JD-5/2- ...											

5/2-way valves, mechanical spring return




[1] Captive retaining screws [2] Slot for inscription label

Type	B1	B2	B3	D1	H3	H4	H5	L2	L3	L4	L5
VL-5/2- ... -FR- ...	65	48	12	M8	55	12	63.5	164.7	72.7	64	32

Datasheet – Width 65 mm

Dimensions – 5/3-way valves Download CAD data ➔ www.festo.com










[1] Captive retaining screws

[2] Slot for inscription label

Type	B1	B2	B3	D1	H3	H4	H5	L2	L3	L4	L5
VL-5/3...	65	48	12	M8	55	12	63.5	184	92	64	32


Ordering data

Circuit symbol	Description		Weight [g]	Part no.	Type
5/2-way valve, single solenoid					
	Pneumatic spring return	c UL us – Recognized (OL)	810	**151864**	**VL-5/2-D-3-C**
		ATEX category a page 124	810	**536009**	**VL-5/2-D-3-C-EX**
	Mechanical spring return	c UL us – Recognized (OL)	810	**151863**	**VL-5/2-D-3-FR-C**
		ATEX category a page 124	810	**536012**	**VL-5/2-D-3-FR-C-EX**
5/2-way valve, double solenoid					
	–	–	810	**151865**	**J-5/2-D-3-C**
		ATEX category a page 124	810	**536015**	**J-5/2-D-3-C-EX**
	With dominant signal at 14	c UL us – Recognized (OL)	810	**151866**	**JD-5/2-D-3-C**
		ATEX category a page 124	810	**536018**	**JD-5/2-D-3-C-EX**
5/3-way valve					
	Mid-position closed Mechanical spring return	c UL us – Recognized (OL)	910	**151867**	**VL-5/3G-D-3-C**
		ATEX category a page 124	910	**536021**	**VL-5/3G-D-3-C-EX**
	Mid-position exhausted Mechanical spring return	c UL us – Recognized (OL)	910	**151868**	**VL-5/3E-D-3-C**
		ATEX category a page 124	910	**536024**	**VL-5/3E-D-3-C-EX**
	Mid-position pressurised Mechanical spring return	–	910	**151869**	**VL-5/3B-D-3-C**
		ATEX category a page 124	910	**536027**	**VL-5/3B-D-3-C-EX**

Datasheet – Width 76 mm

- Flow rate
Up to 6000 l/min

- Repair service



General technical data		
Design		Piston spool
Sealing principle		Soft
Actuation type		Pneumatic
Type of control		Direct
Flow direction		Reversible
Exhaust air function		Can be throttled
Manual override		None
Type of mounting		On sub-base with through-hole and screw
Mounting position		Any
Nominal width	[mm]	18
Overlap		Positive overlap
Width	[mm]	76
Grid dimension	[mm]	82
Pneumatic ports		Sub-base size 4 to ISO 5599-1
Noise level	[dB (A)]	85
Conforms to standard		ISO 5599-1

Flow rates			
Valve function		5/2-way valve	5/3-way valve
Standard nominal flow rate	[l/min]	6000	4800

Switching times [ms]				
		Switching time on	Switching time off	Switching time changeover
5/2-way valve, single solenoid	VL-5/2-3/4-D-4	25	90	–
5/2-way valve, double solenoid	J-5/2-3/4-D-4	–	–	20
5/3-way valve	VL-5/3G-3/4-D-4	40	130	–
	VL-5/3E-3/4-D-4	50	170	–


Datasheet – Width 76 mm

Operating and environmental conditions					
Valve function		5/2-way valve		5/3-way valve	
		Monostable	Bistable		
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]			
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]			
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)			
Operating pressure	[bar]	–0.9 ... +16	–0.9 ... +16	–0.9 ... +16	
Pilot pressure	[bar]	3 ... 16	2 ... 16	3 ... 16	
Ambient temperature	[°C]	–10 ... +60			
Temperature of medium	[°C]	–10 ... +60			

Materials	
Housing	Aluminium
Seals	NBR
Note on materials	RoHs-compliant
LABS (PWIS) conformity	VDMA24364-B1/B2-L

Dimensions – 5/3-way valves

Download CAD data ➔ www.festo.com







[1] Captive retaining screws

Type	B1	B2	D1	H3	H4	L2	L3	L4	L5
VL-5/2-3/4-D-4	76	58	M8	74	14	182	91	80	40
J-5/2-3/4-D-4									
VL-5/3E-3/4-D-4									
VL-5/3G-3/4-D-4									

Datasheet – Width 76 mm

Ordering data


Circuit symbol	Description	Weight [g]	Part no.	Type
5/2-way valve, single solenoid				
	Mechanical spring return	1800	**12461**	**VL-5/2-3/4-D-4**
5/2-way valve, double solenoid				
	–	1800	**12462**	**J-5/2-3/4-D-4**
5/3-way valve				
	Normally closed Mechanical spring return	2000	**12463**	**VL-5/3G-3/4-D-4**
	Normally exhausted Mechanical spring return	2000	**12464**	**VL-5/3E-3/4-D-4**

Accessories

Individual sub-base NAS
Sub-base VABS

Ports on the side

Materials:
Die-cast aluminium
Anodised aluminium



General technical data						
Type		NAS-1/4	NAS-3/8	NAS-1/2	NAS-3/4	VABS
Conforms to standard		ISO 5599-1				–
Based on standard		–				ISO 5599-1
Maximum number of valve positions		–				1
Suitable for vacuum		–				Yes
Exhaust air function		–				Can be throttled
Type of mounting		With through-hole				With through-hole for M5 screw


Materials						
Type		NAS-1/4	NAS-3/8	NAS-1/2	NAS-3/4	VABS
Connecting plate		Die-cast aluminium			Anodised aluminium	Die-cast aluminium
Note on materials		–			–	RoHs-compliant
LABS (PWIS) conformity		–			–	VDMA24364-B1/B2-L

Operating and environmental conditions						
Type		NAS-1/4	NAS-3/8	NAS-1/2	NAS-3/4	VABS
Operating medium		–			–	Compressed air to ISO 8573-1:2010 [7:4:4]
Pilot medium		–			–	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on the operating/pilot medium		–			–	Lubricated operation possible (in which case lubricated operation will always be required)
Pilot pressure	[MPa]	–			–	0 ... 1.6
	[bar]	–			–	0 ... 16
Ambient temperature	[°C]	–			–	–10 ... +60
Temperature of medium	[°C]	–			–	–10 ... +60
Storage temperature	[°C]	–			–	–20 ... +60
Corrosion resistance class CRC[1)]		–			–	0 - no corrosion stress
Certification		c UL - Recognized (OL)			–	–

1) More information www.festo.com/x/topic/crc


Accessories

Dimensions – Individual sub-base NAS Download CAD data ➔ www.festo.com



Type	B1	D1	D2	D3	H1	H2	H4	H5	H6	L1	L2	L3	L4	L5
NAS-1/4-1A-ISO	48	G1/4	G1/8	5.5	32	10	9	20.3	20.3	110	98	23	60	46
NAS-3/8-2A-ISO	57	G3/8	G1/8	6.6	40	13	9	25	25	124	112	27	71	54
NAS-1/2-3A-ISO	71	G1/2	G1/8	6.6	32	18	9	16	16	149	136	32	91	64
NAS-3/4-4A-ISO	85	G3/4	G1/8	9	42	19	9	21	21	186	170	42	111	84

Dimensions – Sub-base VABS Download CAD data ➔ www.festo.com



Type	B1	B2	B3	D1	D2	H1	H2	H3	H4	H5	H6
VABS-S1-1S-G38	48	46	23	G3/8	G1/8	38.5	5	16.3	13.5	26.5	13.5
VABS-S1-1HS-G38											
VABS-S1-1S-N38				3/8 NPT	1/8 NPT						
VABS-S1-1HS-N38											
VABS-S1-2S-G12	58	56	28	G1/2	G1/8	45	10	18	16	29	16
VABS-S1-2S-N12				1/2 NPT	1/8 NPT						

Type	L1	L2	L3	L4	L5	L6	L7	L8	L9	L10
VABS-S1-1S-G38	110	98	6	57	26.5	42	26	45.4	32.3	22.7
VABS-S1-1HS-G38										
VABS-S1-1S-N38										
VABS-S1-1HS-N38										
VABS-S1-2S-G12	124	112	6	72	26	46	32	55	34.5	27.5
VABS-S1-2S-N12										

Accessories

Ordering data

Designation to VDMA	Width	Pneumatic connection		Operating pressure		Weight	Part no.	Type
		1, 2, 3, 4, 5	12/14	[MPa]	[bar]	[g]		
VDMA 24345-A-1	–	G1/4	G1/8	–	–	190	**9484**	**NAS-1/4-1A-ISO**
–	48 mm	G3/8	G1/8	–0.09 ... +1.6	–0.9 ... +16	230	**8032642**	**VABS-S1-1S-G38**
				–0.09 ... +1	–0.9 ... +10		**8032646**	**VABS-S1-1HS-G38**
		3/8 NPT	1/8 NPT	–0.09 ... +1.6	–0.9 ... +16	230	**8032643**	**VABS-S1-1S-N38**
				–0.09 ... +1	–0.9 ... +10		**8032647**	**VABS-S1-1HS-N38**
VDMA 24345-A-2	–	G3/8	G1/8	–	–	300	**11310**	**NAS-3/8-2A-ISO**
–	58 mm	G1/2	G1/8	–0.09 ... +1.6	–0.9 ... +16	380	**8032644**	**VABS-S1-2S-G12**
		1/2 NPT	1/8 NPT	–0.09 ... +1.6	–0.9 ... +16	380	**8032645**	**VABS-S1-2S-N12**
VDMA 24345-A-3	–	G1/2	G1/8	–	–	360	**10336**	**NAS-1/2-3A-ISO**
VDMA 24345-A-4	–	G3/4	G1/8	–	–	1260	**152813**	**NAS-3/4-4A-ISO**


-H- Note: This product conforms to ISO 1179-1 and ISO 228-1.

Accessories

Individual sub-base NAU

Connections underneath

Materials:
Die-cast aluminium
Anodised aluminium




General technical data	
Conforms to standard	ISO 5599-1
Type of mounting	With through-hole


Materials				
Type	NAU-1/4	NAU-3/8	NAU-1/2	NAU-3/4
Connecting plate	Die-cast aluminium			Anodised aluminium

Operating and environmental conditions				
Type	NAU-1/4	NAU-3/8	NAU-1/2	NAU-3/4
Certification	c UL - Recognized (OL)		–	–

Dimensions – Individual sub-base NAU

Download CAD data ➔ www.festo.com





Type	B1	D1	D2	D3	H1	H2	H3	H4	H5	L1	L2	L3	L4	L5
NAU-1/4-1B-ISO	46	G1/4	G1/8	5.5	30	10	5	7.5	20	110	98	23	60.7	46
NAU-3/8-2B-ISO	56	G3/8	G1/8	6.6	35	13	6.5	8.3	24	124	112	27	70	54
NAU-1/2-3B-ISO	71	G1/2	G1/8	6.6	32	18	9	10	30	149	136	33	90	66
NAU-3/4-4B-ISO	85	G3/4	G1/8	9	28	19	9.5	12	37	186	170	42	111	84

Accessories

Ordering data

Designation to VDMA	Pneumatic connection		Weight	Part no.	Type
	1, 2, 3, 4, 5	12, 14	[g]		
VDMA 24345-B-1	G1/4	G1/8	–	**9485**	**NAU-1/4-1B-ISO**
VDMA 24345-B-2	G3/8	G1/8	450	**11416**	**NAU-3/8-2B-ISO**
VDMA 24345-B-3	G1/2	G1/8	660	**10337**	**NAU-1/2-3B-ISO**
VDMA 24345-B-4	G3/4	G1/8	1080	**152814**	**NAU-3/4-4B-ISO**

-H- Note: This product conforms to ISO 1179-1 and ISO 228-1.


Accessories

Manifold sub-base
NAV
VABV

Connections underneath

Materials:
Die-cast aluminium
Anodised aluminium

Dimensions NAV a page148



General technical data						
Type		NAV-1/4	NAV-3/8	NAV-1/2	NAV-3/4	VABV
Conforms to standard		ISO 5599-1				–
Based on standard		–				ISO 5599-1
Maximum number of valve positions		–				1
Suitable for vacuum		–				Yes
Exhaust air function		–				Can be throttled


Materials						
Type		NAV-1/4	NAV-3/8	NAV-1/2	NAV-3/4	VABV
Connecting plate		Die-cast aluminium			Anodised aluminium	Die-cast aluminium
Note on materials		–			–	RoHs-compliant
LABS (PWIS) conformity		–			–	VDMA24364-B1/B2-L

Operating and environmental conditions						
Type		NAV-1/4	NAV-3/8	NAV-1/2	NAV-3/4	VABV
Operating medium		–	–		–	Compressed air to ISO 8573-1:2010 [7:4:4]
Pilot medium		–	–		–	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on the operating/pilot medium		–	–		–	Lubricated operation possible (in which case lubricated operation will always be required)
Ambient temperature	[°C]	–	–		–	–10 ... +50
Temperature of medium	[°C]	–	–		–	–10 ... +50
Storage temperature	[°C]	–	–		–	–20 ... +60
Corrosion resistance class CRC[1)]		–	–		–	0 - no corrosion stress
Certification		–	UL – Recognized (OL)		–	–

1) More information www.festo.com/x/topic/crc

Accessories

Dimensions – Manifold sub-base VABV Download CAD data ➔ www.festo.com



Type	B1	B2	B3	H1	H2	H3	H4	H5	L1	L2	L3
VABV-S1-1SB-G38	44	16.5	16	65	13.5	20.5	34	15	124	96.2	19.9
VABV-S1-1HSB-G38							34.5				
VABV-S1-1SB-N38							34				
VABV-S1-1HSB-N38							34.5				
VABV-S1-2SB-G12	59	19.5	22				35.5	14.5			
VABV-S1-2SB-N12											


Ordering data

Designation to VDMA	Width	Pneumatic connection		Operating pressure		Weight	Part no.	Type
		2, 4	12/14	[MPa]	[bar]	[g]		
VDMA 24345-C-1	–	G1/4	G1/8	–	–	240	**10173**	**NAV-1/4-1C-ISO**
–	44 mm	G3/8	–	–0.09 ... +1.6	–0.9 ... +16	490	**8029812**	**VABV-S1-1SB-G38**
				–0.09 ... +1	–0.9 ... +10		**8030650**	**VABV-S1-1HSB-G38**
		3/8 NPT	–	–0.09 ... +1.6	–0.9 ... +16	490	**8029813**	**VABV-S1-1SB-N38**
				–0.09 ... +1	–0.9 ... +10		**8030651**	**VABV-S1-1HSB-N38**
VDMA 24345-C-2	–	G3/8	G1/8	–	–	400	**11305**	**NAV-3/8-2C-ISO**
–	59 mm	G1/2	–	–0.09 ... +1.6	–0.9 ... +16	670	**8029814**	**VABV-S1-2SB-G12**
		1/2 NPT	–	–0.09 ... +1.6	–0.9 ... +16	670	**8029815**	**VABV-S1-2SB-N12**
VDMA 24345-C-3	–	G1/2	G1/8	–	–	700	**10175**	**NAV-1/2-3C-ISO**
VDMA 24345-C-4	–	G3/4	G1/8	–	–	1400	**11139**	**NAV-3/4-4C-ISO**

Accessories

Supply plate VABF

Materials:
Die-cast aluminium
Wrought aluminium alloy
PA



General technical data	
Based on standard	ISO 5599-1
Maximum number of valve positions	1
Suitable for vacuum	Yes
Exhaust air function	Can be throttled

Materials		
Type	VABF-S1-1-P1A11	VABF-S1-1-P1A12
Exhaust air plate	Wrought aluminium alloy	PA
Supply plate	Anodised aluminium	Die-cast aluminium
Note on materials	RoHs-compliant	RoHs-compliant
LABS (PWIS) conformity	VDMA24364-B1/B2-L	VDMA24364-B1/B2-L


Operating and environmental conditions		
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)
Operating pressure	[MPa]	–0.09 ... +1.6
	[bar]	–0.9 ... +16
Ambient temperature	[°C]	–10 ... +50
Temperature of medium	[°C]	–10 ... +50
Storage temperature	[°C]	–20 ... +60
Corrosion resistance class CRC[1)]		0 - no corrosion stress

1) More information www.festo.com/x/topic/crc

Accessories


Dimensions Download CAD data ➔ www.festo.com

Port 3 and 5 separated



Type	B1	B2	B3	H1	H3	H4	H5	L1	L2	L3	L4	L5
VABF-S1-1-P1A11	44	5.5	22	87	52.5	20.5	13.5	124	96.2	19.9	44	40



Port 3 and 5 combined



Type	B1	B2	B3	H1	H2	H3	H4	H5	L1	L2	L3
VABF-S1-1-P1A12	44	5.8	22	115.2	93.8	52.5	20.5	13.5	124	96.2	19.9

Accessories

Ordering data

Width	Description		Pneumatic connection 1, 3, 5	Weight [g]	Part no.	Type
44 mm		Port 3 and 5 separated	G1/2	660	**8037655**	**VABF-S1-1-P1A11-G12**
			1/2 NPT	660	**8037656**	**VABF-S1-1-P1A11-N12**
		Port 3 and 5 combined	G1/2	650	**8037653**	**VABF-S1-1-P1A12-G12**
			1/2 NPT	650	**8037654**	**VABF-S1-1-P1A12-N12**

Accessories

Manifold sub-base with angled connections NAW

Ports on the side and on top

Materials:
Die-cast aluminium
Anodised aluminium

Dimensions apage 148



General technical data	
Conforms to standard	ISO 5599-1

Operating and environmental conditions				
Type	NAW-1/4	NAW-3/8	NAW-1/2	NAW-3/4
Sub-base material	Die-cast aluminium			Anodised aluminium

Ordering data					
Designation to VDMA	Pneumatic connection		Weight	Part no.	Type
	2	4	[g]		
VDMA 24345-E-1	G1/4	G1/4	360	**11304**	**NAW-1/4-1E-ISO**
VDMA 24345-E-2	G3/8	G3/8	600	**11307**	**NAW-3/8-2E-ISO**
VDMA 24345-E-3	G1/2	G1/2	920	**11309**	**NAW-1/2-3E-ISO**
VDMA 24345-E-4	G3/4	G3/4	1550	**11141**	**NAW-3/4-4E-ISO**

Manifold sub-base with angled connections NAVW

Ports on the side and underneath

Materials:
Die-cast aluminium

Dimensions apage 148



General technical data	
Conforms to standard	ISO 5599-1

Operating and environmental conditions	
Operating medium	Compressed air to ISO 8573-1:2010 [7:–:–]

Ordering data				
Pneumatic connection		Weight	Part no.	Type
1, 2, 4	12, 14	[g]		
G1/4	G1/8	320	**152789**	**NAVW-1/4-1-ISO**
G3/8	G1/8	550	**152790**	**NAVW-3/8-2-ISO**
G1/2	G1/8	1020	**152791**	**NAVW-1/2-3-ISO**


-H- Note: This product conforms to ISO 1179-1 and ISO 228-1.

Accessories

End plate kit NEV

Materials:
Die-cast aluminium
Anodised aluminium

Dimensions NEV a page 148



General technical data	
Conforms to standard	ISO 5599-1

Ordering data


Designation to VDMA	Pneumatic connection 1, 3, 5	Weight [g]	Part no.	Type
VDMA 24345-D-1	G3/8	280	**10174**	**NEV-1DA/DB-ISO**
VDMA 24345-D-2	G1/2	450	**11306**	**NEV-2DA/DB-ISO**
VDMA 24345-D-3	G1	760	**10176**	**NEV-3DA/DB-ISO**
VDMA 24345-D-4	G1	1390	**11140**	**NEV-4DA/DB-ISO**

-H- Note: This product conforms to ISO 1179-1 and ISO 228-1.

Accessories

End plate VABE

Materials:
Die-cast aluminium



General technical data	
Based on standard	ISO 5599-1
Suitable for vacuum	Yes
Exhaust air function	Can be throttled
Type of mounting	With through-hole for M6 screw

Materials	
End plate	Die-cast aluminium
Note on materials	RoHs-compliant
LABS (PWIS) conformity	VDMA24364-B1/B2-L


Operating and environmental conditions		
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)
Operating pressure	[MPa]	–0.09 ... +1.6
	[bar]	–0.9 ... +16
Ambient temperature	[°C]	–10 ... +50
Temperature of medium	[°C]	–10 ... +50
Storage temperature	[°C]	–20 ... +60
Corrosion resistance class CRC[1)]		0 - no corrosion stress

1) More information www.festo.com/x/topic/crc

Accessories

Dimensions – End plate left


Download CAD data ➔ www.festo.com



Type	B1	B2	B3	B4	D1	D2	D3	H1	H2	H3	H4	L1	L2	L3	L4	L5	L6	L7	L8
VABE-S1-1L-G12	44	5.8	6	6	G1/2	–	6.5	77.9	33	25.9	20	124.9	108	72	26.4	35.4	54	27	8.4
VABE-S1-1LZ-G12					G1/2	G1/4													
VABE-S1-1L-N12					1/2 NPT	–													
VABE-S1-1LZ-N12					1/2 NPT	1/4 NPT													
VABE-S1-2L-G34					G3/4	–													
VABE-S1-2LZ-G34					G3/4	G1/4													
VABE-S1-2L-N34					3/4 NPT	–													
VABE-S1-2LZ-N34					3/4 NPT	1/4 NPT													

Dimensions – End plate right

Download CAD data ➔ www.festo.com



Type	B1	B3	B4	D1	D2	D3	H1	H2	H3	H4	L1	L2	L3	L4	L5	L6	L7	L8
VABE-S1-1R-G12	44	6	6	G1/2	–	6.5	77.4	33	25.9	19.5	124	108	72	26	35	54	27	8
VABE-S1-1RZ-G12				G1/2	G1/4													
VABE-S1-1R-N12				1/2 NPT	–													
VABE-S1-1RZ-N12				1/2 NPT	1/4 NPT													
VABE-S1-2R-G34				G3/4	–													
VABE-S1-2RZ-G34				G3/4	G1/4													
VABE-S1-2R-N34				3/4 NPT	–													
VABE-S1-2RZ-N34				3/4 NPT	1/4 NPT													

Accessories

Ordering data Width	Pneumatic connection 1, 3, 5	 12, 14	Weight [g]	Pilot air supply	Part no.	Type
Left end plate						
44 mm	G1/2	–	400	Internal	**8032662**	**VABE-S1-1L-G12**
		G1/4		External	**8032660**	**VABE-S1-1LZ-G12**
	1/2 NPT	–	400	Internal	**8032663**	**VABE-S1-1L-N12**
		1/4 NPT		External	**8032661**	**VABE-S1-1LZ-N12**
	G3/4	–	360	Internal	**8032666**	**VABE-S1-2L-G34**
		G1/4		External	**8032664**	**VABE-S1-2LZ-G34**
	3/4 NPT	–	360	Internal	**8032667**	**VABE-S1-2L-N34**
		1/4 NPT		External	**8032665**	**VABE-S1-2LZ-N34**
Right end plate						
44 mm	G1/2	–	410	Internal	**8032670**	**VABE-S1-1R-G12**
		G1/4		External	**8032668**	**VABE-S1-1RZ-G12**
	1/2 NPT	–	410	Internal	**8032671**	**VABE-S1-1R-N12**
		1/4 NPT		External	**8032669**	**VABE-S1-1RZ-N12**
	G3/4	–	370	Internal	**8032674**	**VABE-S1-2R-G34**
		G1/4		External	**8032672**	**VABE-S1-2RZ-G34**
	3/4 NPT	–	370	Internal	**8032675**	**VABE-S1-2R-N34**
		1/4 NPT		External	**8032673**	**VABE-S1-2RZ-N34**

Accessories

Cover plate NDV

Materials:
Width 42 mm, 52 mm, 65 mm:
Steel

Width 76 mm:
Wrought aluminium alloy

Dimensions apage 148



General technical data	
Conforms to standard	ISO 5599-1

Operating and environmental conditions	
Operating medium	Compressed air to ISO 8573-1:2010 [7:–:–]
Note on the operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)

Ordering data

Width	Weight [g]	Part no.	Type
42 mm	113	**9489**	**NDV-1-ISO**
52 mm	166	**11308**	**NDV-2-ISO**
65 mm	314	**10340**	**NDV-3-ISO**
76 mm	1480	**11142**	**NDV-4-ISO**

Isolating disc NSC

Materials:
Wrought aluminium alloy

Dimensions a 148



General technical data	
Conforms to standard	ISO 5599-1


Ordering data

Width	Pneumatic connection	Weight [g]	Part no.	Type
42 mm	G1/4	6	**11550**	**NSC-1/4-1-ISO**
52 mm	G3/8	9.2	**11908**	**NSC-3/8-2-ISO**
65 mm	G1/2	20	**11551**	**NSC-1/2-3-ISO**
76 mm	G3/4	24	**11699**	**NSC-3/4-4-ISO**

Accessories

Duct separation VABD

Materials:
Steel, NBR



General technical data	
Based on standard	ISO 5599-1
Suitable for vacuum	Yes
Type of mounting	With through-hole for M6 screw

Materials	
Separator plate	Steel
	NBR
Note on materials	RoHs-compliant
LABS (PWIS) conformity	VDMA24364-B1/B2-L

Operating and environmental conditions		
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)
Operating pressure	[MPa]	–0.09 ... +1
	[bar]	–0.9 ... +10
Ambient temperature	[°C]	–10 ... +50
Temperature of medium	[°C]	–10 ... +50
Storage temperature	[°C]	–20 ... +60
Corrosion resistance class CRC[1)]		0 - no corrosion stress

1) More information www.festo.com/x/topic/crc

Ordering data

Duct separation	Weight [g]	Part no.	Type
Duct 1	60	**8029438**	**VABD-S1-1-P1-C**
Duct 3 and duct 5	70	**8029439**	**VABD-S1-1-P2-C**
Ducts 1, 3 and 5	75	**8029440**	**VABD-S1-1-P3-C**
Ducts 1, 3, 5, 12 and 14	75	**8029441**	**VABD-S1-1-P6-C**
Duct 12 and duct 14	60	**8036068**	**VABD-S1-1-P7-C**

Accessories

Intermediate plate NZV

For connecting manifold sub-bases of different sizes


Materials:
Die-cast aluminium, anodised



General technical data	
Based on standard	ISO 5599-1


Dimensions Download CAD data ➔ www.festo.com

For manifold sub-bases of width 42 mm, 52 mm



	B1	B2	B3	D1	D2	D3	H1	H2	L1	L2	L3	L4	T1	T2
NZV-1-2	47	24	23	M6	M5	7	25	7.5	135	115	95	30	13	12

For manifold sub-bases of width 42 mm and 65 mm or 52 mm and 65 mm




	B1	B2	B3	B4	D1	D2	D3	D4	H1	H2	L1	L2	L3	L4	L5	T1	T2
NZV-3-2/1	56	25	24	22	M6	M5	12	9	30	15	190	168	115	52	95	12	10

Accessories

Ordering data	Weight [g]	Part no.	Type
For manifold sub-bases of width 42 mm, 52 mm	393	**164940**	**NZV-1-2**
For manifold sub-bases of width 42 mm and 65 mm or 52 mm and 65 mm	473	**12911**	**NZV-3-2/1**

Dimensions – Manifold assembly

Download CAD data ➔ www.festo.com



[1] Left end plate, end plate kit NEV
[2] Manifold sub-base NAV
[3] Cover plate NDV
[4] Right end plate, end plate kit NEV
[5] Manifold sub-base with angled connections NAW
[6] Hole pattern to ISO 5599-1
[7] Manifold sub-base with angled connections NAVW
[8] Isolating disc NSC


Accessories

Width	B1	B2	B3	B4	B5	B6	B7	B8	B9	D1	D2	D3	D4 ø	D5 ø	D6 ø
42 mm	43	22	42	40	11	7.5	1.5	4	21.6	G1/4	G3/8	G1/8	10	5.5	7
52 mm	56	26	55	50	13	6	5	6	27	G3/8	G1/2	G1/8	11	6.6	9
65 mm	71	30	70	70	15	8	6	6	35.5	G1/2	G1	G1/8	15	9	12
76 mm	82	30	80	80	15	9	8	–	–	G3/4	G1	G1/8	15	9	12

Width	H1	H2	H3	H4	H5	H6	H7	L1	L2	L3	L4	L5	L6	L7	T1
42 mm	81	46	44	50.5	12.5	37	5	110	95	80	28	26	11	11	5.7
52 mm	85	47	45	60	15	40	5	135	115	96	35	30	15	14	6.8
65 mm	99	56	54	66	17.5	45	5	190	168	120	52	38	19	19	9
76 mm	120	58	55	–	–	65	5	215	184	–	56	52	–	–	9

-H- Note: This product conforms to ISO 1179-1 and ISO 228-1.

Accessories



Exhaust air flow control for 3 and 5.



General technical data				
Type		VABF-S1-1-F1B1-C	VABF-S1-2-F1B1-C	GRO-ZP-3-ISO
Based on standard		ISO 5599-1		
Pneumatic vertical stacking		Throttle plate, exhaust air flow control		
Mounting position		Any		
Type of mounting		With through-hole		
Standard nominal flow rate	[l/min]	1100	–	1500
Degree of protection		IP65	IP65	–
		NEMA4	NEMA4	–


Materials	
Housing	Die-cast aluminium
Note on materials	RoHs-compliant

Operating and environmental conditions				
Type		VABF-S1-1-F1B1-C	VABF-S1-2-F1B1-C	GRO-ZP-3-ISO
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]		Compressed air to ISO 8573-1:2010 [7:–:–]
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)		Lubricated operation possible (in which case lubricated operation will always be required)
Operating pressure	[MPa]	–0.09 ... +1	–0.09 ... +1	–
	[bar]	–0.9 ... +10	–0.9 ... +10	0 ... +16
Input pressure 1	[MPa]	–	+0.05 ... +1	–
	[bar]	–	+0.5 ... +10	–
	[psi]	–	7.25 ... 145	–
Ambient temperature	[°C]	–5 ... +50	–5 ... +50	–20 ... +80
Temperature of medium	[°C]	–	–	–20 ... +80

Accessories


Standard nominal flow rate qnN as a function of the turns n of the regulating screw

VABF-S1-1-F1B1-C




[1] Flow control screw from 4 to 5
[2] Flow control screw from 2 to 3

VABF-S1-2-F1B1-C



[1] Flow control screw from 2 to 3
[2] Flow control screw from 4 to 5


GRO-ZP-3-ISO



Accessories

Dimensions Download CAD data ➔ www.festo.com


Throttle plate VABF-S1-...



[1] Captive retaining screws [2] Port pattern to ISO 5599-1

Width	B1	B2	B3	D1	H1	H2	H4	L1	L6	T1
42 mm	39.9	24.3	16.1	9.3	17.5	9.2	28	105.3	32	7.3
52 mm	52	32.5	22.5	13.4	29.5	13.5	45	131	40.9	10


Throttle plate GRO-ZP-3-ISO




[1] Adjusting screw for flow control [2] Captive retaining screws

Width	B1	B2	D1	H1	H2	H3	L1	L2	L3	L5
65 mm	70	48	M8	33	12	16.5	132	64	32	7

Ordering data

Circuit symbol	Description	Width	Weight [g]	Part no.	Type
	Exhaust air flow control	42 mm	220	**549102**	**VABF-S1-1-F1B1-C**
		52 mm	565	**555788**	**VABF-S1-2-F1B1-C**
		65 mm	850	**119674**	**GRO-ZP-3-ISO**

Accessories



Alternative compressed air supply for port 1 of the mounted valve.




General technical data			
Type		VABF-S1-1-P1A3-G38	VABF-S1-2-P1A3-G12
Based on standard		ISO 5599-1	
Pneumatic vertical stacking		Alternative compressed air supply for 1	
Mounting position		Any	
Type of mounting		On individual sub-base, on manifold sub-base	
Standard nominal flow rate	[l/min]	1300	2800
Pneumatic port 1		G3/8	G1/2
Degree of protection		IP65	IP65
		NEMA4	NEMA4

Materials	
Housing	Die-cast aluminium
Note on materials	RoHs-compliant

Operating and environmental conditions			
Type		VABF-S1-1-P1A3-G38	VABF-S1-2-P1A3-G12
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure	[MPa]	–0.09 ... +1	–0.09 ... +1
	[bar]	–0.9 ... +10	–0.9 ... +10
Input pressure 1	[MPa]	–	+0.05 ... +1
	[bar]	–	+0.5 ... +10
	[psi]	–	7.25 ... 145
Ambient temperature	[°C]	–5 ... +50	–5 ... +50

Accessories


Dimensions Download CAD data ➔ www.festo.com




[1] Captive retaining screws [2] Port pattern to ISO 5599-1

Type	B1	B2	D1	H1	H4	L1	L6	T1
VABF-S1-1-P1A3-G38	42.1	24.2	G3/8	32.7	45.3	117.6	35.8	7.9
VABF-S1-2-P1A3-G12	54	31	G1/2	42.4	58.9	136	38	10


Ordering data

Circuit symbol	Description	Width	Standard nominal flow rate [l/min]	Weight [g]	Part no.	Type
	Vertical supply plate	42 mm	1300	340	**549100**	**VABF-S1-1-P1A3-G38**
		52 mm	2800	605	**555785**	**VABF-S1-2-P1A3-G12**

Accessories



Vertical pressure shut-off plate for blocking duct 1 and duct 14 upstream of a valve.




General technical data			
Type		VABF-S1-1-L1D1-C	VABF-S1-2-L1D1-C
Based on standard		ISO 5599-1	
Pneumatic vertical stacking		Shut-off for 1	Alternative compressed air supply for 1
Mounting position		Any	
Type of mounting		On individual sub-base, on manifold sub-base	
Standard nominal flow rate	[l/min]	1200	1950
Pneumatic port 1		G3/8	G1/2
Degree of protection		IP65	IP65
		NEMA4	NEMA4

Materials	
Housing	Die-cast aluminium
Note on materials	RoHs-compliant

Operating and environmental conditions			
Type		VABF-S1-1-L1D1-C	VABF-S1-2-L1D1-C
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure	[MPa]	–0.09 ... +1	–0.09 ... +1
	[bar]	–0.9 ... +10	–0.9 ... +10
Input pressure 1	[MPa]	–	+0.05 ... +1
	[bar]	–	+0.5 ... +10
	[psi]	–	7.25 ... 145
Ambient temperature	[°C]	–5 ... +50	–5 ... +50

Accessories

Dimensions Download CAD data ➔ www.festo.com




[1] Captive retaining screws


[2] Port pattern to ISO 5599-1

Type	B1	B2	D1	H1	H2	H4	L1	L6	T1
VABF-S1-1-L1D1-C	42.1	26.7	12.8	15.6	1.6	45.3	173.8	92	7.9
VABF-S1-2-L1D1-C	54	32.6	14	21.3	1.6	58.7	191.2	93.2	10


Ordering data

Circuit symbol	Description	Width	Standard nominal flow rate [l/min]	Weight [g]	Part no.	Type
	Vertical pressure shut-off plate	42 mm	1200	600	**549103**	**VABF-S1-1-L1D1-C**
		52 mm	1950	1030	**555790**	**VABF-S1-2-L1D1-C**

Accessories



The pressure regulator enables a particular pressure in the regulated port to be set manually upstream or downstream of the valve.



General technical data				
Type		VABF-S1-1-R...	VABF-S1-2-R...	LR-ZP-...-3
Width	[mm]	42	52	65
Based on standard		ISO 5599-1	ISO 5599-1	ISO 5599-1
Pneumatic vertical stacking		Pressure regulator	Pressure regulator	Pressure regulator
Design		–	–	Piston
Regulator function		Output pressure constant	Output pressure constant	–
		With secondary exhausting	With secondary exhausting	–
Mounting position		Any	Any	–
Type of mounting		On individual sub-base	On individual sub-base	–
		On manifold sub-base	On manifold sub-base	–
Optional pressure gauge		possible	possible	–
Pressure gauge connection		With retaining clamp	With retaining clamp	–
Degree of protection		IP65	IP65	–
		NEMA4	NEMA4	–

Materials			
Type	VABF-S1-1-R...	VABF-S1-2-R...	LR-ZP-...-3
Regulator housing	Die-cast aluminium	Die-cast aluminium	Die-cast aluminium, steel
Control section	PA	PA	–
Seals	–	–	NBR
Note on materials	RoHs-compliant	RoHs-compliant	RoHs-compliant
	Free of paint-wetting impairment substances	Free of paint-wetting impairment substances	Contains paint-wetting impairment substances


Operating and environmental conditions				
Type		VABF-S1-1-R...	VABF-S1-2-R...	LR-ZP-...-3
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]		–
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)		–
Input pressure 1	[MPa]	0.05 ... 1	0.05 ... 1	–
	[bar]	+0.5 ... +10	+0.5 ... +10	Max. 14
	[psi]	7.25 ... 145	7.25 ... 145	–
Ambient temperature	[°C]	–5 ... +50	–5 ... +50	–
Certification		–	–	UL – Recognized (OL)

Product weight				
Type		VABF-S1-1-R...	VABF-S1-2-R...	LR-ZP-...-3
Regulated port	1	640 g	1190 g	1220 g
	2	640 g	1230 g	1220 g
	4	640 g	1230 g	1220 g
	2 and 4	920 g	1990 g	1770 g

Accessories

Dimensions Download CAD data ➔ www.festo.com

VABF-S1-1-..., VABF-S1-2-...




[1] Captive retaining screws
[2] Port pattern to ISO 5599-1
[3] Regulator housing
[4] Pressure gauge
[5] Regulator knob, locked
[6] Regulator knob during pressure adjustment

Type	B1	B2	H1	H2	H3	L1	L2	L3	L4	L5	L6	L7	L8	L9	L10	T1
Regulator plate, width 42 mm																
VABF-S1-1-R1...	42.1	23.6	115	112	87.1	–	207.1	–	125.3	–	–	49.4	36	27	9	7.9
VABF-S1-1-R2...						–	–	216.2	125.3	–	–					
VABF-S1-1-R3...						–	–	–	125.3	150.3	216.1					
VABF-S1-1-R4...						311.6	–	–	–	–	–					
VABF-S1-1-R5...						311.6	–	–	–	–	–					
VABF-S1-1-R6...						–	–	216.2	125.3	–	–					
VABF-S1-1-R7...						–	–	–	125.3	150.3	216.1					
Regulator plate, width 52 mm																
VABF-S1-2-R1...	54	23.6	182	167	94.4	–	250.2	–	152.2	–	–	49.4	48	38	12	10
VABF-S1-2-R2...						–	–	264.2	152.2	–	–					
VABF-S1-2-R3...						–	–	–	152.2	180.2	264.2					
VABF-S1-2-R4...						380.4	–	–	–	–	–					
VABF-S1-2-R5...						380.4	–	–	–	–	–					
VABF-S1-2-R6...						–	–	264.2	152.2	–	–					
VABF-S1-2-R7...						–	–	–	152.2	180.2	264.2					

Accessories

Dimensions Download CAD data ➔ www.festo.com

LR-ZP-...-3




[1] Pressure gauge connection G1/8
[2] Adjusting screw
[3] Hole pattern to ISO 5599-1
[4] Captive retaining screws
[5] Rotary knob


Type	B	H	H1	H2	L1	L2	L3	L4	L5	L6	L7	L8
Regulator plate, width 65 mm												
LR-ZP-P-D-3	70	63	65	14	201.5	–	274	–	–	–	119	–
LR-ZP-B-D-3					201.5	–	–	–	274	72.5	–	119
LR-ZP-A-D-3					201.5	–	–	403	–	–	119	119
LR-ZP-A/B-D-3					201.5	260	–	–	–	–	119	–

Flow rate qn as a function of output pressure p2








LR-ZP-A-D-3, LR-ZP-B-D-3, LR-ZP-A/B-D-3



LR-ZP-P-D-3










Accessories

Ordering data	Regulated port	Regulator	Control range	Part no.	Type
Regulator plate, width 42 mm					
	1	P	0.05 ... 0.6 MPa 0.5 ... 6 bar 7.25 ... 87 psi	**546817**	**VABF-S1-1-R1C2-C-6**
			0.05 ... 1 MPa 0.5 ... 10 bar 7.25 ... 145 psi	**546818**	**VABF-S1-1-R1C2-C-10**
	2	B	0.05 ... 0.6 MPa 0.5 ... 6 bar 7.25 ... 87 psi	**546821**	**VABF-S1-1-R2C2-C-6**
			0.05 ... 1 MPa 0.5 ... 10 bar 7.25 ... 145 psi	**546822**	**VABF-S1-1-R2C2-C-10**
	2, reversible	B	0.05 ... 0.6 MPa 0.5 ... 6 bar 7.25 ... 87 psi	**546827**	**VABF-S1-1-R6C2-C-6**
			0.05 ... 1 MPa 0.5 ... 10 bar 7.25 ... 145 psi	**546828**	**VABF-S1-1-R6C2-C-10**
	4	A	0.05 ... 0.6 MPa 0.5 ... 6 bar 7.25 ... 87 psi	**546819**	**VABF-S1-1-R3C2-C-6**
			0.05 ... 1 MPa 0.5 ... 10 bar 7.25 ... 145 psi	**546820**	**VABF-S1-1-R3C2-C-10**
	4, reversible	A	0.05 ... 0.6 MPa 0.5 ... 6 bar 7.25 ... 87 psi	**546829**	**VABF-S1-1-R7C2-C-6**
			0.05 ... 1 MPa 0.5 ... 10 bar 7.25 ... 145 psi	**546830**	**VABF-S1-1-R7C2-C-10**
	2 and 4	AB	0.05 ... 0.6 MPa 0.5 ... 6 bar 7.25 ... 87 psi	**546823**	**VABF-S1-1-R4C2-C-6**
			0.05 ... 1 MPa 0.5 ... 10 bar 7.25 ... 145 psi	**546824**	**VABF-S1-1-R4C2-C-10**
	2 and 4, reversible	AB	0.05 ... 0.6 MPa 0.5 ... 6 bar 7.25 ... 87 psi	**546825**	**VABF-S1-1-R5C2-C-6**
			0.05 ... 1 MPa 0.5 ... 10 bar 7.25 ... 145 psi	**546826**	**VABF-S1-1-R5C2-C-10**





Accessories

Ordering data

	Regulated port	Regulator	Control range	Part no.	Type
Regulator plate, width 52 mm					
	1	P	0.05 ... 0.6 MPa 0.5 ... 6 bar 7.25 ... 87 psi	**555757**	**VABF-S1-2-R1C2-C-6**
			0.05 ... 1 MPa 0.5 ... 10 bar 7.25 ... 145 psi	**555758**	**VABF-S1-2-R1C2-C-10**
	2	B	0.05 ... 0.6 MPa 0.5 ... 6 bar 7.25 ... 87 psi	**555759**	**VABF-S1-2-R2C2-C-6**
			0.05 ... 1 MPa 0.5 ... 10 bar 7.25 ... 145 psi	**555760**	**VABF-S1-2-R2C2-C-10**
	2, reversible	B	0.05 ... 0.6 MPa 0.5 ... 6 bar 7.25 ... 87 psi	**555767**	**VABF-S1-2-R6C2-C-6**
			0.05 ... 1 MPa 0.5 ... 10 bar 7.25 ... 145 psi	**555768**	**VABF-S1-2-R6C2-C-10**
	4	A	0.05 ... 0.6 MPa 0.5 ... 6 bar 7.25 ... 87 psi	**555761**	**VABF-S1-2-R3C2-C-6**
			0.05 ... 1 MPa 0.5 ... 10 bar 7.25 ... 145 psi	**555762**	**VABF-S1-2-R3C2-C-10**
	4, reversible	A	0.05 ... 0.6 MPa 0.5 ... 6 bar 7.25 ... 87 psi	**555769**	**VABF-S1-2-R7C2-C-6**
			0.05 ... 1 MPa 0.5 ... 10 bar 7.25 ... 145 psi	**555770**	**VABF-S1-2-R7C2-C-10**
	2 and 4	AB	0.05 ... 0.6 MPa 0.5 ... 6 bar 7.25 ... 87 psi	**555763**	**VABF-S1-2-R4C2-C-6**
			0.05 ... 1 MPa 0.5 ... 10 bar 7.25 ... 145 psi	**555764**	**VABF-S1-2-R4C2-C-10**
	2 and 4, reversible	AB	0.05 ... 0.6 MPa 0.5 ... 6 bar 7.25 ... 87 psi	**555765**	**VABF-S1-2-R5C2-C-6**
			0.05 ... 1 MPa 0.5 ... 10 bar 7.25 ... 145 psi	**555766**	**VABF-S1-2-R5C2-C-10**

Accessories


Ordering data

	Regulated port	Regulator	Control range	Part no.	Type
Regulator plate, width 65 mm					
	1	P	0 ... 12 bar	**35968**	**LR-ZP-P-D-3**
	2	B	0.5 ... 12 bar	**35426**	**LR-ZP-B-D-3**
	4	A	0.5 ... 12 bar	**35971**	**LR-ZP-A-D-3**
	2, 4	AB	0.5 ... 12 bar	**35429**	**LR-ZP-A/B-D-3**

Ordering data – Accessories

	Width	Weight [g]	Part no.	Type
Pressure gauge for intermediate pressure regulator plates LR-ZP	65 mm	64.5	**345395**	**MA-40-16-1/8**








Ordering data

	Description		Cable length [m]	Part no.	Type
Pilot valve for valves with 8 mm armature tube					
	Conforms to ISO 15218	Manual override detenting, non-detenting	–	**8028540**	**VSCS-B-M32C-MD-WB-F8**
		Manual override with accessory detenting, non-detenting	–	**8028541**	**VSCS-B-M32C-MT-WB-F8**
		Manual override non-detenting	–	**8028539**	**VSCS-B-M32C-MH-WB-F8**
		Manual override concealed	–	**8028542**	**VSCS-B-M32C-M-WB-F8**

-H- Note: This product conforms to ISO 1179-1 and ISO 228-1.








Accessories

Ordering data









	Description		Cable length [m]	Part no.	Type
Solenoid coil MSF					
	Solenoid coil	12 V DC	–	**34410**	**MSFG-12-OD**
		24 V DC and 42 V AC, 50 ... 60 Hz	–	**34411**	**MSFG-24/42-50/60-OD**
		42 V DC	–	**34413**	**MSFG-42-OD**
		24 V AC	–	**34415**	**MSFW-24-5 0/60-OD**
		48 V AC, 50 ... 60 Hz	–	**34418**	**MSFW-48-5 0/60-OD**
		110 V AC, 50 ... 60 Hz and 120 V AC, 60 Hz	–	**34420**	**MSFW-110-5 0/60-OD**
		230 V AC, 50 ... 60 Hz and 240 V AC, 60 Hz	–	**34422**	**MSFW-230-5 0/60-OD**
		240 V AC, 50 ... 60 Hz	–	**34424**	**MSFW-240-5 0/60-OD**
	Solenoid coil with socket MSSD	12 V DC	–	**4526**	**MSFG-12**
		24 V DC and 42 V AC, 50 ... 60 Hz	–	**4527**	**MSFG-2 4/42-5 0/60**
		24 V AC	–	**4534**	**MSFW-24-5 0/60**
		110 V AC, 50 ... 60 Hz and 120 V AC, 60 Hz	–	**6720**	**MSFW-110-5 0/60**
		230 V AC, 50 ... 60 Hz and 240 V AC, 60 Hz	–	**4540**	**MSFW-230-5 0/60**
	Solenoid coil for ATEX environment	24 V DC	1	**8059804**	**VACF-B-K1-1-1-EX4-M**
			5	**8059805**	**VACF-B-K1-1-5-EX4-M**
		24 V AC, 50 ... 60 Hz	1	**8059808**	**VACF-B-K1-1A-1-EX4-M**
		110 V AC, 50 ... 60 Hz	1	**8059811**	**VACF-B-K1-16B-1-EX4-M**
			5	**8059812**	**VACF-B-K1-16B-5-EX4-M**
		230 V AC, 50 ... 60 Hz	1	**8059809**	**VACF-B-K1-3A-1-EX4-M**
			5	**8059810**	**VACF-B-K1-3A-5-EX4-M**
Solenoid coils for valves with 8 mm armature tube					
	Plug pattern to EN 175301-803, type A	12 V DC	–	**8030821**	**VACF-A-A1-5**
		24 V DC	–	**8030822**	**VACF-A-A1-1**
		48 V DC	–	**8030823**	**VACF-A-A1-7**
		24 V AC	–	**8030824**	**VACF-A-A1-1A**
		48 V AC	–	**8030825**	**VACF-A-A1-7A**
		110/120 V AC	–	**8030826**	**VACF-A-A1-16B**
		230/240 V AC	–	**8030828**	**VACF-A-A1-3W**
	Plug pattern to industry standard type B (11 mm)	12 V DC	–	**8030801**	**VACF-B-B2-5**
		24 V DC	–	**8030802**	**VACF-B-B2-1**
		48 V DC	–	**8030803**	**VACF-B-B2-7**
		24 V AC	–	**8030804**	**VACF-B-B2-1A**
		48 V AC	–	**8030805**	**VACF-B-B2-7A**
		110/120 V AC	–	**8030806**	**VACF-B-B2-16B**
		230/240 V AC	–	**8030808**	**VACF-B-B2-3W**
	Plug pattern to EN 175301-803, type C	12 V DC	–	**8030810**	**VACF-B-C1-5**
		24 V DC	–	**8030811**	**VACF-B-C1-1**
		48 V DC	–	**8030812**	**VACF-B-C1-7**
		24 V AC	–	**8030813**	**VACF-B-C1-1A**
		48 V AC	–	**8030814**	**VACF-B-C1-7A**
		110/120 V AC	–	**8030815**	**VACF-B-C1-16B**
		230/240 V AC	–	**8030817**	**VACF-B-C1-3W**
	Plug M12x1, A-coded to EN 61076-2-101, 2-pin	24 V DC: 3.4 W	–	**8150876**	**VACF-B-R3-1L**
		24VDC: NS1,2: HS3.3	–	**8150873**	**VACF-B-R3-1RAL**
	Plug M12x1 A-coded according to EN 61076-2-101 4-pin, assignment according to DESINA	24 V DC: 3.4 W	–	**8150877**	**VACF-B-R4-1L**
		24VDC: NS1,2: HS3.3	–	**8150880**	**VACF-B-R4-1RAL**

Accessories








Ordering data

	Description			Cable length [m]	Part no.	Type
Electrical accessories for solenoid coil MSF						
	Angled socket	Screw terminal	Cable fitting Pg9	–	**34431**	**MSSD-F**
			Cable connector M16	–	**59710**	**MSSD-F-M16**
	PUR cable sheath, connection technology M12x1 A-coded	24 AC/DC	• Signal status indication • Protective circuit	0.3	**3679773**	**NEBV-B2W3F-P-K-0.3-N-M12W3**
				0.6	**3679774**	**NEBV-B2W3F-P-K-0.6-N-M12W3**
		110 AC/DC	–	0.3	**3579463**	**NEBV-B2W3-K-0.3-N-M12W3**
				0.6	**3579464**	**NEBV-B2W3-K-0.6-N-M12W3**
	PUR cable sheath	24 AC/DC	• Signal status indication • Protective circuit	0.6	**3679778**	**NEBV-B2W3F-P-K-0.6-N-LE3**
		230 AC/DC	–	0.6	**3579468**	**NEBV-B2W3-K-0.6-N-LE3**
	PVC cable sheath	24 V DC	Signal status indication	2.5	**30935**	**KMF-1-24DC-2.5-LED**
				5	**30937**	**KMF-1-24DC-5-LED**
				10	**193458**	**KMF-1-24DC-10-LED**
		230 V AC	–	2.5	**30936**	**KMF-1-230AC-2.5**
				5	**30938**	**KMF-1-230AC-5**
	Illuminating seal	12 ... 24 V DC	Signal status indication	–	**19143**	**MF-LD-12-24DC**
		230 V DC/V AC	Signal status indication	–	**19144**	**MF-LD-230AC**
Electrical accessories for solenoid coil MD						
	Angled socket	Screw terminal	Cable fitting Pg9	–	**34583**	**MSSD-C**
			Cable connector M16	–	**539709**	**MSSD-C-M16**
	PUR cable sheath, connection technology M12x1 A-coded	24 AC/DC	• Signal status indication • Protective circuit	0.3	**3679771**	**NEBV-A1W3F-P-K-0.3-N-M12W3**
				0.6	**3679772**	**NEBV-A1W3F-P-K-0.6-N-M12W3**
		110 AC/DC	–	0.3	**3579461**	**NEBV-A1W3-K-0.3-N-M12W3**
				0.6	**3579462**	**NEBV-A1W3-K-0.6-N-M12W3**
	PUR cable sheath	24 AC/DC	• Signal status indication • Protective circuit	0.6	**3679776**	**NEBV-A1W3F-P-K-0.6-N-LE3**
		230 AC/DC	–	0.6	**3579466**	**NEBV-A1W3-K-0.6-N-LE3**
	PVC cable sheath	24 V DC	Signal status indication	2.5	**30931**	**KMC-1-24DC-2.5-LED**
				5	**30933**	**KMC-1-24DC-5-LED**
				10	**193459**	**KMC-1-24DC-10-LED**
		230 V AC	–	2.5	**30932**	**KMC-1-230AC-2.5**
				5	**30934**	**KMC-1-230AC-5**
	Illuminating seal	12 ... 24 V DC	Signal status indication	–	**19145**	**MC-LD-12-24DC**
		230 V DC/V AC	Signal status indication	–	**19146**	**MC-LD-230AC**
Electrical accessories for valves with square plug type B to industry standard						
	Angled socket	Via screw terminals	Cable fitting Pg9	–	**34431**	**MSSD-F**
			Cable connector M16	–	**539710**	**MSSD-F-M16**
	PVC cable sheath	24 V DC	Signal status indication	2.5 m	**30935**	**KMF-1-24DC-2.5-LED**
				5 m	**30937**	**KMF-1-24DC-5-LED**
				10 m	**193458**	**KMF-1-24-10-LED**
	Illuminating seal	24 V DC	Signal status indication	–	**19143**	**MF-LD-12-24DC**

Accessories

Ordering data	Description			Cable length [m]	Part no.	Type
Electrical accessories for electrical connection Type A according to EN 175301-803						
	Angled socket	Screw terminal	Cable fitting Pg9	–	**34583**	**MSSD-C**
			Cable connector M16	–	**539709**	**MSSD-C-M16**
			Cable connector M20x1.5	–	**550067**	**MSSD-N**
	PUR cable sheath, connection technology M12x1 A-coded	24 AC/DC	• Signal status indication • Protective circuit	0.3	**3679771**	**NEBV-A1W3F-P-K-0.3-N-M12W3**
				0.6	**3679772**	**NEBV-A1W3F-P-K-0.6-N-M12W3**
		110 AC/DC	–	0.3	**3579461**	**NEBV-A1W3-K-0.3-N-M12W3**
				0.6	**3579462**	**NEBV-A1W3-K-0.6-N-M12W3**
	PUR cable sheath	24 AC/DC	• Signal status indication • Protective circuit	0.6	**3679776**	**NEBV-A1W3F-P-K-0.6-N-LE3**
		230 AC/DC	–	0.6	**3579466**	**NEBV-A1W3-K-0.6-N-LE3**
	PVC cable sheath	24 V DC	Signal status indication	2.5	**30931**	**KMC-1-24DC-2.5-LED**
				5	**30933**	**KMC-1-24DC-5-LED**
				10	**193459**	**KMC-1-24DC-10-LED**
		230 V AC	–	2.5	**30932**	**KMC-1-230AC-2.5**
				5	**30934**	**KMC-1-230AC-5**
	Illuminating seal	12 ... 24 V DC	Signal status indication	–	**19145**	**MC-LD-12-24DC**
		230 V DC/V AC	Signal status indication	–	**19146**	**MC-LD-230AC**
Electrical accessories for electrical connection Type B						
	Angled socket	Screw terminal	Cable fitting Pg9	–	**34431**	**MSSD-F**
			Cable connector M16	–	**59710**	**MSSD-F-M16**
	PUR cable sheath, connection technology M12x1 A-coded	24 AC/DC	• Signal status indication • Protective circuit	0.3	**3679773**	**NEBV-B2W3F-P-K-0.3-N-M12W3**
				0.6	**3679774**	**NEBV-B2W3F-P-K-0.6-N-M12W3**
		110 AC/DC	–	0.3	**3579463**	**NEBV-B2W3-K-0.3-N-M12W3**
				0.6	**3579464**	**NEBV-B2W3-K-0.6-N-M12W3**
	PUR cable sheath	24 AC/DC	• Signal status indication • Protective circuit	0.6	**3679778**	**NEBV-B2W3F-P-K-0.6-N-LE3**
		230 AC/DC	–	0.6	**3579468**	**NEBV-B2W3-K-0.6-N-LE3**
	PVC cable sheath	24 V DC	Signal status indication	2.5	**30935**	**KMF-1-24DC-2.5-LED**
				5	**30937**	**KMF-1-24DC-5-LED**
				10	**193458**	**KMF-1-24DC-10-LED**
		230 V AC	–	2.5	**30936**	**KMF-1-230AC-2.5**
				5	**30938**	**KMF-1-230AC-5**
	Illuminating seal	12 ... 24 V DC	Signal status indication	–	**19143**	**MF-LD-12-24DC**
		230 V DC/V AC	Signal status indication	–	**19144**	**MF-LD-230AC**
Electrical accessories for electrical connection Type C according to EN 175301-803						
	Angled socket	0 ... 30 V DC	Cable connector M12	–	**570367**	**MSSD-EB-M12-24VDC-SD-EX**
		0 ... 300 V DC	Cable connector Pg7	–	**151687**	**MSSD-EB**
		–	Cable connector M12	–	**539712**	**MSSD-EB-M12**
	PVC cable sheath	24 V DC	• Signal status indication • Protective circuit	2.5 m	**8032623**	**NEBV-C1SW2L-P-K-2.5-N-LE2-S9**
				5 m	**8032626**	**NEBV-C1SW2L-P-K-5-N-LE2-S9**
				10 m	**8032627**	**NEBV-C1SW2L-P-K-10-N-LE2-S9**
		230 V DC/V AC	Signal status indication	2.5 m	**8032628**	**NEBV-C1SW3-K-2.5-N-LE3-S9**
				5 m	**8032629**	**NEBV-C1SW3-K-5-N-LE3-S9**

Accessories

Ordering data	Description			Part no.	Type
Electrical accessories for valves with central plug					
	Angled socket, M12x1 A-coded according to EN 61076-2-101, 4-pin, screw terminal			**8162292**	**NECB-M12W4-C2**
	Modular system for a choice of connecting cables a Internet: neba		0.1 ... 20 m	**8078221**	**NEBA-...**
	Straight socket, M12x1, 5-pin Open end, 4-core		2.5 m	**8078239**	**NEBA-M12G5-U-2.5-N-LE4**
			5 m	**8078240**	**NEBA-M12G5-U-5-N-LE4**
	Angled socket, M12x1, 5-pin, Open end, 4-core		2.5 m	**8078248**	**NEBA-M12W5-U-2.5-N-LE4**
			5 m	**8078249**	**NEBA-M12W5-U-5-N-LE4**
Pressure gauge					
	With cartridge connector, for pressure regulator	Display range 0 ... 16 bar		**543487**	**PAGN-26-16-P10**
		Display range 0 ... 10 bar		**543488**	**PAGN-26-10-P10**
Seal					
	Enables the valves with central plug M12, 3-pin, to be mounted on the sub-bases of the valve terminal VTS/VTSA-F			**571343**	**VABD-S2-1-S-C**
Inscription label					
	Inscription label	6x10 mm	Labelling 64	**18576**	**IBS-6X10**
	Inscription label for valves	17x9 mm	Labelling 24	**161937**	**IBS-9x17**
	Inscription label for manifold sub-bases		Pack size 5	**8037164**	**ASCF-M-S1**
	Clip-on inscription label holder for valve cap, for valves with central plug M12, 3-pin			**540888**	**ASCF-T-S6**
	Inscription label holders for inscription labels 6x10 mm, for valves		Pack size 10	**561109**	**VMPAL-ST-AP-10**
Manual override					
	For manual override non-detenting or covered	For valves with square plug type B to industry standard		**8049538**	**VAMC-B10-20-CH2-S**
	Cover cap for manual override, non-detenting	For valves with central plug M12, 3-pin		**541010**	**VAMC-S6-CH**
	Cover cap for manual override, concealed	For valves with central plug M12, 3-pin		**541011**	**VAMC-S6-CS**
	Heavy-duty cover cap for manual override, non-detenting, detenting via accessory	For valves with central plug M12, 3-pin		**4105147**	**VAMC-B-S6-CTR**
	Tool for manual override	For MFH valves		**157651**	**AHB-MD/MF/MV**
		For heavy-duty cover cap, detenting position		**1662543**	**AHB-MEB-B**